



SAFETY DATA SHEET 5W-40 FULLY SYNTHETIC OIL

SECTION 1: IDENTIFICATION OF THE SUBSTANCE/MIXTURE AND OF THE COMPANY/UNDERTAKING

1.1. Product identifier

Product name 5W-40 FULLY SYNTHETIC OIL
Product No. DRF001, DRF005, DRF025, DRF199, GFY025, GFY050, HBS105, HBS106, JSB126, JSB130, JSB131, MAC310, MAC939, MOR126, XAK010, XAK050, XAK455, XFS401, YAK025, YAK199, YAK020

1.2. Relevant identified uses of the substance or mixture and uses advised against

Identified uses Engine oil.

1.3. Details of the supplier of the safety data sheet

Supplier TETROSYL LIMITED
BEVIS GREEN WORKS
WALMERSLEY
BURY
BL9 6RE
0161 764 5981
0161 797 5899
info@tetrosyl.com
Manufacturer TETROSYL LIMITED
BEVIS GREEN WORKS
WALMERSLEY
BURY
BL9 6RE
0161 764 5981
0161 797 5899
info@tetrosyl.com

1.4. Emergency telephone number

0161 764 5981

SECTION 2: HAZARDS IDENTIFICATION

2.1. Classification of the substance or mixture

Classification (EC 1272/2008)
Physical and Chemical Hazards Not classified.
Human health Not classified.
Environment Not classified.

Classification (1999/45/EEC) Not classified.

The Full Text for all R-Phrases and Hazard Statements are Displayed in Section 16.

2.2. Label elements

5W-40 FULLY SYNTHETIC OIL

Label In Accordance With (EC) No. 1272/2008

No pictogram required.

Precautionary Statements

P101	If medical advice is needed, have product container or label at hand.
P102	Keep out of reach of children.

2.3. Other hazards**SECTION 3: COMPOSITION/INFORMATION ON INGREDIENTS****3.2. Mixtures**

ORGANOMOLYBDENUM AMIDE		<0.5
CAS-No.: 445409-27-8	EC No.:	
Classification (EC 1272/2008) Aquatic Chronic 2 - H411	Classification (67/548/EEC) N;R51/53.	
ZINC DIALKYLDITHIOPHOSPHATE		<1%
CAS-No.: 68649-42-3	EC No.: 272-028-3	
Classification (EC 1272/2008) Skin Irrit. 2 - H315 Eye Dam. 1 - H318 Aquatic Chronic 2 - H411	Classification (67/548/EEC) Xi;R38,R41. N;R51/53.	

The Full Text for all R-Phrases and Hazard Statements are Displayed in Section 16.

SECTION 4: FIRST AID MEASURES**4.1. Description of first aid measures**

General information

Get medical attention if any discomfort continues. Remove affected person from source of contamination.

General first aid, rest, warmth and fresh air.

Inhalation

In case of inhalation of spray mist: Move person into fresh air and keep at rest.

Ingestion

Contact physician if larger quantity has been consumed. Rinse mouth thoroughly.

Skin contact

Promptly wash contaminated skin with soap or mild detergent and water. Promptly remove clothing if soaked through and wash as above. Contact physician if irritation continues or sores develop.

Eye contact

Immediately flush with plenty of water for up to 15 minutes. Remove any contact lenses and open eyes wide apart. Do not rub eye.

4.2. Most important symptoms and effects, both acute and delayed

General information

The severity of the symptoms described will vary dependant of the concentration and the length of exposure.

NOTE! Effects may be delayed. Keep affected person under observation.

5W-40 FULLY SYNTHETIC OIL**Inhalation**

May cause an asthma-like shortness of breath. Vapours may cause headache, fatigue, dizziness and nausea.

Ingestion

May cause discomfort if swallowed. May cause stomach pain or vomiting. May cause nausea, headache, dizziness and intoxication.

Skin contact

Prolonged or repeated contact with skin may cause redness, itching, irritation and eczema/chapping. Allergic rash.

Eye contact

May cause temporary eye irritation.

4.3. Indication of any immediate medical attention and special treatment needed

No recommendation given, but first aid may still be required in case of accidental exposure, inhalation or ingestion of this chemical. If in doubt, GET MEDICAL ATTENTION PROMPTLY!

SECTION 5: FIREFIGHTING MEASURES**5.1. Extinguishing media****Extinguishing media**

Use: Foam, carbon dioxide or dry powder. Use fire-extinguishing media appropriate for surrounding materials.

Unsuitable extinguishing media

Do not use water jet as an extinguisher, as this will spread the fire.

5.2. Special hazards arising from the substance or mixture**Hazardous combustion products**

During fire, toxic gases (CO, CO₂) are formed.

Unusual Fire & Explosion Hazards

No unusual fire or explosion hazards noted.

Specific hazards

Fire creates: Carbon monoxide (CO). Carbon dioxide (CO₂).

5.3. Advice for firefighters

Protective equipment for fire-fighters

Leave danger zone immediately.

SECTION 6: ACCIDENTAL RELEASE MEASURES**6.1. Personal precautions, protective equipment and emergency procedures**

Follow precautions for safe handling described in this safety data sheet. Avoid inhalation of vapours and aerosol spray. Avoid contact with eyes and prolonged skin contact. Provide adequate ventilation. In case of spills, beware of slippery floors and surfaces.

6.2. Environmental precautions

Avoid discharge into drains, water courses or onto the ground. The product should not be dumped in nature but collected and delivered according to agreement with the local authorities.

6.3. Methods and material for containment and cleaning up

Stop leak if possible without risk. Extinguish all ignition sources. Avoid sparks, flames, heat and smoking. Ventilate. Provide ventilation and confine spill. Do not allow runoff to sewer. Collect with absorbent, non-combustible material into suitable containers.

6.4. Reference to other sections

Wear protective clothing as described in Section 8 of this safety data sheet. Collect and dispose of spillage as indicated in section 13.

SECTION 7: HANDLING AND STORAGE

5W-40 FULLY SYNTHETIC OIL

7.1. Precautions for safe handling

Good personal hygiene is necessary. Wash hands and contaminated areas with water and soap before leaving the work site. Do not eat, drink or smoke when using the product. Avoid forming spray/aerosol mists. Provide good ventilation. Avoid contact with skin and eyes. Always remove oil with soap and water or skin cleaning agent, never use organic solvents. Do not use oil-contaminated clothing or shoes, and do not put rags moistened with oil into pockets.

7.2. Conditions for safe storage, including any incompatibilities

Keep upright. Store in tightly closed original container.

7.3. Specific end use(s)

The identified uses for this product are detailed in Section 1.2.

SECTION 8: EXPOSURE CONTROLS/PERSONAL PROTECTION

8.1. Control parameters

8.2. Exposure controls

Protective equipment



Engineering measures

Provide adequate ventilation. Observe Occupational Exposure Limits and minimise the risk of inhalation of vapours.

Respiratory equipment

No specific recommendations.

Hand protection

Protective gloves should be used if there is a risk of direct contact or splash. Nitrile gloves are recommended, but be aware that the liquid may penetrate the gloves. Frequent change is advisable.

Eye protection

Wear approved, tight fitting safety glasses where splashing is probable.

Other Protection

Wear suitable protective clothing as protection against splashing or contamination.

Hygiene measures

Wash contaminated clothing before reuse. Wash promptly with soap & water if skin becomes contaminated.

SECTION 9: PHYSICAL AND CHEMICAL PROPERTIES

9.1. Information on basic physical and chemical properties

Appearance	Clear liquid.
Colour	Brown.
Odour	Mineral. Oil smell.
Solubility	Insoluble in water
Initial boiling point and boiling range (°C)	>250°C
Melting point (°C)	
Not determined.	
	Scientifically unjustified.
Relative density	0.855

5W-40 FULLY SYNTHETIC OIL

Vapour density (air=1)

Not determined.

Scientifically unjustified.

Vapour pressure

Not determined.

Scientifically unjustified.

Evaporation rate

Not determined.

Scientifically unjustified.

Evaporation Factor

Not determined.

Scientifically unjustified.

pH-Value, Conc. Solution

Not determined.

Scientifically unjustified.

Viscosity

85.2 cSt @ 40°C

Decomposition temperature (°C)

Not determined.

Scientifically unjustified.

Odour Threshold, Lower

Not determined.

Scientifically unjustified.

Odour Threshold, Upper

Not determined.

Scientifically unjustified.

Flash point (°C)

220°C

Auto Ignition Temperature (°C)

Not determined.

Scientifically unjustified.

Flammability Limit - Lower(%)

Not determined.

Scientifically unjustified.

Flammability Limit - Upper(%)

Not determined.

Scientifically unjustified.

Partition Coefficient

(N-Octanol/Water)

Not determined.

Scientifically unjustified.

Oxidising properties

Not determined.

9.2. Other information

None.

SECTION 10: STABILITY AND REACTIVITY**10.1. Reactivity**

No specific reactivity hazards associated with this product.

10.2. Chemical stability

No particular stability concerns.

10.3. Possibility of hazardous reactions

Not applicable.

5W-40 FULLY SYNTHETIC OIL**10.4. Conditions to avoid**

No specific conditions are likely to result in a hazardous situation.

10.5. Incompatible materials

Materials To Avoid

Strong oxidising substances.

10.6. Hazardous decomposition products

Thermal decomposition or combustion may liberate carbon oxides and other toxic gases or vapours.

SECTION 11: TOXICOLOGICAL INFORMATION**11.1. Information on toxicological effects**

Toxicological information

No information available.

SECTION 12: ECOLOGICAL INFORMATION

Ecotoxicity

The product components are not classified as environmentally hazardous. However, this does not exclude the possibility that large or frequent spills can have a harmful or damaging effect on the environment.

12.1. Toxicity

Acute Toxicity - Fish

Not available.

Acute Toxicity - Aquatic Invertebrates

Not available.

12.2. Persistence and degradability

Degradability

There are no data on the degradability of this product.

12.3. Bioaccumulative potential

Bioaccumulative potential

No data available on bioaccumulation.

Partition coefficient

Not determined.

Scientifically unjustified.

12.4. Mobility in soil

Mobility:

The product is insoluble in water.

12.5. Results of PBT and vPvB assessment

Not Classified as PBT/vPvB by current EU criteria.

12.6. Other adverse effects

Not available.

SECTION 13: DISPOSAL CONSIDERATIONS

General information

Waste is classified as hazardous waste. Disposal to licensed waste disposal site in accordance with the local Waste Disposal Authority.

5W-40 FULLY SYNTHETIC OIL**13.1. Waste treatment methods**

Confirm disposal procedures with environmental engineer and local regulations.

SECTION 14: TRANSPORT INFORMATION**14.1. UN number****14.2. UN proper shipping name****14.3. Transport hazard class(es)****14.4. Packing group****14.5. Environmental hazards****14.6. Special precautions for user****14.7. Transport in bulk according to Annex II of MARPOL73/78 and the IBC Code****SECTION 15: REGULATORY INFORMATION****15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture****EU Legislation**

Regulation (EC) No 1907/2006 of the European Parliament and of the Council of 18 December 2006 concerning the Registration, Evaluation, Authorisation and Restriction of Chemicals (REACH), establishing a European Chemicals Agency, amending Directive 1999/45/EC and repealing Council Regulation (EEC) No 793/93 and Commission Regulation (EC) No 1488/94 as well as Council Directive 76/769/EEC and Commission Directives 91/155/EEC, 93/67/EEC, 93/105/EC and 2000/21/EC, including amendments.

15.2. Chemical Safety Assessment

No chemical safety assessment has been carried out.

SECTION 16: OTHER INFORMATION**Revision Comments**

NOTE: Lines within the margin indicate significant changes from the previous revision.

Revision Date 30/10/2012

Revision 22

Supersedes date 14/06/2012 V21

Safety Data Sheet Status Approved.

Risk Phrases In Full

R38 Irritating to skin.

NC Not classified.

R41 Risk of serious damage to eyes.

R51/53 Toxic to aquatic organisms, may cause long-term adverse effects in the aquatic environment.

Hazard Statements In Full

H315 Causes skin irritation.

H318 Causes serious eye damage.

H411 Toxic to aquatic life with long lasting effects.