

6.04116.50 DG 25 set

Compressed Air Die Grinder DG 25 set



- For sanding/grinding, deburring, moulding/routing and engraving
- Integrated speed control
- Ergonomic, partially rubber-coated housing: cold-insulating, non-slip and low vibration for comfortable work
- Safety lever for protection against accidental start up
- Rotatable exhaust guide at the side of the housing.

Comparative technical values

Operating pressure	6,2 bar
Air requirement	300 l/min
Revolutions	25.000 /min
Weight	0,43 kg

Scope of delivery

5 mounted points each (3 mm and 6 mm), 2 open-jawed spanners (13 mm, 16 mm), Plug-in nipple 1/4", 2 collets (3 mm, 6 mm), Plastic carry case