



FEDERATION EUROPEENNE DES
FABRICANTS DE PRODUITS ABRASIFS



Confidential

EC-Technical Data Sheet

Reference: **69936625778**

41_150x1.6X12.7_5D10A601RB25

Version/date: 07/03/13

page 1 of 4

TECHNICAL DATA SHEET FOR ORGANIC BONDED ABRASIVES
Voluntary product information based on the format of a safety data sheet

1. Identification of Product and Company:

Product Name:

Norton

69936625778 41_150x1.6x12.7_5D10A601RB25

Application

Organic bonded Abrasive cut-off for cutting

Company identification:

Company: Saint-Gobain Abrasives S.P.A

Address: Via per Cesano Boscone 4

20094 Corsico (Mi) Italy

Phone: (+39) 024485306

Fax: (+39) 0245101434

E-mail:

Emergency number:

.....

2. Hazards Identification

Not applicable

Abrasives are articles and not dangerous substances or preparations according to directive 1999/45/EC.
See also section 8 and 16.

3. Composition/Information on Ingredients

The product contains the following ingredients which are classified according to 67/548/EEC and 99/45/EC

| Name | EC Nr. (ELINCS/EINECS) | CAS N° | Concentration range | Classification |
|------|---------------------------|--------|------------------------|----------------|
| | | | | |
| | | | | |
| | | | | |

(For the full text of the R-phrases see section 16)

4. First Aid Measures

See also section 8 and 16

Inhalation:

Not possible, due to the form of the product

Eye contact:

Not possible, due to the form of the product

Skin contact:

No harmful effects known

Ingestion:

Not likely, due to the form of the product; if necessary contact physician

Note to physician:

Not available.

5. Fire Fighting Measures

Toxic fumes may occur. Use respiratory protective equipment.



FEDERATION EUROPEENNE DES
FABRICANTS DE PRODUITS ABRASIFS



Confidential

EC-Technical Data Sheet
Reference: **69936625778**
41_150x1.6X12.7_5D10A601RB25
Version/date: 07/03/13
page 2 of 4

Extinguishing media: water, foam, sand, powder or CO₂ as appropriate for surrounding materials

6. Accidental release measures

Not applicable.

7. Handling and Storage

Follow instructions of grinding machine manufacturers and the relevant national regulations. In addition, observe the safety recommendations of the manufacturer.

8. Exposure Controls / Personal Protection

Before grinding it is recommended to perform a risk assessment and to use personal protection equipment accordingly.

8.1. Occupational exposure limit values and/or biological limit values

Keep exposure to the following components under surveillance

(Observe also the regional official regulations)

| Name | CAS Nr. | Specification | Concentration limits (daily average value) | Short term value | remarks |
|------|---------|---------------|---|---------------------|---------|
| | | | | | |
| | | | | | |
| | | | | | |
| | | | | | |
| | | | | | |

Note: Hazardous dust of the workpiece material may be generated during grinding and/or sanding operations. National regulations for dust exposure limit values have to be taken into consideration.

8.2. Exposure controls

8.2.1. Occupational exposure controls

8.2.1.1. Respiratory protection: Use respiratory protective equipment
(type depends on specific application and material being ground)

8.2.1.2. Hand protection: Wear protective gloves
(type depends on specific application and material being ground)

8.2.1.3. Eye protection: Wear protective goggles or face shield
(type depends on specific application and material being ground)

8.2.1.4. Hearing protection: Use hearing protection
(type depends on specific application and material being ground)

8.2.1.5. Body protection: Use protective clothing
(type depends on specific application and material being ground)

9. Physical and Chemical Properties



FEDERATION EUROPEENNE DES
FABRICANTS DE PRODUITS ABRASIFS



Confidential

EC-Technical Data Sheet

Reference: **69936625778**

41_150x1.6X12.7_5D10A601RB25

Version/date: 07/03/13

page 3 of 4

- | | | |
|-----|----------------------|-------|
| 9.1 | Physical state: | solid |
| 9.2 | Colour: | |
| 9.3 | Solubility in water: | |

10. Stability and Reactivity

Stability

Bonded Abrasives are stable when handled or stored correctly.

Reactivity

- 10.1 Conditions to avoid:
No decomposition in normal use.
- 10.2 Materials to avoid:
No dangerous reactions known.
- 10.3 Hazardous decomposition products:
At temperatures exceeding 250° C hazardous or toxic decomposition products may be generated.

11. Toxicological Information

No toxicological effects if inhaled or swallowed or with eye or skin contact are known.
See also section 8.

12. Ecological Information

- | | | |
|------|--------------------------------|-----------------------------------|
| 12.1 | Ecotoxicity: | no effects known |
| 12.2 | Mobility: | no potentials known |
| 12.3 | Persistence and degradability: | no biodegradable potentials known |
| 12.4 | Bioaccumulative potential: | no potentials known |
| 12.5 | Other hazardous effects: | no effects known |

13. Disposal Considerations

13.1. Product

Follow national and regional regulations!

Due to the ingredients and properties disposal as non hazardous waste (2000/532/EC) is possible if no hazardous materials are added to the abrasives. (EWC – Nr. 120121),

Due to the ingredients and properties disposal as hazardous waste (2000/532/EC) (EWC – Nr. 120120)

13.2. Packing

Follow national and regional regulations!

14. Transport Information



FEDERATION EUROPEENNE DES
FABRICANTS DE PRODUITS ABRASIFS



Confidential

EC-Technical Data Sheet

Reference: **69936625778**

41_150x1.6X12.7_5D10A601RB25

Version/date: 07/03/13

page 4 of 4

The product is not covered by international regulation on the transport of dangerous goods.

15. Regulatory Information

No specific labelling requirements under respective EC directives

16. Other Information

The above information is based on our current standard of knowledge and does not constitute any warranty of conditions of the product. The information does not form part of any contractual agreement. It remains the user's responsibility to adhere existing laws and regulations.

Issued by: R&D

Contact: Marco Tana