

# Panasonic SD Memory Offers the High Reliability Demanded for Industrial/automotive Use

## High Reliability and Panasonic Controller Technology

### Data Programming and Erase Endurance

#### Wear Levelling

● Maximising SD Memory Life  
Static wear levelling controls written data, including fixed data. Various use cases eliminate intensive data writing and maximise the lifetime of the SD card.



### Secure Storage

#### Bit Error Auto Refresh

● Withstanding Repeated Reading Operations  
Automatically refreshes the bit errors that accumulate over time, before they exceed the threshold. (Accumulated bit errors are detected from read data.)  
\* This function does not guarantee permanent data retention.



### Power Failure Robustness

#### Recovery

● Protects saved data and device  
Unique Panasonic algorithms minimise data damage in the event of a power interruption. Even in the event that an error is generated, the controller recovers the data, restoring it to the condition prior to the error, and preventing errors from reaching the entire SD memory area.  
\* Power Fail Robustness Mode firmware also available for more robust MLC system

### Intelligent Data Writing

● Dispersion of Writing Stress to NAND Flash Memory  
Intelligent data writing disperses the writing stress to NAND flash memory, to reduce program disturbances.

## Durable Performance

Panasonic SD memory features high endurance against static electricity, magnetism, and X-rays.

#### Temperature Resistance

Operation is assured even under harsh temperature conditions.  
A usable temperature range of -40 °C to 85 °C maintains stable performance everywhere, from extremely cold to intensely hot climates.

#### Electrostatic Resistance

ICE 61000-4-2 compliance: Clears Electrostatic Discharge Immunity Tests of 150-pF energy storage capacitance, 15-kV aerial discharge, and 330-Ω discharge resistance.

#### Impact Resistance

High endurance against bending and twisting.

Bending load resistance	20 N (Newton) min. (SD standard: 10 N)
Twisting torque resistance	0.3 N·m (Newton meter) min. (SD standard: 0.15 N·m)

#### Magnetic Resistance

Minimal damage from magnetic forces.  
Operable after being set onto a 1,000-gauss DC magnetic field for approx. 1 minute.

#### X-Ray Resistance

Data is protected from X-rays.  
ISO 7816-1 compliance: Operable after 0.1 Gy (gray) of X-ray irradiation.

#### Water Resistance

JIS IPX7 compliance: Operable after submerging the product in water (tap water, 1-m depth) for 30 minutes.  
\* micro SD – Excluding SD adaptor use.  
\* Card only.

#### Built-in Fuse


The internal card fuse protects against excess current and abnormal heating. Even if excess current or abnormal heating were to occur due to internal card damage caused by the device being used or the environment, the built-in fuse will operate to prevent the SD Memory Card from overheating or igniting.

## Applications by Model

	Data Protection*				Card Endurance							
	Wear Levelling	Intelligent Data Writing	Refresh	Recovery	Temperature Resistance	Electrostatic Resistance	Impact Resistance	Magnetic Resistance	X-Ray Resistance	Water Resistance	Fuse	
FX Series	●	●	●	●	-40 °C to +85 °C	●	●	●	●	—	●	
P Series	●	●	●	●		●	●	●	●	●	—	●
microSD/ KC Series	●	●	●	●		●	●	●	●	●	●	●
microSD/JC Series	●	●	●	●		●	●	●	●	●	●	●
eSD (Flexible connection type)	●	●	●	●		●	●	●	●	●	—	—
eSD (Semiconductor mounting type)	●	●	●	●		●	●	●	●	●	—	—

\* Based on Panasonic test results. Protection may not be possible in certain usage environments. The data stored inside a card cannot be guaranteed.

## SD Memory Card Roadmap



## What is UHS-I?

UHS-I (Ultra High Speed I) is a speed specification for SD Memory Cards that was established in 2010. Its features include a maximum bus interface speed of up to 104 MB/s. It utilizes conventional SD design assets and offers enhanced speeds. Three different modes (DDR50, SDR50 and SDR104) have been standardized for the UHS-I based on the application and objective.

## Speed Specification and Performance of SD Memory Cards

(Years indicate the year that the standard was established.)



Bus Interface Standard	Conventional	UHS-I		
		DDR50	SDR50	SDR104
Mode	HS	1.8 V Amplitude		
Signal Amplitude	3.3 V Amplitude			
Clock Frequency	50 MHz	50 MHz	100 MHz	208 MHz
Data Frequency	50 MHz	100 MHz	100 MHz	208 MHz
Logic Performance (Bus Speed)	25 MB/s	50 MB/s	50 MB/s	104 MB/s

## Product Precautions

- SDHC memory cards can be used with SDHC and SDXC host products. SDHC memory cards cannot be used with products that are solely compliant with SD memory cards.
- SDXC memory cards can be used only with SDXC host products. SDXC memory cards cannot be used with SD and SDHC host products. Check if the device has an SDXC logo, or refer to the device's instruction manual or other manufacturer's information
- Please note that using an SDXC Memory Card in a non-compatible computer or device may cause card compatibility problems or loss of data.
- The SD Memory Card is intended for ordinary use in for home or professional devices and embedded systems. Consult with Panasonic in advance about uses for applications that require a high degree of reliability (uses that may have a serious impact on human lives, such as in nuclear power or social infrastructure applications.)

## For more information

[http://panasonic.net/avc/sdcard/industrial\\_sd/](http://panasonic.net/avc/sdcard/industrial_sd/)

Media Business Unit, Business Solutions Group, AVC Network System Company, Panasonic Corporation

1-15, Matsuo-cho, Kadoma, Osaka, 571-8504, Japan

- The product colours shown in this printed material may vary from the actual colours.
- Specifications and designs are subject to change without notice.
- SDXC, SDHC, SD, and microSDHC Logos are trademarks of SD-3D, LLC.
- As of January 1st, 2013.

# Panasonic ideas for life

## Industrial/Automotive SD Memory



- Extended Temperature
- Power Failure Robustness
- Program/Erase Endurance

- Specifications for industrial/automotive applications demanding high reliability.
- Various customization to meet customer requirements.
- B-to-B specialised support provided.




# SD Memory

# Industrial/Automotive Use SD Memory Line-up

## SLC and MLC

The NAND flash memory that is used in SD Memory Cards has Single Level Cells (SLC), which each store 1 bit of data, and Multi Level Cells (MLC), which each store 2 bits. The FX Series use SLCs to provide superior data retention and reliability.



## SLC FX Series

\* 128MB/512MB SLC line-up also available



### Performance Specifications

Model	RP-SDF02G	RP-SDF04G	RP-SDF08G	RP-SDF16G
Capacity*1	2 GB	4 GB	8 GB	16 GB
Flash Memory Type	Single-Level Cell (SLC) NAND Flash Memory			
SD Physical Specification	Ver.3.01 (No UHS-I Compliant)	Ver. 3.01 (UHS-I Compliant)		
Speed Class	SD Speed Class 6	SD Speed Class10, UHS Speed Class 1		
Transfer Rate (Max)*2	Read	22 MB/s	90 MB/s	95 MB/s
	Write	20 MB/s	40 MB/s	80 MB/s
Operating Temperature	-40 to +85 °C by Panasonic			
Controller	Functions	Static Wear Levelling, Intelligent Data Writing, Recovery Function from Power Failure, Refresh Function		
		by Panasonic		
Size	32.0 x 24.0 mm			

\* Release date under consideration \*1: SD Memory utilise a portion of the memory for copy protection and other purposes. Therefore Usable capacity will be less. \*2: Speed performance is subject to change.

## MLC KC Series



### Performance Specifications

Model	RP-SMKC04	RP-SMKC08	RP-SMKC16
Capacity*1	4 GB	8 GB	16 GB
Flash Memory Type	Multi-Level Cell (MLC) NAND Flash Memory		
SD Physical Specification	Ver. 3.01 (UHS-I Compliant)		
Speed Class	SD Speed Class 10, UHS Speed Class 1		
Transfer Rate (Max)*2	Read	45 MB/s	
	Write	12 MB/s	
Operating Temperature	-40 to +85 °C by Panasonic		
Controller	Functions	Static Wear Levelling, Intelligent Data Writing, Recovery Function from Power Failure, Refresh Function	
		by Panasonic	
Size	15.0 x 11.0 mm (Max)		

\*1: SD Memory utilise a portion of the memory for copy protection and other purposes. Therefore Usable capacity will be less. \*2: Speed performance is subject to change.

## MLC P Series



### Performance Specifications

Model	RP-SDP04G	RP-SDP08G	RP-SDP16G
Capacity*1	4 GB	8 GB	16 GB
Flash Memory Type	Multi-Level Cell (MLC) NAND Flash Memory		
SD Physical Specification	Ver.3.01 (No UHS-I Compliant)		
Speed Class	SD Speed Class 4		
Transfer Rate (Max)*2	Read	22 MB/s	
	Write	-	
Operating Temperature	-40 to +85 °C by Panasonic		
Controller	Functions	Static Wear Levelling, Intelligent Data Writing, Recovery Function from Power Failure, Refresh Function	
		by Panasonic	
Size	32.0 x 24.0 mm		

\* Release date under consideration \*1: SD Memory utilise a portion of the memory for copy protection and other purposes. Therefore Usable capacity will be less. \*2: Speed performance is subject to change.

## MLC eSD (Flexible Connection Type)

Products converted to SLC are also available on demand. Form factor of module can be customized.



### Performance Specifications

Model	RP-SD04GP	RP-SD08GP	RP-SD16GP
Capacity*1	4 GB	8 GB	16 GB
Flash Memory Type	Multi-Level Cell (MLC) NAND Flash Memory		
SD Physical Specification	Ver. 3.01 (No UHS-I Compliant)		
Speed Class	SD Speed Class 4		
Transfer Rate (Max)*2	Read	22 MB/s	
	Write	-	
Operating Temperature	-40 to +85 °C by Panasonic		
Controller	Functions	Static Wear Levelling, Intelligent Data Writing, Recovery Function from Power Failure, Refresh Function	
		by Panasonic	
Size	30.0 x 24.0 mm		

\*1: SD Memory utilise a portion of the memory for copy protection and other purposes. Therefore Usable capacity will be less. \*2: Speed performance is subject to change.

## MLC eSD (Semiconductor Mounting Type)



### Performance Specifications

Model	RP-SVBC04	RP-SVBC08	RP-SVBC16
Capacity*1	4 GB	8 GB	16 GB
Flash Memory Type	Multi-Level Cell (MLC) NAND Flash Memory		
SD Physical Specification	Ver. 3.01 (UHS-I Compliant)		
Speed Class	SD Speed Class 10, UHS Speed Class 1		
Transfer Rate (Max)*2	Read	90 MB/s	
	Write	12 MB/s	
Operating Temperature	-40 to +85 °C by Panasonic		
Controller	Functions	Static Wear Levelling, Intelligent Data Writing, Recovery Function from Power Failure, Refresh Function	
		by Panasonic	
Size	18.0 x 12.2 mm		

\*1: SD Memory utilise a portion of the memory for copy protection and other purposes. Therefore Usable capacity will be less. \*2: Speed performance is subject to change.

### Environmental Specifications (Common to all models)

Temperature (Operating)	-40 to +85 °C		Vibration	15 Gp-p
	(Non-operating)			Shock
Humidity	5 to 95 % (No condensation)		RoHS Directive Compatibility	

Applicable EMC Standards  
 1) VCCI Class B (Option B)  
 2) FCC Part 15 Class B (Verification)  
 3) EC Directive 89/336/EEC EN55022: 2006 Class B EN55024: 1998 +A1: 2001 +A2: 2003  
 4) AS/NZS CISPR Pub22: 2006

• Panasonic industrial/automotive use SD memory has a unique Panasonic function that reports data such as bad blocks, writing cycles, and the SD memory internal connection status.  
 • A special B to B support system also allows Panasonic to offer consultation concerning customisation upon customer request.

For details, consult a salesperson.

