










Han-Modular® RJ45 Module



Identification	Part-Number		Drawings	Dimensions in mm
	Male insert (M)	Female insert (F)		
<p>Han® RJ45 module</p> <p>gender changer for patch cable</p> 		09 14 001 4721		<p>Contact arrangement view from termination side</p> 
<p>for patch cable</p> 	09 14 001 4621			
<p>with RJ45 terminal</p> 	09 14 001 4622			

Features

- Single module with standard shielded RJ45 plug and jack
- Cat 5e for all data pairs (all 8 pins)
- Conforming to the RoHS directive
- The RJ45 inserts are protected by a reliable plastic insulator

Technical characteristics

Specifications

DIN EN 61 984
DIN VDE 0110

Inserts

Number of contacts	8
Electrical data accd. to DIN EN 61 984	1 A 50 V 0.8 kV 3
Rated current	1 A
Rated voltage	50 V
Rated impulse voltage	0.8 kV
Pollution degree	3
Insulation resistance	$\geq 10^{10} \Omega$
Material	Polycarbonate
Limiting temperatures	-40 °C ... +85 °C
Flammability accd. to UL 94	V 0
Mechanical working life	≥ 500 mating cycles