



Quick Reference

Search by part #

Products

Browse Products

-By Device-

-By Product Line-

-Attachment Methods-

-Interface Materials-

-Accessories-

- Useful Links**
- [MSDS Safety Sheets](#)
 - [How to Order?](#)
 - [Find Sales Rep](#)
 - [Find Distributor](#)
 - [Sample Request](#)
 - [Quote Request](#)
 - [Catalog Request](#)
 - [Building a Part #](#)
 - [Part # Cross Ref](#)

Products | The Max Clip System™ | Search Results

Max Clip System™

Max Clips



<p>Part Number: MAX01G Low force clip</p> <p>RoHS Compliant Product Change Notice </p> <p>Force: 22 N [4.9 lbs]</p> <p>Width: 10 mm [0.39 in]</p> <p>Thickness: 0.5 mm [0.02 in]</p>	<p>T0220/Max220</p> <p>14.7 [0.58]</p>
<p>Part Number: MAX01-HG High force clip</p> <p>RoHS Compliant Product Change Notice </p> <p>Force: 80 N [18.0 lbs]</p> <p>Width: 10 mm [0.39 in]</p> <p>Thickness: 0.7 mm [0.03 in]</p>	<p>T0220/Max220</p> <p>14.7 [0.58]</p>
<p>Part Number: MAX02G Standard force clip</p> <p>RoHS Compliant Product Change Notice </p> <p>Force: 35 N [7.9 lbs]</p> <p>Width: 12 mm [0.47 in]</p> <p>Thickness: 0.5 mm [0.02 in]</p>	<p>T0220/Max220</p> <p>14.7 [0.58]</p>
<p>Part Number: MAX02-HG High force clip</p> <p>RoHS Compliant Product Change Notice </p> <p>Force: 60 N [13.5 lbs]</p> <p>Width: 13 mm [0.51 in]</p> <p>Thickness: 0.6 mm [0.02 in]</p>	<p>T0220/Max220</p> <p>14.7 [0.58]</p>
<p>Part Number: MAX03G Standard force clip</p> <p>RoHS Compliant Product Change Notice </p> <p>Force: 45 N [10.1 lbs]</p> <p>Width: 15 mm [0.59 in]</p> <p>Thickness: 0.5 mm [0.02 in]</p>	<p>T0247/Max247 T0247J</p> <p>14.7 [0.58]</p>
<p>Part Number: MAX03-HG High force clip</p> <p>RoHS Compliant Product Change Notice </p> <p>Force: 80 N [18.0 lbs]</p> <p>Width: 18 mm [0.71 in]</p> <p>Thickness: 0.6 mm [0.02 in]</p>	<p>T0247/Max247 T0247J</p> <p>14.7 [0.58]</p>
<p>Part Number: MAX04G Standard force clip</p> <p>RoHS Compliant Product Change Notice </p> <p>Force: 60 N [13.5 lbs]</p> <p>Width: 20 mm [0.79 in]</p> <p>Thickness: 0.5 mm [0.02 in]</p>	<p>T0247/Max247 T0247J</p> <p>14.7 [0.58]</p>
<p>Part Number: MAX09G Short standard force clip</p> <p>RoHS Compliant </p> <p>Force: 45 N [10.1 lbs]</p> <p>Width: 10 mm [0.39 in]</p> <p>Thickness: 0.5 mm [0.02 in]</p>	<p>T0220</p> <p>10.1 [0.40]</p>
<p>Part Number: MAX10G Long standard force clip</p> <p>RoHS Compliant Product Change Notice </p> <p>Force: 40 N [9.0 lbs]</p> <p>Width: 12 mm [0.47 in]</p> <p>Thickness: 0.6 mm [0.02 in]</p>	<p>T0220/Max220 Thin components</p> <p>19.7 [0.78]</p>
<p>Part Number: MAX12G Low force clip</p> <p>RoHS Compliant Product Change Notice </p> <p>Force: 25 N [5.6 lbs]</p> <p>Width: 6 mm [0.24 in]</p> <p>Thickness: 0.6 mm [0.02 in]</p>	<p>T092 Sensors</p> <p>19.7 [0.78]</p>
<p>Part Number: MAX11G Extra long standard force clip</p> <p>RoHS Compliant Product Change Notice </p> <p>Force: 40 N [9.0 lbs]</p> <p>Width: 12 mm [0.47 in]</p> <p>Thickness: 0.6 mm [0.02 in]</p>	<p>T0220/Max220 Thin components</p> <p>24.7 [0.97]</p>
<p>Part Number: MAX23G High force clip for use with thick insulator</p> <p>RoHS Compliant </p> <p>Force: 100 N [22.5 lbs]</p> <p>Width: 18 mm [0.71 in]</p> <p>Thickness: 0.6 mm [0.02 in]</p>	<p>T0247/Max247 T0247J</p> <p>4.0 [0.16]</p> <p>15.4 [0.61]</p> <p>INSULATOR</p>
<p>Part Number: MAX20G Standard force clip for use with thick insulator</p> <p>RoHS Compliant </p> <p>Force: 47 N [10.6 lbs]</p> <p>Width: 12 mm [0.47 in]</p> <p>Thickness: 0.6 mm [0.02 in]</p>	<p>T0220/Max220</p> <p>4.0 [0.16]</p> <p>20.0 [0.79]</p> <p>INSULATOR</p>
<p>Part Number: MAX13G Standard force clip with locating features</p> <p>RoHS Compliant </p> <p>Force: 45 N [10.1 lbs]</p> <p>Width: 17 mm [0.67 in]</p> <p>Thickness: 0.5 mm [0.02 in]</p>	<p>T0247</p> <p>10.5 [0.41]</p>
<p>Part Number: MAX14G Low force clip with locating features</p> <p>RoHS Compliant </p> <p>Force: 20 N [4.5 lbs]</p> <p>Width: 13 mm [0.51 in]</p> <p>Thickness: 0.5 mm [0.02 in]</p>	<p>T0220</p> <p>14.5 [0.57]</p>
<p>Part Number: MAX15G Standard force clip with locating features</p> <p>RoHS Compliant </p> <p>Force: 60 N [13.5 lbs]</p> <p>Width: 18 mm [0.71 in]</p> <p>Thickness: 0.6 mm [0.02 in]</p>	<p>D61</p> <p>13.3 [0.52]</p>
<p>Part Number: MAX16G Standard force clip with locating features</p> <p>RoHS Compliant </p> <p>Force: 45 N [10.1 lbs]</p> <p>Width: 17 mm [0.67 in]</p> <p>Thickness: 0.5 mm [0.02 in]</p>	<p>T0247</p> <p>10.5 [0.41]</p>