

AC TO AC ADAPTOR

Ideal Power Ltd.

77DB-06-12M

INPUT VOLTAGE **240VAC**
OUTPUT VOLTAGE **12VAC**



ELECTRICAL & MECHANICAL SPECIFICATION





KM81689



18718



OUTPUT CORD:
2468 22AWG*2C 80°C



ELECTRONICAL SPECIFICATION

Input Voltage	240	Volts
Frequency (Hz)	50	Hz
Power Rated (W)	10	W
Exciting Current With No load	50	mA Max
Exciting Current With Full load	70	mA Max
Output Voltage	12.0	Volts±5%
Output Current	0.5	Amp
Output Voltage Without Load	16.0	Volts±5%

HI-POT :

Test Time	1	Min
PRI TO SEC	3750	Volts
PRI TO CORE	3750	Volts
SEC TO CORE	1250	Volts
Efficiency	80	%
Insulation Class	B (130)	°C


MECHANICAL SPECIFICATION

Dimensions (L*W*H)	64.0*52.0*40.0	mm
Weight	265	g
Environment:		
Operating Temperature	-10 To 40	°C
Storage Temperature	-20 To 70	°C
Relative Temperature	40°C±2°C	
RELATIVE HUMIDITY	90% RH	

Input Cable: **BS PLUG IN(3PIN)**

Output Cable: **2468 22AWG*2C 1.8M LENGTH+JACK**

ELECTRICAL CIRCUIT



Head Office : Acorn House, Tree Beech Enterprise Park, Gunn, Barnstaple, Devon, England EX32 7NZ

TEL: +44 (0) 845 260 3400

FAX: +44 (0) 845 260 3400

E-Mail: info@idealpower.co.uk

WEB: www.idealpower.co.uk