

WORKGATE™ BARRIER

NEW ROBUST MINI BARRIER SUPPLIED AS 3 OR 4 GATE VERSIONS THAT EASILY FOLD FOR QUICK DEPLOYMENT

TECHNICAL
SPECIFICATION

TRAFFIC MANAGEMENT

INSTRUCTIONS FOR USE

Distribute Barrier as per requirements and the requirements of:
"The Traffic Signs Regulations and General Directions 2002"
"Safety at Street Works and Road Works"
Both are published by TSO®

DIMENSIONS OF MINI BARRIER

Each individual barrier section:
Weight: 2.85kg
Length of single barrier: 84cm
Height: 100cm

WORKGATE™ BARRIER FEATURES & BENEFITS

- Reflective Panel:** Fully reflective panel meeting EN12899-1 requirements
- Flexible Linking:** Black adjoining clips give flexible multi positioning configurations
- Handles:** Convenient handles with moulded finger grips make the Workgate™ especially easy to manoeuvre
- Contractor Branding:** Large area to allow contractor details to be applied in decal form
- Feet:** Optional anti trip feet create a more stable Workgate™ for linear usage
- Options:** The Workgate™ can be linked in a square, a triangle or in a single line making it practical for most uses and environments
- Recyclable:** Contains no metal parts, making it ideal for working in electrical environments and easy to recycle
- Temporary Signage:** Locating holes enable courtesy or pedestrian signs to be fitted

BARRIER FRAME:
Polypropylene

LINK:
Polypropylene



WORKGATE

CLEANING & MAINTENANCE

Clean with a warm soapy cloth and allow to air dry
Keep clean and in a suitable environment

WORKGATE™ BARRIER CONFORMITY

Workgate™ Barrier conforms to BS8442-2006 Miscellaneous Road Traffic Signs and Devices
Robust mini barrier supplied with a class R1 EN12899-1 reflective tape for higher visibility in poor light conditions

TESTING

Barrier was pre-conditioned to -16°C, then dropped from a height of 2m onto concrete



MANUFACTURING FOR SAFETY
WWW.JSP.CO.UK



UKSALES@JSP.CO.UK
TEL: +44 (0)1993 826050



Issued 18/12/12, V1