

STEALTH 8000™

CLEAR FRAME - CLEAR ANTI-MIST HC LENS

TECHNICAL
SPECIFICATION

PRODUCT CODE: ASA790-151-300

LOW PROFILE TENSION CONTROL TEMPLES PROVIDE EXTRA GRIP & ARE SUITABLE FOR USE WITH HEARING PROTECTION

EYE & FACE PROTECTION

INSTRUCTIONS FOR USE

In use ensure that the safety spectacles fit comfortably and securely on the head

Ensure that the safety spectacles are in place, before entering the hazard area

STEALTH 8000

TEMPLE INSERT PAD:
PVC

TEMPLE:
Polycarbonate

NOSE PAD:
PVC

LENS:
Polycarbonate

STEALTH 8000™ FEATURES & PERFORMANCE

Lens and frame offer protection against low energy high-speed particles at 45 m/s (101mph)

The optical qualities of the lens comply with the requirements of optical class 1 (highest)

Full eye protection

Soft grip inserts in temples to avoid slipping

Browguard integral to frame

Single lens design with wraparound protection

Maximum field of vision

Soft nose pad releases the pressure from the nose

Stylish torsion control temple design offers snug fitting

Lens filters 99.9% of harmful UV light

UVA, UVB and UVC protection

The temple tips have a spectacle cord anchor point for further practicality

K class anti scratch lens

Anti-fog lens

CLEANING & MAINTENANCE

The safety spectacles may be cleaned with soap and warm water and dried with a soft cloth

Do not clean with chemical or abrasive cleaners

The eye shield should be stored out of direct sunlight, away from chemicals and not exposed to extremes of temperature

CONFORMITY

Conforms to EN 166.1.F.T.K & EN 170

EC Certificate Number CEPPE20069, issued by SAI Global Assurance Services Limited

STEALTH 8000™

CLEAR FRAME - CLEAR ANTI-MIST HC LENS

TECHNICAL
SPECIFICATION

PRODUCT CODE: ASA790-151-300


LOW PROFILE TENSION CONTROL TEMPLES PROVIDE EXTRA GRIP & ARE SUITABLE FOR USE WITH HEARING PROTECTION

EYE & FACE PROTECTION

DIMENSIONS OF INNER PACKAGING

Quantity: 10

Weight: 265g (Approx.)



WIDTH:
172mm

LENGTH:
290mm

HEIGHT:
85mm




STEALTH 8000

DIMENSIONS OF OUTER PACKAGING

Quantity: 120

Weight: 3.8kg (Approx.)



WIDTH:
315mm

LENGTH:
545mm

HEIGHT:
377mm

DIMENSIONS OF SPECTACLE

Lens Thickness: 2.2mm

Lens Base: 9mm curve

Lens Size (Vertical): 43mm

Lens Size (Diagonal): 85mm

Bridge: 15mm

Temple Length (Lens to tip): 152mm

Overall Width: 145mm

Closest point between temple tips: 95mm

Weight: 26g (Approx.)

LIMITATIONS OF USE

Protection will only be offered if the safety spectacles are fitted correctly

If the safety spectacles become scratched or damaged they should be replaced, likewise if the safety spectacles are subjected to severe impact they should be replaced immediately

Do not apply paint, solvents, adhesives or self-adhesive labels, except in accordance with instructions from the manufacturer

The safety spectacles, when in contact with the skin may cause allergic reactions to susceptible individuals. If this occurs leave the hazard area, remove the eye shield and seek medical advice

The attention of users is also drawn to the dangers of modifying or removing any of the original component parts, other than as recommended by the manufacturer

The Stealth 8000™ is not suitable for protection against dusts, liquids or molten metals

MARKINGS

Frame: EN166 1.F.T

Amber/Clear Lens: 2-1.2 ↑ 1.F.T.K

Indoor/Outdoor Lens: 5-1.7 ↑ 1.F.T

Smoke Lens: 5-2.5 ↑ 1.F.T.K