SERIES Ver.2

FIBER SENSORS Related Information

■ General terms and conditions...... F-17 ■ Glossary of terms......P.1359~ ■ Sensor selection guide...... P.283~ ■ General precautions P.1405

Ver.2

MICRO PHOTOELECTRIC

SENSORS AREA SENSORS

LASER SENSORS

LIGHT CURTAINS

PRESSURE / **FLOW** SENSORS INDUCTIVE PROXIMITY **SENSORS**

PARTICUI AR USE SENSORS

SENSOR OPTIONS

SIMPLE WIRE-SAVING UNITS

WIRE-SAVING SYSTEMS

MEASUREMENT SENSORS

STATIC CONTROL DEVICES

ENDOSCOPE

LASER

PLC / TERMINALS

HUMAN MACHINE INTERFACES

ENERGY CONSUMPTION VISUALIZATION COMPONENTS

FA COMPONENTS

MACHINE VISION SYSTEMS

UV CURING SYSTEMS

panasonic-electric-works.net/sunx







The next-generation new form series A new alternative to fiber sensors

Simpler design

All you need to do is to make a ø4 mm Ø0.157 in hole where you would like to stop or check the object (ø6 mm Ø0.236 in hole for reflective type). Furthermore, the center of the sensing axis is the same as the center of the mounting hole, which makes it much easier to set the sensing position.



New design solves all weak points of fiber sensors


The EX-30 series solves all of the difficulties associated with fiber sensors, such as:

- · Difficulty finding a suitable place for the amplifier
- · Fragility of the fiber
- · Extra space needed because of difficulty in bending the fiber
- The nuisance of having to use a protective tube to prevent fiber breakage

BASIC PERFORMANCE

Electric power saving

The EX-30 series achieves reductions in power consumption of up to 65 %. These sensors contribute to environmental friendliness.



Long sensing range

The EX-30 series achieves long distance sensing [thru-beam type: 500 mm 19.685 in (EX-33(-PN): 800 mm 31.496 in), reflective type: 50 mm 1.969 in.]



High response speed of 0.5 ms

The same high response speed of 0.5 ms as fiber sensor amplifiers is provided, making these sensors ideal for sensing small objects, counting objects that are moving quickly and positioning items such as circuit boards.

Globally usable

It conforms to the EMC Directive and obtains the UL Recognition. (excluding 5 m 16.405 ft cable length type) Moreover, PNP output type which is much in demand in Europe, is also available.

Amplifier Built-in Power Supply Built-in Amplifier-separated

CX-400 **EX-10**

EX-20 EX-30 EX-40

CX-440 EQ-30


EQ-500 MQ-W

RX-LS200


RXRT-610

APPLICATIONS

Detecting IC height







VARIETIES

New thru-beam types now feature operation mode switch and sensitivity adjuster! EX-33(-PN)



1 Operation mode switch 2 Sensitivity adjuster

Bright 2-color indicator

Switching between light-ON and dark-ON operating modes is possible with a single model.

It is convenient when you need fine adjustment.

A bright 2-color indicator has been incorporated in all types.



Receiver





Receiver

MOUNTING / SIZE


Can be installed in the same way as standard fibers

The EX-30 series can be screwmounted (M4 for thrubeam type, M6 for reflective type) in the same way as standard fiber sensors. This means that they can be inserted into production lines in exactly the same way as conventional high-priced fiber sensors.




Single-point tightening cuts down on installation work by half

Conventional photoelectric sensors required four (for thru-beam type) or two (for reflective type) mounting holes and screws to be used. However, the EX-30 series is installed with a single screw, thus cutting down on installation work by half.



Takes up very little space

Unlike conventional fibers, bending radius is not a problem, so that the sensor can be securely installed alongside conveyors.



FIBER SENSORS

LASER SENSORS

MICRO PHOTOELECTRIC SENSORS

AREA SENSORS

LIGHT CURTAINS

PRESSURE FLOW SENSORS INDUCTIVE PROXIMITY **SENSORS**

PARTICUI AR USE SENSORS

SENSOR OPTIONS

SIMPLE WIRE-SAVING UNITS

WIRE-SAVING SYSTEMS

MEASUREMENT SENSORS

STATIC CONTROL DEVICES

ENDOSCOPE

LASER MARKERS

PLC / TERMINALS

HUMAN MACHINE INTERFACES

ENERGY CONSUMPTION VISUALIZATION COMPONENTS

FA COMPONENTS

MACHINE VISION SYSTEMS

UV CURING SYSTEMS

Selection Guide

Power Supply Built-in

CX-400

EX-10

EX-20

EX-30 EX-40

CX-440

EQ-30

EQ-500 MQ-W

RX-LS200

RX

RT-610

FIBER SENSORS

LASER

MICRO PHOTOELECTRIC SENSORS

AREA SENSORS

LIGHT CURTAINS

PRESSURE / **FLOW** SENSORS INDUCTIVE PROXIMITY **SENSORS**

PARTICUI AR USE SENSORS

SENSOR OPTIONS

SIMPLE WIRE-SAVING UNITS

WIRE-SAVING SYSTEMS

MEASUREMENT SENSORS

STATIC CONTROL DEVICES

ENDOSCOPE

LASER MARKERS

PLC / TERMINALS

HUMAN MACHINE INTERFACES

ENERGY CONSUMPTION VISUALIZATION COMPONENTS

FA COMPONENTS

MACHINE VISION SYSTEMS

UV CURING SYSTEMS

Power Supply Built-in Amplifier-separated

> CX-400 EX-10

> > EX-20 EX-30

EX-40

CX-440

EQ-30 EQ-500 MQ-W

RX-LS200

RX

RT-610

ENVIRONMENTAL RESISTANCE

Incorporated an inverter countermeasure circuit

The EX-30 series become significantly stronger against inverter light and other extraneous light.

*Effective from production in April 2011.







FUNCTIONS

Bright 2-color indicator

A bright 2-color indicator is incorporated in all types.



No protective tube needed

The EX-30 series has high bending strength, so that the protective tube used to protect conventional fiber from breakage is not needed. This also adds up to excellent cost performance.



OPERABILITY

Incorporates a sensitivity adjuster (Excluding EX-31□)

The sensor incorporates a sensitivity adjuster. It is convenient when you need fine adjustment.




Sensitivity adjuster

Waterproof IP67 (IEC)

The sensor can be hosed down because of its IP67 construction.

Note: However, take care that if it is exposed to water splashes during operation, it may detect a water drop itself.



ORDER GUIDE

Туре	Appearance	Sensing range	Model No. (Note)	Output	Output operation
Thru-beam		500 mm 19.685 in	EX-31A	NPN open-collector	Light-ON
			EX-31B	transistor	Dark-ON
			EX-31A-PN	PNP open-collector	Light-ON
			EX-31B-PN	transistor	Dark-ON
operation e switch		800 mm 31.496 in	EX-33	NPN open-collector transistor	Switchable either Light-ON or Dark-ON
With op mode s			EX-33-PN	PNP open-collector transistor	
Diffuse reflective			EX-32A	NPN open-collector	Light-ON
		50 mm 1.969 in	EX-32B	transistor	Dark-ON
			EX-32A-PN	PNP open-collector	Light-ON
			EX-32B-PN	transistor	Dark-ON

Note: The model No. with "P" shown on the label affixed to the thru-beam type sensor is the emitter, "D" shown on the label is the receiver. (e.g.) Emitter of EX-31A: EX-31P, Receiver of EX-31A: EX-31AD

5 m 16.404 ft cable length type

5 m 16.404 ft cable length type(standard: 2 m 6.562 ft) is also available for NPN output type [excluding EX-33(-PN)]. When ordering this type, suffix "-C5" to the model No

(e.g.) 5 m 16.404 ft cable length type of **EX-31A** is "**EX-31A-C5**".

OPTIONS

Designation	Model No.	Description
Slit mask /For thru-beam	OS-EX30-1 (Slit size ø1 mm) ø0.039 in	• Sensing range: 200 mm 7.874 in [EX-31□(-PN)] Slit on one side 320 mm 12.598 in [EX-33(-PN)] • Min. sensing object: Ø2 mm Ø0.079 in
		• Sensing range: 150 mm 5.906 in [EX-31□(-PN)] Slit on both sides 240 mm 9.449 in [EX-33(-PN)] • Min. sensing object: ø1 mm ø0.039 in

Note: One slit and two spacers are provided per set. Two sets are required when installing on both sides.

Slit mask

• OS-EX30-1



Apply the optional slit mask when detecting small objects or for increasing the accuracy of sensing position.

However, the sensing range is reduced when the slit mask is mounted.

SPECIFICATIONS

Туре		Thru-beam With operation mode switch			Diffuse reflective				
	Model No.	NPN output	EX-31A	EX-31B	EX-33	EX-32A	EX-32B		
Item	ı \ ğ	PNP output	EX-31A-PN	EX-31B-PN	EX-33-PN	EX-32A-PN	EX-32B-PN		
Sensing range		500 mm	19.685 in	800 mm 31.496 in	50 mm 1.969 in (Note 2)				
Sensing object		ø2 mm ø0.079 in or more	opaque object (Completely	beam interrupted objects)	Opaque, translucent or transparent object (Note 3)				
Hysteresis					15 % or less of operation distance (Note 2)				
Repeatability (perpendicular to sensing axis)		0.05 mm 0.002 in or less			0.5 mm 0.020 in or less				
Supply voltage		12 to 24 V DC ±10 % Ripple P-P 10 % or less							
Curr	ent consum	nption	Emitter: 10 mA or less, Receiver: 10 mA or less			13 mA or less			
Output		<npn output="" type=""> NPN open-collector transistor Maximum sink current: 50 mA Applied voltage: 30 V DC or less (between output and 0 V) Residual voltage: 2 V or less (at 50 mA sink current) 1 V or less (at 16 mA sink current)</npn>			<pnp output="" type=""> PNP open-collector transistor Maximum source current: 50 mA Applied voltage: 30 V DC or less (between output and +V) Residual voltage: 2 V or less (at 50 mA source current) 1 V or less (at 16 mA source current) </pnp>				
	Utilization	category			DC-12 o	r DC-13			
	Output op	eration	Light-ON	Dark-ON	Switchable either Light-ON or Dark-ON	Light-ON	Dark-ON		
	Short-circuit protection		Incorporated						
Res	oonse time		0.5 ms or less						
Operation indicator		Orange LED (lights up when the output is ON) (incorporated on the receiver for thru-beam type)							
Stability indicator		Green LED (lights up under stable light received condition or stable dark condition, incorporated on the receiver)			Green LED (lights up under stable light received condition or stable dark condition				
Sens	Sensitivity adjuster		Contin			Continuously variable adju	uster		
	Pollution of	degree	3 (Industrial environment)						
	Protection	1	IP67 (IEC)						
Environmental resistance	Ambient to	emperature	-25 to +55 °C −13 to +131 °F (No dew condensation or icing allowed), Storage: -30 to +70 °C −22 to +158 °F						
sista	Ambient h	umidity	35 to 85 % RH, Storage: 35 to 85 % RH						
al re	Ambient il	luminance	Incandescent light: 3,000 tx at the light-receiving face						
nent	EMC		EN 60947-5-2						
ronn	Voltage w	ithstandability	1,000 V AC for one min. between all supply terminals connected together and enclosure						
Envi	Insulation	resistance	20 MΩ, or more, with 250 V DC megger between all supply terminals connected together and enclosure						
_	Vibration r	resistance	10 to 500 Hz frequency, 3 mm 0.118 in amplitude (20			0 G max.) in X, Y and Z directions for two hours each			
Shock resistance		500 m/s ² acceleration (50 G approx.) in X, Y and Z directions for three times each							
Emitting element		Red LED (modulated)							
Material		Enclosure: Die-cast zinc (Nickel plated), Lens: Polycarbonate [EX-32 (-PN): Acrylic], Enclosure cover: Polycarbonate							
Cable		0.1 mm² 3-core (thru-beam type sensor emitter: 2-core) cabtyre cable, 2 m 6.562 ft long							
Cable extension		Extension up to total 50 m 164.042 ft is possible with 0.3 mm			n², or more, cable (thru-beam type: both emitter and receiver).				
Weight		Net weight (each emitter and receiver): 20 g approx. Gross weight: 65 g approx.			Net weight: 20 g approx., Gross weight: 45 g approx.				
Accessories		Nut: 2 pcs., Toothed lock washer: 2 pcs.			Nut: 1 pc., Toothed lock washer: 1 pc.				

Notes: 1) Where measurement conditions have not been specified precisely, the conditions used were an ambient temperature of +23 °C +73.4 °F.

2) The sensing range and the hysteresis are specified for white non-glossy paper (100 × 100 mm 3.937 × 3.937 in) as the object.

3) Make sure to confirm detection with an actual sensor before use.

FIBER SENSORS

LASER SENSORS

PHOTO-ELECTRIC SENSORS MICRO PHOTO-ELECTRIC

AREA

LIGHT CURTAINS

PRESSURE / FLOW SENSORS

INDUCTIVE PROXIMITY SENSORS

PARTICULAR USE SENSORS

SENSOR OPTIONS

SIMPLE WIRE-SAVING LINITS

WIRE-SAVING SYSTEMS

MEASURE-MENT SENSORS

STATIC CONTROL DEVICES

ENDOSCOPE

LASER MARKERS

PLC / TERMINALS

HUMAN MACHINE INTERFACES ENERGY CONSUMPTION VISUALIZATION COMPONENTS

FA COMPONENTS

MACHINE VISION SYSTEMS

> V URING YSTEMS

Selection Guide Amplifier Built-in ower Supply

Built-in Amplifierseparated

EX-10 EX-20

EX-40 CX-440

EQ-30 EQ-500

MQ-W RX-LS200

RX RT-610

LASER SENSORS

MICRO PHOTO-ELECTRIC SENSORS AREA SENSORS LIGHT CURTAINS

PRESSURE / SENSORS PARTICULAR

SENSORS SENSOR OPTIONS SIMPLE WIRE-SAVING UNITS

MEASURE-MENT SENSORS STATIC

CONTROL ENDOSCOPE

LASER MARKERS

HUMAN MACHINE INTERFACES ENERGY VISUALIZATION COMPONENTS COMPONENTS

VISION SYSTEMS

MACHINE

Power Supply Built-in

CX-400 EX-10 EX-20 EX-30 EX-40 CX-440 EQ-30 EQ-500 MQ-W RX-LS200


RX

RT-610

■ I/O CIRCUIT AND WIRING DIAGRAMS

NPN output type

I/O circuit diagram




Internal circuit -→ Users' circuit

Note: The emitter of the thru-beam type sensor does not incorporate the output.

Symbols ... D1: Reverse supply polarity protection diode D2: Reverse output polarity protection diode ZD: Surge absorption zener diode Tr: NPN output transistor


Wiring diagram



Note: The emitter of the thru-beam type sensor does not incorporate the black wire.

PNP output type

I/O circuit diagram




Internal circuit -→ Users' circuit

Note: The emitter of the thru-beam type sensor does not incorporate the output.


Symbols ... D1: Reverse supply polarity protection diode D2: Reverse output polarity protection diode ZD: Surge absorption zener diode Tr : PNP output transistor

Wiring diagram



Note: The emitter of the thru-beam type sensor does not incorporate the black wire.

SENSING CHARACTERISTICS (TYPICAL)



600 distance L distance L distance L Emitter Setting 200 7.874 \$ Receiver

Ó

Center


Operating angle θ ($^{\circ}$)

20

Angular deviation


200 Setting distance L (mm Emitter 100 20 Ó 20 0.787 → Right 1.575 Center Operating point & (mm in)

Parallel deviation with slit mask on one side



Thru-beam type


EX-31 EX-31 PN Thru-beam type




Sensing field

Left -

EX-32 EX-32 PN




Correlation between sensing object size and sensing range



Correlation between setting distance and excess gain 50 gain 10 Excess Ó 100 200 Setting distance L (mm in)

Diffuse reflective type

SENSING CHARACTERISTICS (TYPICAL)



PRECAUTIONS FOR PROPER USE


Refer to General precautions.

<u>^</u>


- Never use this product as a sensing device for personnel protection.
- In case of using sensing devices for personnel protection, use products which meet laws and standards, such as OSHA, ANSI or IEC etc., for personnel protection applicable in each region or country.
- Do not use during the initial transient time (50 ms) after the power supply is switched on.
- In case of using the sensor at a place where static electricity is generated, use a metal mounting plate. Also, ensure to ground the mounting plate.

DIMENSIONS (Unit: mm in)

The CAD data in the dimensions can be downloaded from our website



Note: Not incorporated on the emitter



Notes: 1) Not incorporated on the emitter.

2) It is the sensitivity adjuster on the emitter.

OS-EX30-1

Slit mask (optional)

Slit mask


Internal thread part (0.276) (0.276) (0.316)

M4 × 0.7 0.028, 3.8 0.150 deep

Material: Brass(Nickel plated)

Spacer

Material: POM



FIBER SENSORS

LASER SENSORS

> ELECTRIC SENSORS MICRO PHOTO-ELECTRIC

AREA SENSORS

LIGHT

PRESSURE / FLOW SENSORS INDUCTIVE PROXIMITY SENSORS

PARTICULAR USE SENSORS

> SENSOR OPTIONS

WIRE-SAVING UNITS

WIRE-SAVING SYSTEMS

MEASURE-MENT SENSORS

STATIC CONTROL DEVICES

ENDOSCOPE

LASER MARKERS

PLC / TERMINALS

HUMAN MACHINE INTERFACES ENERGY CONSUMPTION VISUALIZATION COMPONENTS

FA COMPONENTS

MACHINE VISION SYSTEMS

CURING SYSTEMS

Selection Guide Amplifier Built-in

Power Supply Built-in Amplifierseparated

CX-400 EX-10

EX-20

EX-40 CX-440

EQ-30 EQ-500

MQ-W RX-LS200

RX RT-610