

GST 150 BCE Professional



Advantages: GST 150 BCE Professional

The most powerful tool in its price class

- High power reserves, even in hard and thick beams, due to powerful and overload-capable 780-watt motor
- Extremely robust and bend-resistant sole plate for the toughest jobs
- High cutting precision due to new saw blade clamping system
- Tool-free saw blade clamping system for easy and fast saw blade changes
- Ergonomic grip area with softgrip surfaces for a high level of work comfort
- 4-stage pendulum action for fine through to coarse cuts
- Electronic speed preselection

Technical data: GST 150 BCE Professional

Rated power input	780 W
No-load stroke rate	500 – 3.100 spm
Weight	2,7 kg
Cable length	4 m
Stroke height	26 mm
Cutting depth	

Rated power input	780 W
Cutting depth in wood	150 mm
Cutting depth in aluminium	20 mm
Cutting depth in non-alloyed steel	10 mm

Functions

- Pendulum stroke adjustment
- Dust extraction
- Bosch SDS System
- Electronic
- Constant Electronic

Noise/vibration information

Measured values determined according to EN 60745
 Total vibration values (vector sum of three directions)

Sawing sheet metal	
Vibration emission value a_h	4.0 m/s ²
Uncertainty K	1.5 m/s ²
Sawing wood	
Vibration emission value a_h	7.0 m/s ²
Uncertainty K	1.5 m/s ²

The A-rated noise level of the power tool is typically as follows: Sound pressure level 83 dB(A); Sound power level 94 dB(A). Uncertainty K= 3 dB.