

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

95501-2641

Status:

Active

Overview:

Modular Plugs - Jacks

Description:

Modular Jack, Right Angle, Low Profile, Through Hole, 6/4, Gold (Au)

Documents:

3D Model

Drawing (PDF)

Product Specification PS-95501 (PDF)

Application Specification AS-85513-001 (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification

UL

E107635

General

Product Family

Series

Component Type

Magnetic

Overview

Performance Category

Power over Ethernet (PoE)

Product Name

Modular Jacks/Plugs

95501

PCB Jack

No

Modular Plugs - Jacks

3

N/A

RJ11

Physical

Color - Resin

Durability (mating cycles max)

Flammability

Inverted / Top Latch

Jack Height

Lightpipes/LEDs

Material - Metal

Material - Plating Mating

Material - Plating Termination

Material - Resin

Orientation

PCB Locator

PCB Retention

PCB Thickness - Recommended

Packaging Type

Pitch - Mating Interface

Pitch - Termination Interface

Ports

Positions / Loaded Contacts

Surface Mount Compatible (SMC)

Temperature Range - Operating

Termination Interface: Style

Waterproof / Dustproof

Wire/Cable Type

Black

500

94V-0

No

11.50mm

None

Copper Alloy

Gold

Tin

High Temperature Thermoplastic

Right Angle (Side Entry)

Yes

Yes

1.60mm

Tray

1.02mm

1.27mm

1

6/4

Yes

-40°C to +80°C

Through Hole

No

N/A

Electrical

Current - Maximum per Contact

Shielded

Voltage - Maximum

1.5A

No

125V DC

Solder Process Data

Duration at Max. Process Temperature (seconds)

Lead-free Process Capability

5

Wave Capable (TH only)




image - Reference only

Series

EU RoHS

ELV and RoHS

Compliant

REACH SVHC

Contains SVHC: No

Low-Halogen Status

Not Reviewed

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

95501Series

Mates With

90075 FCC 68 Plugs

Use With

90075

Max. Cycles at Max. Process Temperature	1
Process Temperature max. C	260
Material Info	
UPC	822350967532
Reference - Drawing Numbers	
Application Specification	AS-85513-001
Product Specification	PS-95501
Sales Drawing	SD-95501-001

This document was generated on 06/20/2012

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION