



# INTERCONNECTS


## SERIES 410, 450, 499 • .100" GRID (.018" DIA.) PINS, STRAIGHT AND RIGHT ANGLE • DOUBLE ROW STRIPS




**FIG. 1**



**FIG. 2**



**FIG. 3**


















**FIG. 4**

- Series 4XX are available with straight and right angle solder tails
- Series 450 & 499...009 use MM #3404 and #5011/5113 pins. See pages 212 and 214 for details
- Series 410 & 499...003 use MM #1001 and #1103/1602 receptacles. See pages 165, 166 and 167 for details
- Receptacles use Hi-Rel, 4-finger #30 BeCu contact rated at 3 amps. See page 253 for details
- Insulators are high temperature thermoplastic, suitable for all soldering operations



## ORDERING INFORMATION

<b>FIG. 1</b>	<b>Series 450...006</b>	<b>Straight Pin Header</b>		
	450-XX-2	-00-006000		
	Specify number of pins	02-64		
<b>FIG. 2</b>	<b>Series 499...009</b>	<b>Right Angle Pin Header</b>		
	499-10-2	-10-009000		
	Specify number of pins	02-64		
  				
<b>SPECIFY PLATING CODE XX=</b>		10 	90	40 
Pin Plating 		10 μ" Au	200 μ" Sn/Pb	200 μ" Sn

<b>FIG. 3</b>	<b>Series 410...001</b>	<b>Solder Tail Socket</b>					
	410-XX-2	-41-001000					
	Specify number of pins	02-64					
<b>FIG. 4</b>	<b>Series 499...003</b>	<b>Right Angle Socket</b>					
	499-XX-2	-10-003000					
	Specify number of pins	02-64					
  							
<b>SPECIFY PLATING CODE XX=</b>		11 	13 	91	93	41 	43 
Sleeve (Pin) 		10 μ" Au	10 μ" Au	200 μ" Sn/Pb	200 μ" Sn/Pb	200 μ" Sn	200 μ" Sn
Contact (Clip) 		10 μ" Au	30 μ" Au	10 μ" Au	30 μ" Au	10 μ" Au	30 μ" Au

