

Search Results


- Evaluate
 - FAQ's
- Design a Solution
 - Part Drawings
 - PDF-Tie Mount Me ..
- How to Buy
 - Bill of Material
 - Favorite Products List
 - Locate Distributor

Home > Product On-Line Catalog > Search Results >

Current refinements (click to remove) Search Tips

Cable Tie Mounts > Text Search: 'TM2S8-C100'

TM2S8-C100



- Unique cradle design provides maximum stability for the cable bundle
- Low profile design keeps bundle close to mounting surface where overhead space is limited

‡Cable tie cross section sizes: M = Miniature, I = Intermediate, S = Standard, HS = Heavy-Standard, LH = Light-Heavy

▪ Part Number	TM2S8-C100
▪ RoHS Compliancy Status	Compliant
▪ Part Description	Cable Tie Mount - Screw Applied
▪ Product Type	Cable Tie Mounts - Screw Applied
▪ Material	Weather Resistant Polypropylene
▪ Color	Black
▪ UL Recognized	E136577
▪ Height (In.)	0.28
▪ Height (mm)	7.0
▪ Length (In.)	0.63
▪ Length (mm)	16.0
▪ Width (In.)	0.43
▪ Width (mm)	10.8
▪ CE Compliant	Yes
▪ Environment	Outdoor
▪ Max. Continuous Use Temperature	-40°F – 221°F (-40°C – 105°C)
▪ Mounting Method	#8 (M4) Screw
▪ Pricing Description	Cable Tie Mount, .43" (10.9mm)W, #8 Screw (M4), Weather Resistant Poly
▪ Screw Size	#8 (M4)
▪ Screw Size Metric	M4
▪ Temperature Range	-40°F – 221°F (-40°C – 105°C)
▪ Type	Screw Applied
▪ Used With Cable Ties	M, I, S
▪ Min. Order UOM	PC
▪ Min. Order Qty.	100
▪ BOM Qty. (# of Pkgs.)	<input type="text" value="0"/>
▪ Add to Favorite Product List	

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.