

N-11MG

Electrical Specifications (@25°C)

1. Maximum Power: 2,000 VA
2. Input Voltage: 230 V, 50 / 60 Hz
3. Output Voltage: 115V \pm 5%
4. Full Secondary Load: 17.40 Amps RMS

Description:

The N-11MG is part of the line of Auto-Transformers that are single winding transformers in which the secondary coil is a fraction of the entire winding for voltage step-down. This causes part of the power to be transferred conductively through the windings, rather than all of the power being transferred by induction.

Safety:

These units are designed with 1500V isolation between the winding and the core. Materials and construction are rated for Class B insulation system.

Dimensions:

Unit: In inches




A	B	C	D	E
5.375	4.50	8.250	3.50	6.875

Weight: 33.25 lbs

Mounting Holes: .656 x 281

Cord: 6 ft. long, Plug NEMA 5-15P, Socket NEMA 6-15P

Schematic:



RoHS Compliance: As of manufacturing date February 2005, all standard products meet the requirements of 2002/95/EC, known as the RoHS initiative.

* Upon printing, this document is considered "uncontrolled". Please contact Triad Magnetics' website for the most current version.