



SAFETY DATA SHEET
STICK 2 DEBONDER AND REMOVER

Page 1
Issued: 5/11/08
Revision No: 2

1. IDENTIFICATION OF THE SUBSTANCE / PREPARATION AND OF THE COMPANY / UNDERTAKING

Product name: STICK 2 DEBONDER AND REMOVER
Product code: DEBOND
Company name: EVERBUILD BUILDING PRODUCTS LTD
SITE 41, KNOWSTHORPE WAY
CROSS GREEN INDUSTRIAL ESTATE
LEEDS
WEST YORKSHIRE
LS9OSW
ENGLAND
Tel: 0044 113 240 3456
Fax: 0044 113 240 0024
Emergency tel: 0044 113 240 3456 (office hours only)
Email: pault@everbuild.co.uk

2. HAZARDS IDENTIFICATION

Main hazards: Highly flammable. Harmful if swallowed. Irritating to skin. Very toxic to aquatic organisms, may cause long-term adverse effects in the aquatic environment. Harmful: may cause lung damage if swallowed. Vapours may cause drowsiness and dizziness.
Other hazards: In use, may form flammable / explosive vapour-air mixture.

3. COMPOSITION / INFORMATION ON INGREDIENTS

Hazardous ingredients: HEPTANE 30-50%
EINECS: 205-563-8 CAS: 142-82-5
[F] R11; [Xi] R38; [N] R50/53; [Xn] R65; [-] R67
• NITROMETHANE 30-50%
EINECS: 200-876-6 CAS: 75-52-5
[-] R5; [-] R10; [Xn] R22

4. FIRST AID MEASURES (SYMPTOMS)

Skin contact: There may be irritation and redness at the site of contact.
Eye contact: There may be irritation and redness. The eyes may water profusely.
Ingestion: There may be soreness and redness of the mouth and throat. Nausea and stomach pain may occur. There may be vomiting.
Inhalation: There may be irritation of the throat with a feeling of tightness in the chest.

4. FIRST AID MEASURES (ACTION)

Skin contact: Remove all contaminated clothes and footwear immediately unless stuck to skin. Drench the affected skin with running water for 10 minutes or longer if substance is still on skin. Consult a doctor.

[cont...]

SAFETY DATA SHEET

STICK 2 DEBONDER AND REMOVER

Eye contact: Bathe the eye with running water for 15 minutes. Consult a doctor.

Ingestion: Wash out mouth with water. Do not induce vomiting. If conscious, give half a litre of water to drink immediately. Consult a doctor.

Inhalation: Remove casualty from exposure ensuring one's own safety whilst doing so. Consult a doctor.

5. FIRE-FIGHTING MEASURES

Extinguishing media: Alcohol or polymer foam. Carbon dioxide. Dry chemical powder. Use water spray to cool containers.

Exposure hazards: Highly flammable. In combustion emits toxic fumes. Forms explosive air-vapour mixture. Vapour may travel considerable distance to source of ignition and flash back.

Protection of fire-fighters: Wear self-contained breathing apparatus. Wear protective clothing to prevent contact with skin and eyes.

6. ACCIDENTAL RELEASE MEASURES

Personal precautions: Refer to section 8 of SDS for personal protection details. If outside do not approach from downwind. If outside keep bystanders upwind and away from danger point. Mark out the contaminated area with signs and prevent access to unauthorised personnel. Turn leaking containers leak-side up to prevent the escape of liquid. Eliminate all sources of ignition.

Environmental precautions: Do not discharge into drains or rivers. Contain the spillage using bunding.

Clean-up procedures: Absorb into dry earth or sand. Transfer to a closable, labelled salvage container for disposal by an appropriate method. Do not use equipment in clean-up procedure which may produce sparks.

7. HANDLING AND STORAGE

Handling requirements: Avoid direct contact with the substance. Ensure there is sufficient ventilation of the area. Do not handle in a confined space. Avoid the formation or spread of mists in the air. Smoking is forbidden. Use non-sparking tools.

Storage conditions: Store in cool, well ventilated area. Keep container tightly closed. Keep away from sources of ignition. Prevent the build up of electrostatic charge in the immediate area. Ensure lighting and electrical equipment are not a source of ignition. Store in original containers between +5 and +25°C. Storage outside these parameters will dramatically reduce shelf life and invalidates all product warranties.

Suitable packaging: Must only be kept in original packaging.

8. EXPOSURE CONTROLS / PERSONAL PROTECTION

Hazardous ingredients: HEPTANE

WEL (8 hr TWA): 500 ppm

- NITROMETHANE

WEL (8 hr TWA): 254 mg/m³ WEL (15 min STEL): 381 mg/m³

Engineering measures: Ensure there is sufficient ventilation of the area. Ensure lighting and electrical equipment are not a source of ignition.

SAFETY DATA SHEET

STICK 2 DEBONDER AND REMOVER

Respiratory protection: Self-contained breathing apparatus must be available in case of emergency.

Hand protection: Impermeable gloves.

Eye protection: Safety glasses. Ensure eye bath is to hand.

Skin protection: Impermeable protective clothing.

9. PHYSICAL AND CHEMICAL PROPERTIES

State: Liquid

Colour: Colourless

Odour: Characteristic odour

Evaporation rate: Fast

Boiling point/range°C: 40

Flash point°C: -9

10. STABILITY AND REACTIVITY

Stability: Stable under normal conditions. Stable at room temperature.

Conditions to avoid: Heat. Hot surfaces. Sources of ignition. Flames.

Materials to avoid: Strong oxidising agents. Strong acids.

Haz. decomp. products: In combustion emits toxic fumes.

11. TOXICOLOGICAL INFORMATION

Hazardous ingredients: HEPTANE

IVN MUS LD50 222 mg/kg

- NITROMETHANE

IPR RAT LDLO 1500 mg/kg

ORL MUS LD50 950 mg/kg

ORL RAT LD50 940 mg/kg

Routes of exposure: Refer to section 4 of SDS for routes of exposure and corresponding symptoms.

12. ECOLOGICAL INFORMATION

Mobility: Readily absorbed into soil.

Persistence and degradability: No data available.

Bioaccumulative potential: No data available.

Other adverse effects: No data available.

13. DISPOSAL CONSIDERATIONS

NB: The user's attention is drawn to the possible existence of regional or national regulations regarding disposal.

14. TRANSPORT INFORMATION

SAFETY DATA SHEET
STICK 2 DEBONDER AND REMOVER**ADR / RID**

UN no: 1206 **ADR Class:** 3
Packing group: II **Classification code:** F1
Shipping name: HEPTANES
Labelling: 3 **Hazard ID no:** 33

**IMDG / IMO**

UN no: 1206 **Class:** 3
Packing group: II **EmS:** F-E,S-D
Marine pollutant: NO
Labelling: 3

IATA / ICAO

UN no: 1206 **Class:** 3
Packing group: II
Packing instructions: 305(P&CA); 307(CAO)
Labelling: 3

15. REGULATORY INFORMATION

Hazard symbols: Highly flammable.
Dangerous for the environment.
Harmful.



Risk phrases: R11: Highly flammable.
R22: Harmful if swallowed.
R38: Irritating to skin.
R50/53: Very toxic to aquatic organisms, may cause long-term adverse effects in the aquatic environment.
R65: Harmful: may cause lung damage if swallowed.
R67: Vapours may cause drowsiness and dizziness.

Safety phrases: S2: Keep out of the reach of children.
S29: Do not empty into drains.
S46: If swallowed, seek medical advice immediately and show this container or label.

SAFETY DATA SHEET
STICK 2 DEBONDER AND REMOVER

S61: Avoid release to the environment. Refer to special instructions / safety data sheets.

S16: Keep away from sources of ignition - No smoking.

S23: Do not breathe vapour.

Haz. ingredients (label): HEPTANE; NITROMETHANE

Note: The regulatory information given above only indicates the principal regulations specifically applicable to the product described in the safety data sheet. The user's attention is drawn to the possible existence of additional provisions which complete these regulations. Refer to all applicable national, international and local regulations or provisions.

16. OTHER INFORMATION

Risk phrases used in s.3: R11: Highly flammable.
R38: Irritating to skin.
R50/53: Very toxic to aquatic organisms, may cause long-term adverse effects in the aquatic environment.
R65: Harmful: may cause lung damage if swallowed.
R67: Vapours may cause drowsiness and dizziness.
R5: Heating may cause an explosion.
R10: Flammable.
R22: Harmful if swallowed.

Legal disclaimer: The above information is believed to be correct but does not purport to be all inclusive and shall be used only as a guide. This company shall not be held liable for any damage resulting from handling or from contact with the above product.