


OPEN GROMMETS



A	B	C	D	E	FIO Order Code
4.8	1.6	3.2	6.4	8.0	118-9027
6.4	1.2	4.0	4.0	9.5	118-9028
6.4	1.6	4.0	6.4	9.5	118-9030
6.4	1.6	4.8	7.1	9.5	118-9031
8.0	1.6	4.8	6.4	11.1	118-9032
9.5	1.6	4.8	5.6	12.7	118-9033
9.5	1.6	6.4	4.8	12.7	118-9034
9.5	1.6	6.4	6.4	14.3	118-9035
9.5	1.6	7.5	6.4	13.5	118-9036
9.5	1.6	8.0	4.8	14.3	118-9038
10.3	1.6	8.0	6.4	15.9	118-9039
11.1	1.6	7.2	6.4	15.9	118-9040
11.1	1.6	8.0	4.8	14.3	118-9041
11.9	1.6	6.4	8.0	15.9	118-9042
11.9	1.6	9.5	6.8	17.5	118-9043
12.7	1.6	9.5	6.3	15.9	118-9044
14.3	1.6	11.1	6.4	19.0	118-9045
19.0	1.6	12.7	6.4	25.4	118-9046
20.0	1.6	15.9	6.4	23.8	118-9047
25.4	1.6	19.0	7.5	30.0	118-9048

MAXIMUM CONSTANT WORKING TEMPERATURE 70°C
 MINIMUM CONSTANT TEMPERATURE -35°C
 BLACK PVC NORMAL SHORE HARDNESS FROM 43° TO 55°