

### V60-1xx Attenuators for IRS and MATV Systems

- 3dB, 6dB, 10dB and 18dB models available
- High accuracy and stability performance design with PCB construction
- Unique wall mount design with secure fixing to avoid connector strain
- DC pass for use with line powered accessories

Vision's "System" Attenuators are designed for long-term stable performance in a surface mount package. The surface mount design means that the attenuator can be securely and stably mounted onto a headend board for reliability and ease of use without the risk of straining the cables or connectors. Stable long term performance is essential in a system. Strained coaxial connectors on amplifiers, multiswitches and other system accessories may alter performance and change the results of the system.



Model	V60-103	V60-106	V60-110	V60-118
Frequency Range	40-2100MHz			
Attenuation Value	3dB $\pm 0.2$	6dB $\pm 0.2$	10dB $\pm 0.2$	18dB $\pm 0.2$
Return Loss	>23dB	>28dB	>29dB	>18dB
Screening factor	>105dB			
Connector	2 x F female connector			
DC Pass	Bi-directional 18V 500mA max			
Dimensions (inc fixings and connectors)	70 x 26 x 16mm			
Material	Diecast Zinc Alloy			

In the interests of continued product development & improvement, Vision Products (Europe) Ltd reserves the right to change product specifications, design & dimensions.  
Data correct at time of going to press 21<sup>st</sup> March 2011.

ES&OE © Vision Products (Europe) Ltd.

Vision Products (Europe) Ltd Unit 1 Redbourne Park, Liliput Road,  
Brackmills, Northampton NN4 7DT  
Tel: 0845 017 1010 Fax: 0845 017 1011 Email: [technical@vision-products.co.uk](mailto:technical@vision-products.co.uk)  
ES&OE ©2009 Vision Products (Europe) Ltd  
Company Reg No. 05044212  
[www.vision-products.co.uk](http://www.vision-products.co.uk)