

9013GHG1S8J54

PRESSURE SWITCH 575VAC 5HP G +OPTIONS



by Schneider Electric

List Price \$93.00 USD

Availability **Stock Item: This item is normally stocked in our distribution facility.**

Technical Characteristics

Maximum Allowable Pressure	300 PSIG
Maximum Voltage Rating	575VAC
Application	Control electrically driven water pumps and air compressors
Action	Standard Action
Actuator Type	Diaphragm
Marketing Trade Name	Pumptrol
Contact Arrangement	DPST
Approvals	UL Listed File: E12158 CCN NKPZ - CSA Certified File: LR25490
Depth	3.68 Inches
Diaphragm	Nitrile (Buna N)
Differential Type	Adjustable
Differential	20 to 40 PSIG
Enclosure Rating	NEMA 1
Height	5.72 Inches
Enclosure Type	General Purpose (Indoor)
Flange Material	Zinc Plated Steel
Horsepower Rating (1-Phase)	2HP@115VAC - 3HP@230VAC - 5HP@460/575VAC
Horsepower Rating (3-Phase)	3HP@115VAC - 5HP@230VAC - 5HP@460/575VAC
Number of Poles	2-Pole
Weight	2.25 Pounds
Mounting Type	Bracket
Width	3.44 Inches
Pressure Setting	110 to 125 PSIG
Range on Increasing Pressure	65 to 200 PSIG
Terminal Type	Screw Clamp
Range on Decreasing Pressure	40 to 170 PSIG
Pressure Connection	0.13 Inch NPSF
Type	G

Shipping and Ordering

Category	21536 - Pressure Switches, Light Industrial, Type GMG, GSB, GSG, GSR, GSW, GHB, GHG, GHR & GHW
Discount Schedule	CP7G

Generated: 08/06/2012 07:26:01

GTIN	00785901461425
Package Quantity	1
Weight	1.88 lbs.
Availability Code	Stock Item: This item is normally stocked in our distribution facility.
Returnability	Y
Country of Origin	MX

As standards, specifications, and designs change from time to time, please ask for confirmation of the information given in this document.