

TELEDATA ELECTRONIC SERVICE CASE

The case with a basic equipment of special tools for the installation and maintenance of complex telecommunication systems and data networks.

6700 **BERNSTEIN** TELEDATA with tool set

6715 **BERNSTEIN** TELEDATA without tool set

Description:

Case made from deep-drawn, impact-resistant, grained black plastic, with sturdy aluminium frame, dustproof and rainproof, acid- and scratch-resistant. 80 tools are clearly arranged on two removable tool trays, one of it on both sides, and in the plastic tray with adjustable partitions in the bottom of the case. The basic equipment for special operations at telecommunication systems and data networks may efficiently be completed by special tools additionally recommended.

The case has 2 locks.

Outside dimensions: 470 x 340 x 170 mm

Weight without tools: approx. 4.600 kg

Weight with tools: approx. 8.700 kg

Tool set

No.	Description of individual tools	No.	Description of individual tools
2-265	2 test prods , red and black, extremely slim, pointed and flexible, blade made from 1 mm steel wire	5-107	Engineer's tweezers , with bent tips, 150 mm, made from steel, nickel-plated
2-601	IC-tweezers , nickel-plated, 125 mm, for gripping, inserting and removing IC's	5-117	Engineer's tweezers , straight-flat-wide, 145 mm, made from steel, nickel-plated
2-620	PLCC-extractor	5-240	Warding files , 6-piece set, with wooden handles, in plastic wallet
2-701	Insertion tool with sensor , for connecting the wires and simultaneously cutting off the residual wire	5-505	Insulation stripping tool , with hook blade, for cable diameter of 4 up to 28 mm
3-112-2	Side cutters , 120 mm, for soft wire up to 1.0 mm, with rounded head, double leaf spring, chrome-plated, with transparent insulation	6-103	Socket wrench , 4.5 mm, chrome vanadium, chrome-plated, with square handle
3-134 VDE	Side cutters , 160 mm, for steel wire up to 1.6 mm Ø, chrome-plated, with VDE safety insulation	6-104	Socket wrench , 5.0 mm, chrome vanadium, chrome-plated, with square handle
3-235-1	Telephon pliers , 160 mm, chrome-plated, with BERNSTEINIT-insulation	6-105	Socket wrench , 5.5 mm, chrome-vanadium, chrome-plated, with square handle
3-532-1	Flat nose pliers , 160 mm, with long jaws, chrome-plated, with BERNSTEINIT-insulation	6-500-12	Double open-ended wrench , 12 x 13 mm, chrome vanadium, chrome-plated
3-574-1	Water pump pliers , 175 mm, made from chrome vanadium, chrome-plated, with BERNSTEINIT-insulation	6-500-18	Double open-ended wrench , 18 x 19 mm, chrome vanadium, chrome-plated
3-732-1	Combination pliers , 165 mm, chrome-plated, with BERNSTEINIT-insulation	6-600	Combination ring- and open-ended wrench , 7-piece set, chrome vanadium, chrome-plated, 6.0, 7.0, 8.0, 9.0, 10.0, 11.0, 13.0 mm
3-0605	Combination crimping pliers , 200 mm, for connector types 6P/6C, 6P/4C, 6P/2C, 8P/8C	6-600-12	Combination ring- and open-ended wrench , 12 mm, chrome vanadium, chrome-plated
4-222	Screwdriver , with special square BERNSTEIN handle, blade made from chrome vanadium, chrome-plated, 260 x 3.0 mm, with black tip	6-600-17	Combination ring- and open-ended wrench , 17 mm, chrome vanadium, chrome-plated
4-227	Crosspoint-screwdriver , size 1, with special square BERNSTEIN handle, blade made from chrome vanadium, chrome-plated, 300 mm, with black tip	6-600-19	Combination ring- and open-ended wrench , 19 mm, chrome vanadium, chrome-plated
4-228	Crosspoint-screwdriver , size 2, with special square BERNSTEIN handle, blade made from chrome vanadium, chrome-plated, 300 mm, with black tip	6-880	Hexagon wrench keys , 8-piece set in a wallet, 1/16", 5/64", 3/32", 1/8", 5/32", 3/16", 7/32", 1/4"
4-431	Retaining screwdrivers , for inserting and tightening slotted screws, blade made from chrome vanadium, nickel-plated, insulated, blade 100 x 3.0 mm,	6-950	Ballpoint wrench keys , hexagon, 8-piece set in a wallet, 1.5, 2.0, 2.5, 3.0, 4.0, 5.0, 6.0, 8.0 mm
4-437	Retaining screwdriver , for inserting and tightening cross-recess screws size 1, blade made from chrome vanadium, nickel-plated, insulated	6-995	Torx screwdrivers with bore-hole in the tip , 8-piece set in a box, T 9, T 10, T 15, T 20, T 25, T 27, T 30, T 40
14-651 VDE	Screwdriver , blade 75 x 2.5 mm, with VDE-insulation	7-425	Duster
14-652 VDE	Screwdriver , blade 100 x 3.5 mm, with VDE-insulation	7-506	Roller tape measure , 2 m
14-653 VDE	Screwdriver , blade 100 x 4.0 mm, with VDE-insulation	7-616	Pocket saw , with adjustable wooden handle, in a wallet
14-681 VDE	Cross-recess screwdriver , size 0, with VDE-insulation, blade length 60 mm	9-316/5	5 Chip-Container , conductive box with lid, black, internal dimensions: 118 x 32 x 14 mm
14-682 VDE	Cross-recess screwdriver , size 1, with VDE-insulation, blade length 80 mm		
14-683 VDE	Cross-recess screwdriver , size 2, with VDE-insulation, blade length 100 mm		
14-684 VDE	Cross-recess screwdriver , size 3, with VDE-insulation, blade length 150 mm		

To complete the set we recommend:

2-751	Test headphones , 1 x 600 ohm, switchable from 600 to 10.000 ohm, with fine control including test prods, maximum load 2 W
2-702	Insertion tool for systems HVt 71 , for connecting the cable conductors and jumper wires
8-110	ERSA fine soldering iron , Tip 260 BN/230 V/16 W
8-385	ERSA OVAC X desoldering pump

TELEDATA 6700 ELECTRONIC SERVICE CASE

The service case for the ambitious Telecommunication engineer

