



2182Y (Har. code H03VV-F2)

pro-POWER

Two-Core Round 300 / 300 V



Application

Power supply wire, suitable for indoor small electrical instrument, or general in portable tool

Construction

Conductor

Material : Stranded plain annealed copper wire

Insulation

Material : PVC
Colours : Blue and brown

Sheath

Material : PVC

Physical Properties

Operating Temperature : -15°C to 70°C

Electrical Properties

Voltage Test : Core to core : 1,500 V ac / 1 min
Voltage Rating : 300 / 300 V

2182Y (Har. code H03VV-F2)

pro-POWER

Two-Core Round 300 / 300 V

Specification Table

Description	Conductor Stranding (mm (mm ²))	Insulation Nominal Inner Diameter (mm)	Sheath Nominal Outer Diameter (mm)	Minimum Bend Radius	Nominal DC Resistance (Ω / km)	Current Rating (A)	Part Number
Cable, Flex, 2182Y, White, 0.75 mm, 50 m	24 / 0.2 (0.75)	2.2	5.8	58	26	6	2182Y-0.75MMWHT50M
Cable, Flex, White, 0.75 mm, 100 m							2182Y-0.75MMWHT100M
Cable, Flex, 2182Y, Black, 0.75 mm, 50 m							2182Y-0.75MMBLK50M
Cable, Flex, Black, 0.75 mm, 100 m							2182Y-0.75MMBLK100M
Cable, Flex, 2182Y, Grey, 0.75 mm, 100 m							2182Y-0.75MMGRY100M
Cable, Flex, 2182Y, White, 0.5 mm, 50 m	16 / 0.2 (0.5)	2	5.4	54	39	3	2182Y-0.5MMWHT50M
Cable, Flex, 2182Y, White, 0.5 mm, 100 m							2182Y-0.5MMWHT100M
Cable, Flex, 2182Y, Black, 0.5 mm, 50 m							2182Y-0.5MMBLK50M
Cable, Flex, 2182Y, Black, 0.5 mm, 100 m							2182Y-0.5MMBLK100M
Cable, Flex, 2182Y, Grey, 0.5 mm, 100 m							2182Y-0.5MMGRY100M

Dimensions : Millimetres

Important Notice : This data sheet and its contents (the "Information") belong to the members of the Premier Farnell group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Pro-POWER is the registered trademark of the Group. © Premier Farnell plc 2012.

www.element14.com
www.farnell.com
www.newark.com
www.cpc.co.uk

pro-POWER