

Soldering Tips - Hakko

HS SERIES

COMPATIBLE STATIONS: Hakko FX-888, Hakko FX-888E, Hakko FX-8801, Hakko 926, Hakko 928, Hakko 936, Hakko 937, Hakko 951, Hakko 952, Hakko 958, Hakko 959, Hakko 701, Hakko 702B, Hakko 900M, Hakko 900M-ESD, Hakko 907, Hakko 907-ESD

Plato is one of the largest manufacturers of soldering tips in the world, producing tips to fit all of the most popular soldering stations. The long life and fast heat recovery of Plato soldering tips increases user effectiveness and decreases production times. All Plato soldering tips manufactured since January 2004 are tinned with Lead-Free solder.

Long Life: Using a high quality Plato soldering tip increases soldering speed and decreases the total cost of manufacture. Higher temperatures and high tin content solders, common in lead-free soldering processes, place additional strain on soldering iron tips. The long life of a Plato soldering iron tip reduces tip changes, decreasing the total number of tips used and decreasing production time.

Rapid Heat Recovery: Plato soldering tips are constructed from highly conductive premium grade copper to transmit heat to the work more quickly than other brands of soldering tips. This quick heat recovery enables more joints to be soldered per minute, thus reducing manufacturing time and costs.



- . HS Popular Plato tip shapes
- HS18 New tip designs for faster heat recovery
- Fast heat recovering increases soldering speed
- Longer tip reduces manufacturing costs
- · Fewer tip change overs

Product Dimensions

HS-5701 Bevel, micro

Cross Reference: Hakko 900M-T-1C, Hakko T18-C1 1.2mm 10 units/case



HS-5702 Bevel, micro

Cross Reference: Hakko 900M-T-2C, Hakko T18-C2 2.0mm 10 units/case



HS-5703 Bevel

Cross Reference: Hakko 900M-T-3C, Hakko T18-C3 3.0mm 10 units/case



HS18-5703 Bevel

Cross Reference: Hakko 900M-T-3C, Hakko T18-C3 3.0mm







HS-5875 Bevel

Cross Reference: Hakko 900M-T-4C, Hakko T18-C4 4.0mm 10 units/case

5/32" (4.0)

HS-2863 Screwdriver

Cross Reference: Hakko 900M-T-0.8D, Hakko T18-D08 0.8mm 10 units/case



HS-6030 Screwdriver, long

Cross Reference: Hakko 900M-T-1.2LD, Hakko T18-DL12 1.2mm 10 units/case



HS-2751 Screwdriver

Cross Reference: Hakko 900M-T-1.6D, Hakko T18-D16
1.6mm



HS-2752 Screwdriver

Cross Reference: Hakko 900M-T-2.4D, Hakko T18-D24 2.4mm 10 units/case



HS18-2752 Screwdriver

Cross Reference: Hakko 900M-T-2.4D, Hakko T18-D24 2.4mm 10 units/case



HS-2753 Screwdriver

Cross Reference: Hakko 900M-T-3.2D, Hakko T18-D32 3.2mm





HS-4791 Angled SMD

Cross Reference: Hakko 900M-T-0.2RB, Hakko T18-BR02 0.4mm 10 units/case







HS-0925 Angled SMD


Cross Reference: Hakko 900M-T-H 1.6mm 10 units/case





HS-4785 Point, rounded

Cross Reference: Hakko 900M-T-B, Hakko T18-B 1.0mm x 6.4mm tin length 10 units/case




HS18-4785 Point, rounded

Cross Reference: Hakko T18-B, Hakko 900M-T-B



HS-8179 Point, rounded

1.0mm x 7.6mm tin length 10 units/case



HS-4786 Point, rounded

Cross Reference: Hakko 900M-T-LB, Hakko T18-BL 0.8mm 10 units/case



HS-4787 Point, micro rounded

Cross Reference: Hakko 900M-T-I, Hakko T18-I 0.4mm 10 units/case




HS18-4787 Point, micro rounded

Cross Reference: Hakko T18-I, Hakko 900M-T-I 0.4mm 10 units/case



HS-0927 Knife

Cross Reference: Hakko 900M-T-K, Hakko T18-K 6.3mm 10 units/case







HS18-0927 Knife

Cross Reference: Hakko 900M-T-K, Hakko T18-K 10 units/case





HS18-0929 Knife

10 units/case





HS-2796 Screwdriver

Cross Reference: Hakko 900M-T-1.2D, Hakko T18-D12 1.2mm





HS-1665 Screwdriver


Cross Reference: Hakko 900M-T-S3, Hakko T18-S3



HS-8175 Pointed

Cross Reference: Hakko 900M-T-S4, Hakko T18-S4 10 units/case





HS-8157 Angled SMD

Cross Reference: Hakko 900M-T-S5, Hakko T18-S5 10 units/case



HS-0530 SMD flow tip

Cross Reference: Hakko SMD Flow Tip 3.3mm





HS-0531 SMD flow tip



Environmental Policy

Techspray is committed to developing products to ensure a safer and cleaner environment. We will continue to meet and sustain the regulations of all federal, state and local government agencies.





Resources

Techspray products are supported by a global sales, technical and customer services resources.

For additional technical information on this product or other Techspray products in the United States, call the technical sales department at 800-858-4043, email tsales@techspray.com or visit our web site at: www.techspray.com.

North America

Techspray P.O. Box 949 Amarillo, TX 79105 800-858-4043

Email: tsales@techspray.com

<u>Europe</u>

ITW Contamination Control Saffierlaan 5 2132 VZ Hoofddorp The Netherlands +31 88 1307 400 Email: info@itw-cc.com Countries Outside US

Call to locate a distributor in your country.

Important Notice to Purchaser/User: The information in this publication is based on tests that we believe are reliable. The results may vary due to differences in tests type and conditions. We recommend that each user evaluate the product to determine its suitability for the intended application. Conditions of use are outside our control and vary widely. Techspray's only obligation and your only solution is replacement of product that is shown to be defective when you receive it. In no case will Techspray be liable for any special, incidental, or consequential damages based on breach of warranty, negligence or any other theory.

© 2013 Techspray, A Division of ITW

