part no: HI 98130 (high range)

HI 98129 and HI 98130 are waterproof testers that offer high accuracy pH, conductivity, total dissolved solids and temperature measurements in a single meter.

No more switching between meters for routine measurements:

- These floating, waterproof combination testers have an easy to read display and automatic shut-off
- pH and EC/TDS readings are automatically temperature compensated
- The EC/TDS conversion factor is user selectable as well as the temperature compensation coefficient
- Both testers feature a replaceable pH electrode cartridge together with an EC/TDS graphite electrode
- Automatic shut-off helps preserve battery life
- Replaceable pH cartridge extends life of the tester when pH sensor is exhausted, simply replace it with a new one

Calibrate direct into Hanna buffer solution sachets



Multiparameter pH, EC, TDS

Automatic 1 or 2 point pH calibration рН

Rubberised keyboard

- Quick and easy to operate
- Easy switch between Celsius & Fahrenheit readouts
- **HOLD** function



Easy to replace pH electrode cartridge with sturdy snap-in connector means there are no pins to bend or break



Illustration shows Low Range Tester HI 98129

Large LCD display

- pH and temperature displayed simultaneously
- Automatic temperature compensation
- **BEPS Battery Error Prevention** System
- Floating waterproof casing with tactile grip makes testing easier and less of a headache!



Removable safety cap



On-screen battery life

LCD indicates the percentage of battery power remaining at startup



HOLD function

The HOLD function "freezes" the LCD display temporarily



Instability & ATC indicators

Ensures reliable EC and TDS measurements, ATC symbol is shown when active



Standard or N.I.S.T buffer clibration

Automatic calibration is performed with 2 sets of memorised buffers for greater accuracy



Adjustable temperature coefficient factor

Users can choose between different BETA (B) factors for precise temperature compensated measurements



Adjustable TDS ratio

For measurement accuracy, users can choose between different conductivity to TDS conversion factors

рН

pH/TDS/Conductivity

Low or High range conductivity?

Simply select the model that is most appropriate for your testing range:

For low range: select HI 98129 0 to 3999 uS/cm; 0 to 2000 ppm

For high range: select HI 98130

0.00 to 20.00 mS/cm; 0.00 to 10.00 ppt

Supplied with

- HI 73127 pH electrode
- HI 73128 electrode removal tool
- **Batteries**
- Instructions



Solutions

We manufacture a wide range of solutions for the care, cleaning and calibration of your electrodes.



High accuracy EC/TDS graphite probe 130 The graphite conductivity probe provides greater accuracy because it cannot be contaminated by salt deposits in the solution. The exposed temperature sensor provides fast response times and guarantees highly accurate temperature compensated readings. For replacement probe quote part number: HI 73127

Specifications

Product Code		HI 98129	HI 98130
	рН	0.00 to 14.00	
Range	EC	0 to 3999 μS/cm	0.00 to 20.00 mS/cm
	TDS	0 to 2000 ppm	0.00 to 10.00 ppt
	Temperature	0.0 to 60.0 °C / 30.0 to 140.0 °F	
Resolution	рН	0.01	
	EC	1 μS/cm	0.01 mS/cm
	TDS	1 ppm	0.01 ppt
	Temperature	0.1°C	
Accuracy	рН	±0.05	
	EC/TDS	±2% F.S.	
	Temperature	±0.5 °C / ±1 °F	
Calibration	pH Automatic	1 or 2 points with 2 sets of memorised buffers (pH 4.01/7.01/10.1 or pH 4.01/6.86/9.18)	
	EC/TDS Automatic	1 point at 1413 μS/c, or 12.88 mS/cm	
Automatic Temperature Compensation		Yes	
Battery Type / Life		(4) 1.5V / 100 hours	
Battery Error Prevention System		Yes	
Auto-off		After 8 minutes	
Dimension / Weight		163 x 40 x 26 mm / 100 g	