






REVISIONS		
ISS	DESCRIPTION	DATE

RoHS COMPLIANT



RECOMMENDED
CABLE STRIPPING DIM'S



1. CRIMPED FERRULE
HEX CRIMP SIZE .213"
2. CRIMPED CONTACT PIN
HEX CRIMP SIZE .068"



TITLE: BNC MALE CRIMP (75 ohms)
(FOR RG179/U)

PART NO: BNC2-179

DR. NO: 50013-606(B002B179-96-100)

APRD:	UNLESS OTHERWISE SPECIFIED TOLERANCES 0.5-6 = ±0.2 >6-30 = ±0.4 >30-120 = ±0.6 >120-315 = ±1 >315-1000 = ±1.6 ANGLES = ±5°
CHKD:	
DR:	
DATE: 06/27/08"	UNIT: mm
SHEET: .	SCALE: 3/1

10	FERRULE	BRASS	NICKEL	KA/2005/10527\ KA/2005/60362
9	SPACER	DELRIN	WHITE	KA/2005/10531
8	CONTACT PIN	BRASS	GOLD	KA/2005/10527\ KA/2005/30993
7	SHELL	BRASS	NICKEL	KA/2005/10527\ KA/2005/60362
6	WASHER	STEEL	NICKEL	KA/2005/10523\ KA/2005/60362
5	SPRING	SK-5	NICKEL	KA/2005/10524\ KA/2005/60362
4	C WASHER	STEEL	NICKEL	KA/2005/10523\ KA/2005/60362
3	GASKET	PVC	RED	KA/2005/10533
2	INSULATOR	DELRIN	WHITE	KA/2005/10531
1	BODY	BRASS	NICKEL	KA/2005/10527\ KA/2005/60362
NO.	DESCRIPTION	MATERIAL	FINISH	SGS REPORT NO