

LED

Orange / Green, 3mm



Specifications:

Dice material	: GaAsP on GaP/GaP
Emitted colour	: Orange / Green
Lens colour	: White Diffused
Peak wavelength	: 635/568nm
Viewing angle	: 76°
Luminous intensity (IV)	: 8.2/8mcd

Absolute Maximum Ratings (T_a = 25°C)

Reverse Voltage	5V
Reverse Current	10µA (V _R = 5V)
Operating Temperature Range	-40°C to +85°C
Storage Temperature Range	-40°C to +100°C
Lead Soldering Temperature Range 1.6mm (1/16 inch) from body	260°C for 5 Seconds

Electrical/Optical Characteristics at T_a = 25°C






Parameter	Symbol	Minimum	Typical	Maximum	Unit	Test
Luminous Intensity	IV	3.8/3.6	8.2/8	12/11	mcd	IF = 20mA
Viewing Angle	2θ 1/2	-	76	-	degrees	
Peak Emission Wavelength	λP	-	635/568	-	nm	-
Dominant Wavelength	λD	-	625/570	-		-
Spectral Line Half-Width	Δλ	-	45/30	-		-
Forward Voltage	VF	1.6/1.7	2/2.1	2.6/2.6	V	IF = 20mA
Power Dissipation	Pd	-	-	85	-	-
Peak Forward Current (Duty 1/10 at 1KHz)	IF (Peak)	-	-	100	-	-
Recommended Operating Current	IF (Rec)	-	20	-	mA	-

LED

Orange / Green, 3mm



Orange (GaAsP/CaP $\lambda_P = 635\text{nm}$)



LED

Orange / Green, 3mm



Green (GaP $\lambda_P = 568\text{nm}$)

