

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

502351-0500

Status:

Active

Overview:

DuraClik™ Connector System

Description:

DuraClik™ Wire-to-Board Receptacle Housing, Single Row, 5 Circuits

Documents:

3D Model

Drawing (PDF)

Product Specification PS-502351-001 (PDF)

Product Specification PS-502351-002 (PDF)

Packaging Specification PK-502351-001 (PDF)


RoHS Certificate of Compliance (PDF)

General	
Product Family	Crimp Housings
Series	502351
Application	Signal, Wire-to-Board
Comments	Molex part has an inner-locking system versus an outer-locking system. Molex Part with tail protection feature.
Overview	DuraClik™ Connector System
Product Name	DuraClik™
UPC	884982894488
Physical	
Circuits (maximum)	5
Color - Resin	White
Gender	Receptacle
Glow-Wire Compliant	No
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Net Weight	0.238/g
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	2.00mm
Polarized to Mating Part	Yes
Temperature Range - Operating	-40°C to +105°C

Electrical	
Current - Maximum per Contact	3A

Material Info

Reference - Drawing Numbers	
Packaging Specification	PK-502351-001
Product Specification	PS-502351-001, PS-502351-002, RPS-502351-001, RPS-502351-006-JP, RPS-502351-008-JP, RPS-502351-009-JP, RPS-502351-011-JP
Sales Drawing	SD-502351-001



EU RoHS

ELV and RoHS Compliant

REACH SVHC

Contains SVHC: No

Low-Halogen Status

Not Low-Halogen

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

502351Series

Mates With

560020 , 502352 2.00mm Pitch DuraClik™ Wire-to-Board Header

Use With

50212 Crimp Terminal . 560085 Crimp Terminal . 56161 Crimp Terminal

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION