TPC-651H TPC-1251H TPC-1551H

5.7" VGA / 12.1" SVGA / 15" XGA TFT LCD Intel® Atom™ Touch Panel Computers with Wide Operating Temperatures



Features

- Intel® Atom™ processor (up to 1.33 GHz)
- 5.7" VGA / 12.1" SVGA / 15" XGA TFT LED backlight LCDs
- -20 ~ 60° C wide operating temperature
- Compact design with die-cast Al alloy front bezel
- Fanless cooling system
- NEMA4/IP65 compliant front panel
- Supports Microsoft® Windows WES7/XP/XPe/CE
- Dual Gigabit Ethernet supported
- Isolation Protection for Serial ports
- Energy Star approval



Introduction

With a high quality TPC product line, TPC extends its Touch Panel Computer family with Intel® Atom™ platform for 5.7", 12.1" & 15". They are designed with Intel® Atom™ eMenlow XL processor as its core. The Intel Atom has low power consumption and wide operating temperature. This system is fanless, slim design and the front bezel is die-cast Al alloy material. This product also provides a -20~60° C wide operating temperature solution and complete isolation protection for its serial ports. TPC series are durable and reliable platform.

Specifications

General

■ **BIOS** Award® 4 MB

Certifications
 BSMI, CCC, CE, FCC Class A, UL

• Cooling System Fanless design

■ **Dimensions (W x H x D)** TPC-651H: 195 x 148 x 58 mm (7.68" x 5.83" x 2.28")

1251H: 311 x 237 x 54 mm (12.24" x 9.33" x 2.12") 1551H: 383 x 307 x 58.1 mm (15.08" x 12.09" x 2.29")

• **Enclosure** TPC-651H: ABS and ABS + PC

1251H /1551H: Front bezel: Die-cast Aluminum alloy

Back housing: SECC

Mounting Desktop, Wall or Panel Mount
 OS Support Windows XP/WES7/XPe/CE/Linux
 Power Consumption 17 W / 35 W / 40 W (typical)

Power Input
 Watchdog Timer
 18 ~ 32 V_{DC}
 1 ~ 255 sec (system)

• **Weight (Net)** 1.43 kg (3.15 lb) / 2.5 kg (5.51 lb) / 3 kg (5.51 lb)

System Hardware

■ CPU Intel Atom 1.33 GHz with 512KB cache

• Chipset eMenlow XL + Poulsbo

Memory
 1GB SO-DIMM DDR2 667 SDRAM

Up to 2GB (One channel)

■ LAN 10/100/1000Base-T x 2
■ Storage CompactFlash® slot x 1
■ I/O RS-232 x 1 (with isolation)
RS-422/485 x 1 (with isolation)

USB 2.0 x 2 (Host)

LCD Display

Display Type
 VGA / SVGA / XGA TFT LED LCD

■ **Display Size** 5.7" / 12.1" / 15"

Max. Resolution
 640 x 480 / 800 x 600 / 1024 x 768

Max. Colors 262 K
 Luminance cd/m² 700 / 450 / 350
 Viewing Angle (H/V°) 160/140
 Backlight Life 50,000 hrs

Contrast Ratio 800:1 / 700:1 / 700:1

Touchscreen

• **Lifespan** 10 million touches at single point

Light Transmission Above 75%Resolution Linearity


• **Type** 5-wire, analog resistive

Environment

• **Humidity** $10 \sim 95\%$ RH @ 40° C, non-condensing

Ingress Protection
 Operating Temperature
 Storage Temperature
 Vibration Protection
 Front panel: NEMA4, IP65
 -20 ~ 60° C (-4 ~ 140° F)
 -30 ~ 80° C (-22 ~ 176° F)
 2 Grms (5 ~ 500 Hz)
 (Operating, random vibration)

TPC-651H/ 1251H/ 1551H



Ordering Information

■ TPC-651H-Z2AE 5.7" VGA Touch Panel PC, Atom 1.33GHz, 1GB TPC-1251H-Z2AE 12.1" SVGA Touch Panel PC, Atom 1.33GHz, 1GB TPC-1551H-Z2AE 15" XGA Touch Panel PC, Atom 1.33GHz, 1GB

Accessories

■ TPC-1570H-SMKE TPC-1551H Desktop Stand TPC-1251H Desktop Stand ■ TPC-1250H-SMKE ■ TPC-1570H-WMKE TPC-1551H Wallmount Kit TPC-1250H-WMKE TPC-1251H Wallmount Kit

■ TPC-651H-EHKE TPC-651H/1251H/1551H Extension HDD Kit


PWR-247-AE 24 V 50 W AC-DC Power Adapter

1702002600 Power Cord 3P UL/CSA(USA) 125V 10A 1.83M


* Stand and Wall mount kits not compatible with HDD extension kit.

Rear View

TPC-1251H/1551H



TPC-651H



a. COM (RS-232, RS-422/485)

b. USB 2.0

c. LAN (10/100/1000)

d. Power Receptor