

**AMPROBE®**

Beha-Amprobe GT-400-D Portable Appliance Tester

Built tough to test the safety and integrity of electrical devices.

Designed for the commercial electrician or facilities maintenance person to carry out a wide variety of safety measurements of electrical appliances, the GT-400-D is highly portable and easy to use.

Ensure safety, functionality and compliance of regulatory standards.

- Intuitive and simple to use – no training required
- Small, portable and light weight
- Fast answers - Instantly measures safety and operation of electrical appliances
- Manufactured in Germany with high quality construction for years of service
- Insulation resistance measurements up to 500V
- Tests appliances for safety in accordance with DIN VDE 0701-0702 (BGV A3) EN 61010 Safety Standards

GT-400-D Specifications

FEATURES	GT-400-D
Advantages	Portability and simplicity
Target customer	Commercial Electrician, Facilities Managers, Service and Maintenance
Earth ground resistance	■
Insulation resistance (500V)	0.100 - 9.999 MΩ, 10.00 - 20.00 MΩ ± (5% + 2 digits)
Substitute leakage current	0.100 - 9.999 mA, 10.00 - 20.00 mA ± (5% + 2 digits)
Protective conductor current	0.1000 to 2000 Ω ± (5% + 2 digits)
Direct testing of IEC cables without adapter device information	■

Model	Product Number	EAN
GT-400-D	4380998	00 95969 68242 8

Amprobe® Europe

In den Engematten 14,
79286 Glottertal, Germany
Tel.: +49 (0) 7684 8009 - 0

For complete information on Amprobe test tools, visit www.Amprobe.eu



