




# Shielded Power Inductors - SER1590



Designed for high current, low voltage power supply applications, the SER1590 Series offers unmatched electrical performance in an extremely robust package.

With their heavy flat wire windings, these inductors have exceptionally low DC resistance and offer saturation current ratings up to 50 Amps. Winding to core isolation is 300 Vrms.

**SPICE models** ON OUR WEB SITE

Part number <sup>1</sup>	Inductance <sup>2</sup> ±20% (µH)	DCR (mOhms) <sup>3</sup>		SRF typ <sup>4</sup> (MHz)	Isat (A) <sup>5</sup>			Irms <sup>6</sup> (A)
		typ	max		10% drop	20% drop	30% drop	
SER1590-301ML_	0.30	0.66	0.72	260	53	56	57	32
SER1590-501ML_	0.50	0.87	0.94	202	39	42	44	27
SER1590-601ML_	0.60	0.87	0.94	182	33	35	36	27
SER1590-681ML_	0.68	0.87	0.94	160	30	32	33	27
SER1590-801ML_	0.80	0.87	0.94	123	25	26	27	27
SER1590-901ML_	0.90	1.08	1.15	160	27	28	29	22
SER1590-102ML_	1.0	0.87	0.94	115	20	22	23	27
SER1590-122ML_	1.2	1.08	1.15	90	20	22	23	22
SER1590-152ML_	1.5	1.08	1.15	73	17	18	19	22

1. When ordering, please specify **termination** and **packaging** codes:

SER1590-102MLD

**Termination: L** = RoHS compliant tin-silver over copper.

**Special order: T** = RoHS tin-silver-copper (95.5/4/0.5) or **S** = non-RoHS tin-lead (63/37).

**Packaging: D** = 13" machine-ready reel. EIA-481 embossed plastic tape (250 parts per full reel).

**B** = Less than full reel. In tape, but not machine ready. To have a leader and trailer added (\$25 charge), use code letter D instead.

- Inductance measured at 100 kHz, 0.1 Vrms, 0 Adc on an Agilent/HP 4284A LCR meter or equivalent.
- DCR measured on a Keithley 580 micro-ohmmeter.
- SRF measured using an Agilent/HP 8753D network analyzer and Coilcraft SMD-D test fixture.
- DC current at which the inductance drops the specified amount from its value without current.
- Current that causes a 40°C temperature rise from 25°C ambient. When Irms is greater than Isat, Isat is the more critical specification, and Irms is shown in gray type. See Temperature Rise vs Current curve on next page.
- Electrical specifications at 25°C.

Refer to Doc 362 "Soldering Surface Mount Components" before soldering

**Designer's Kit C366** contains 4 of each value

**Core material** Ferrite

**Core and winding loss** See [www.coilcraft.com/coreloss](http://www.coilcraft.com/coreloss)

**Terminations** RoHS tin silver (96.5/3.5) over copper. Other terminations available at additional cost.

**Weight** 4.14 – 5.2 g

**Ambient temperature** –40°C to +85°C with Irms current, +85°C to +125°C with derated current

**Storage temperature** Component: –40°C to +125°C.  
Tape and reel packaging: –40°C to +80°C

**Resistance to soldering heat** Max three 40 second reflows at +260°C, parts cooled to room temperature between cycles

**Moisture Sensitivity Level (MSL)** 1 (unlimited floor life at <30°C / 85% relative humidity)

**Failures in Time (FIT) / Mean Time Between Failures (MTBF)**

38 per billion hours / 26,315,789 hours, calculated per Telcordia SR-332

**Packaging** 250 per 13" reel; Plastic tape: 32 mm wide, 0.4 mm thick, 32 mm pocket spacing, 10.4 mm pocket depth

**PCB washing** Only pure water or alcohol recommended



**US** +1-847-639-6400 sales@coilcraft.com  
**UK** +44-1236-730595 sales@coilcraft-europe.com  
**Taiwan** +886-2-2264 3646 sales@coilcraft.com.tw  
**China** +86-21-6218 8074 sales@coilcraft.com.cn  
**Singapore** +65-6484 8412 sales@coilcraft.com.sg

Document 289-1 Revised 04/23/10


© Coilcraft Inc. 2011

This product may not be used in medical or high risk applications without prior Coilcraft approval. Specifications subject to change without notice. Please check our web site for latest information.




# Shielded Power Inductors – SER1590 Series



## L vs Frequency



## L vs Current




## Temperature Rise vs Current





**Caution:**  
Terminal 3 is provided for mounting stability only. This terminal is connected to the winding of the inductor and must not be connected to ground or any circuitry.

## Recommended Land Pattern



## Current Derating



A max	B max	C max	D	E	F	G	H	
0.62	0.64	0.40	0.10	0.23	0.09	0.260±0.006	0.45	
15,75	16,26	10,16	2,54	5,84	2,29	6,60±0,15	11,43	
I	J	K	L	M	N	O	P	Q
0.08	0.10	0.15	0.18	0.35	0.25	0.035	0.16	0.15
2,03	2,54	3,81	4,57	8,89	6,35	0,89	4,06	3,81

Dimensions are in  $\frac{\text{inches}}{\text{mm}}$



**US** +1-847-639-6400 sales@coilcraft.com  
**UK** +44-1236-730595 sales@coilcraft-europe.com  
**Taiwan** +886-2-2264 3646 sales@coilcraft.com.tw  
**China** +86-21-6218 8074 sales@coilcraft.com.cn  
**Singapore** +65-6484 8412 sales@coilcraft.com.sg

Document 289-2 Revised 04/23/10

© Coilcraft Inc. 2011

This product may not be used in medical or high risk applications without prior Coilcraft approval. Specifications subject to change without notice. Please check our web site for latest information.