



Male headers soldering technique

□ 0.635 mm, standard



art. no.	dim. [mm]			art. no.	dim. [mm]		
	A	B	C		A	B	C
SL 11 097...	9.70	3.00	3.90	SL 1 025 ...	11.20	2.60	5.80
SL 11 112 ...	11.20	3.00	5.40	SL 1 053 ...	13.90	5.80	5.30
SL 11 124 ...	12.40	3.00	6.60	SL 1 078 ...	16.40	5.80	7.80
SL 11 139 ...	13.90	3.00	8.10	SL 1 104 ...	19.00	5.80	10.40
SL 11 164 ...	16.40	3.00	10.60	SL 1 128 ...	21.40	5.80	12.80
SL 11 190 ...	19.00	3.00	13.20	SL 1 154 ...	24.00	5.80	15.40
SL 11 214 ...	21.40	3.00	15.60	SL 1 179 ...	26.50	5.80	17.90
SL 11 240 ...	24.00	3.00	18.20	SL 1 230 ...	31.60	5.80	23.00
SL 11 265 ...	26.50	3.00	20.70		-	-	-
SL 11 316 ...	31.60	3.00	25.80				



art. no.	dim. [mm]			art. no.	dim. [mm]		
	A	B	C		A	B	C
SL 22 097 ...	9.70	3.00	3.90	SL 2 025 ...	11.20	2.60	5.80
SL 22 112 ...	11.20	3.00	5.40	SL 2 053 ...	13.90	5.80	5.30
SL 22 124 ...	12.40	3.00	6.60	SL 2 078 ...	16.40	5.80	7.80
SL 22 139 ...	13.90	3.00	8.10	SL 2 104 ...	19.00	5.80	10.40
SL 22 164 ...	16.40	3.00	10.60	SL 2 128 ...	21.40	5.80	12.80
SL 22 190 ...	19.00	3.00	13.20	SL 2 154 ...	24.00	5.80	15.40
SL 22 214 ...	21.40	3.00	15.60	SL 2 179 ...	26.50	5.80	17.90
SL 22 240 ...	24.00	3.00	18.20	SL 2 230 ...	31.60	5.80	23.00
SL 22 265 ...	26.50	3.00	20.70		-	-	-
SL 22 316 ...	31.60	3.00	25.80				

please indicate: ... no. of contacts
 one row 1-36
 two rows 2-72

 ... surface
 S = selective gold-plated
 G = gold-plated
 Z = tin-plated

Every pin length is available on request.

- PC connector design DIL → H 2
- Female headers 2.54 solder → G 27
- Technical data → G 75 - 80
- Fem. head. 2.54 solder, put through → G 29
- Female headers 2.54 SMD → G 46 - 49
- Special male & female headers → G 19
- High-prec. fem. headers 2.54 sold. → G 31 - 34

G 8

A
B
C
D
E
F
G
H
I
K
L
M
N