



DWP1000 Water Pump

Water Pump Specification:

Inlet & Output Diameter (Inlet Filter):	75mm
Pump Lift:	28m
Suction Height:	8m
Flow Rate:	1000L/min
Max. Solids:	8mm
Weight:	10.7kg
Product Dimensions (H x D x W):	395 x 345 x 300mm
Packaging Dimensions (H x D x W):	320 x 350 x 425mm

Engine Unit Specification:

Engine Brand:	Evolution
Engine Type:	4-Stroke (Single Cylinder)
Engine Displacement:	200cc
Engine Power:	6.5hp
Max Speed:	3150rpm
Fuel Tank Capacity:	3.1L
Starter:	Recoil
Oil Warning:	Oil Low Sensor
Weight:	29.1kg
Wheels (Supplied Detached):	8" Rubber Tyres
Brake:	Manual Foot Brake
Frame:	1" Steel Tubular Frame
Sound Power Level:	98db(A)
Handle:	Fold-away