



Prokit's Industries CO., LTD.

5F, No.7, Lane 130,
Ming-Chung Rd., Hsin-Tien Dist,
New Taipei City, Taiwan, R.O.C. Post code: 23114
Tel: 886-2-2218-3233; Fax: 886-2-2218-2722

<http://www.prokits.com.tw> Email: sales-c@mail.prokits.com.tw

PRODUCT SPECIFICATION

Item #	Farnell UK Item #	Description	MOQ	Carton Quantity	N.W	G.W	CUFT
NT-6540	N/A	Laser Distance Measurer(40M)	40 PCS	40 PCS	7.25 kgs	8.1 kgs	1.55



*** Picture for reference only. All specifications are subject to change by supplier. ***

Spec.

Display	LCD display (2 lines)
Backlight	Y
Measuring range	0.1-40M
Accuracy	±2mm
Unit selection	m/ft/in/ft+in
Continuous measurement	Y
MAX/MIN measurement	N
Area calculations	Y
Volume calculations	N

memory	10 records
Buzzer indication	Y
Pythagorean 1	Y
Pythagorean 2	N
Add/Subtraction	N
Auto laser off	After 20 second
Auto power off	After 3 min
Laser Class	Class II
Laser type	650 nm, < 1mW
Certificate	IP54
Operating Temperature	0°C to +50°C(32°F to 104°F)
Storage Temperature	-10 °C+60°C (14°F to 140°F)
Battery type	Type AAA 2 x 1.5V
Battery life	Up to 5000 time (only for reference)
Dimension	100x43x28mm
Weight(not include batteries)	60g

Individual packing: Double Blister Card

~ THE END ~