

SAFETY DATA SHEET BBQ SPRAY PAINT (SILVER & BLACK)

SECTION 1: IDENTIFICATION OF THE SUBSTANCE/MIXTURE AND OF THE COMPANY/UNDERTAKING

1.1. Product identifier

Product name BBQ SPRAY PAINT (SILVER & BLACK)
Product No. XUK1001/1009

1.2. Relevant identified uses of the substance or mixture and uses advised against

Identified uses Paint aerosol

1.3. Details of the supplier of the safety data sheet

Supplier James Briggs Limited
Salmon Fields,
Royton, Oldham,
Lancashire,
OL2 6HZ,
England
0161 627 0101
sds@jamesbriggs.co.uk

Manufacturer James Briggs Limited
Salmon Fields,
Royton, Oldham,
Lancashire,
OL2 6HZ,
England
0161 627 0101
sds@jamesbriggs.co.uk

1.4. Emergency telephone number

National Emergency Telephone Number
0044 (0) 161 627 0101

SECTION 2: HAZARDS IDENTIFICATION

2.1. Classification of the substance or mixture

Classification (1999/45/EEC) Xi;R36. F+;R12. R66, R67.

Human health

Vapours/aerosol spray may irritate the respiratory system. May irritate eyes and skin. In high concentrations, vapours and aerosol mists have a narcotic effect and may cause headache, fatigue, dizziness and nausea.

Environment

The product is not expected to be hazardous to the environment.

Physical and Chemical Hazards

The product is extremely flammable, and explosive vapour/air mixtures may be formed even at normal room temperatures. Aerosol containers can explode when heated, due to excessive pressure build-up. When sprayed on a naked flame or any incandescent material the aerosol vapours can be ignited.

2.2. Label elements

Labelling



Irritant



Extremely flammable

Risk Phrases

R12	Extremely flammable.
R36	Irritating to eyes.
R66	Repeated exposure may cause skin dryness or cracking.
R67	Vapours may cause drowsiness and dizziness.

Safety Phrases

S2	Keep out of the reach of children.
----	------------------------------------

BBQ SPRAY PAINT (SILVER & BLACK)

S16	Keep away from sources of ignition - No smoking.
S23	Do not breathe vapour/spray.
S26	In case of contact with eyes, rinse immediately with plenty of water and seek medical advice.
S51	Use only in well-ventilated areas.
S37	Wear suitable gloves.

2.3. Other hazards

Not Classified as PBT/vPvB by current EU criteria.

SECTION 3: COMPOSITION/INFORMATION ON INGREDIENTS

3.2. Mixtures

ACETONE	30-60%
CAS-No.: 67-64-1	EC No.: 200-662-2
Classification (EC 1272/2008) Flam. Liq. 2 - H225 EUH066 Eye Irrit. 2 - H319 STOT SE 3 - H336	Classification (67/548/EEC) F;R11 Xi;R36 R66 R67
BUTANE	5-10%
CAS-No.: 106-97-8	EC No.: 203-448-7
Classification (EC 1272/2008) Flam. Gas 1 - H220	Classification (67/548/EEC) F+;R12
ETHYLBENZENE	< 1%
CAS-No.: 100-41-4	EC No.: 202-849-4
Classification (EC 1272/2008) Flam. Liq. 2 - H225 Acute Tox. 4 - H332	Classification (67/548/EEC) F;R11 Xn;R20
ISOBUTANE	1-5%
CAS-No.: 75-28-5	EC No.: 200-857-2
Classification (EC 1272/2008) Flam. Gas 1 - H220	Classification (67/548/EEC) F+;R12
ISO-BUTANOL	< 1%
CAS-No.: 78-83-1	EC No.: 201-148-0
Classification (EC 1272/2008) Flam. Liq. 3 - H226 Skin Irrit. 2 - H315 Eye Dam. 1 - H318 STOT SE 3 - H335 STOT SE 3 - H336	Classification (67/548/EEC) R10 Xi;R37/38,R41 R67

BBQ SPRAY PAINT (SILVER & BLACK)

PROPANE	10-30%
CAS-No.: 74-98-6	EC No.: 200-827-9
Classification (EC 1272/2008) Flam. Gas 1 - H220	Classification (67/548/EEC) F+;R12
XYLENE	10-30%
CAS-No.: 1330-20-7	EC No.: 215-535-7
Classification (EC 1272/2008) Flam. Liq. 3 - H226 Acute Tox. 4 - H312 Acute Tox. 4 - H332 Skin Irrit. 2 - H315 Asp. Tox. 1 - H304	Classification (67/548/EEC) R10 Xn;R20/21 Xi;R38

The Full Text for all R-Phrases and Hazard Statements are Displayed in Section 16.

Composition Comments

The data shown are in accordance with the latest EC Directives.

SECTION 4: FIRST AID MEASURES

4.1. Description of first aid measures

General information

Move the exposed person to fresh air at once. Get medical attention if any discomfort continues.

Inhalation

Move the exposed person to fresh air at once. When breathing is difficult, properly trained personnel may assist affected person by administering oxygen. Keep the affected person warm and at rest. Get prompt medical attention.

Ingestion

DO NOT INDUCE VOMITING! Rinse mouth thoroughly with water and give large amounts of milk or water to people not unconscious. Get medical attention if any discomfort continues.

Skin contact

Wash the skin immediately with soap and water. Get medical attention if any discomfort continues.

Eye contact

Make sure to remove any contact lenses from the eyes before rinsing. Promptly wash eyes with plenty of water while lifting the eye lids. Continue to rinse for at least 15 minutes. Get medical attention if any discomfort continues.

4.2. Most important symptoms and effects, both acute and delayed

General information

The severity of the symptoms described will vary dependant of the concentration and the length of exposure.

Inhalation.

In high concentrations, vapours are anaesthetic and may cause headache, fatigue, dizziness and central nervous system effects.

Ingestion

Due to the physical nature of this material it is unlikely that swallowing will occur.

Skin contact

Prolonged skin contact may cause redness and irritation.

Eye contact

Irritating and may cause redness and pain.

4.3. Indication of any immediate medical attention and special treatment needed

No specific first aid measures noted.

SECTION 5: FIREFIGHTING MEASURES

5.1. Extinguishing media

Extinguishing media

Use: Powder. Dry chemicals, sand, dolomite etc. Water spray, fog or mist.

5.2. Special hazards arising from the substance or mixture

BBQ SPRAY PAINT (SILVER & BLACK)

Hazardous combustion products

When heated, vapours/gases hazardous to health may be formed.

Unusual Fire & Explosion Hazards

Aerosol cans may explode in a fire.

Specific hazards

Aerosol containers can explode when heated, due to excessive pressure build-up.

5.3. Advice for firefighters

Special Fire Fighting Procedures

Containers close to fire should be removed or cooled with water. Use water to keep fire exposed containers cool and disperse vapours.

Protective equipment for fire-fighters

Wear full protective clothing.

SECTION 6: ACCIDENTAL RELEASE MEASURES

6.1. Personal precautions, protective equipment and emergency procedures

Follow precautions for safe handling described in this safety data sheet. Wear protective gloves. Do not smoke, use open fire or other sources of ignition. Avoid inhalation of vapours and aerosol spray. Avoid contact with skin and eyes.

6.2. Environmental precautions

Not relevant considering the small amounts used.

6.3. Methods and material for containment and cleaning up

Wear necessary protective equipment. Extinguish all ignition sources. Avoid sparks, flames, heat and smoking. Ventilate. Let evaporate. Keep out of confined spaces because of explosion risk. If leakage cannot be stopped, evacuate area.

6.4. Reference to other sections

For personal protection, see section 8. For waste disposal, see section 13.

SECTION 7: HANDLING AND STORAGE

7.1. Precautions for safe handling

Keep away from heat, sparks and open flame. Avoid spilling, skin and eye contact. Ventilate well, avoid breathing vapours. Use approved respirator if air contamination is above accepted level.

7.2. Conditions for safe storage, including any incompatibilities

Aerosol cans: Must not be exposed to direct sunlight or temperatures above 50°C.

Storage Class

Store in a dry, well ventilated, moisture free area.

7.3. Specific end use(s)

Decorative paint coating for a range of substrates

Usage Description

Aerosolised paint spray

SECTION 8: EXPOSURE CONTROLS/PERSONAL PROTECTION

8.1. Control parameters

Name	STD	TWA - 8 Hrs		STEL - 15 Min		Notes
ACETONE				500 ppm	1210 mg/m ³	
BUTANE	WEL	600 ppm	1450 mg/m ³	750 ppm	1810 mg/m ³	
ETHYLBENZENE	WEL	100 ppm(Sk)	441 mg/m ³ (Sk)	125 ppm(Sk)	552 mg/m ³ (Sk)	
ISOBUTANE	WEL	800 ppm		800 ppm		
ISO-BUTANOL	WEL	50 ppm	154 mg/m ³	75 ppm	231 mg/m ³	
PROPANE		Asphyxiating	Asphyxiating.	Asphyxiating	Asphyxiating.	
XYLENE	WEL	50 ppm(Sk)	220 mg/m ³ (Sk)	100 ppm(Sk)	441 mg/m ³ (Sk)	

WEL = Workplace Exposure Limit.

Ingredient Comments

WEL = Workplace Exposure Limits

BBQ SPRAY PAINT (SILVER & BLACK)

8.2. Exposure controls

Protective equipment



Process conditions

No specific process measures

Engineering measures

Provide adequate general and local exhaust ventilation.

Respiratory equipment

No specific recommendation made, but respiratory protection must be used if the general level exceeds the recommended occupational exposure limit. Use chemical cartridge protection with appropriate cartridge.

Hand protection

Use protective gloves.

Eye protection

Use approved safety goggles or face shield.

Other Protection

Wear appropriate clothing to prevent any possibility of liquid contact and repeated or prolonged vapour contact.

Hygiene measures

DO NOT SMOKE IN WORK AREA! Wash hands at the end of each work shift and before eating, smoking and using the toilet. Promptly remove any clothing that becomes contaminated. When using do not eat, drink or smoke.

Personal protection

It is advisable to wear suitable eye protection (goggles)

Skin protection

Suitable gloves

Thermal hazards

No specific thermal hazards noted

Environmental Exposure Controls

Due to the method of dispense, the product is likely to have a minimal environmental impact.

SECTION 9: PHYSICAL AND CHEMICAL PROPERTIES

9.1. Information on basic physical and chemical properties

Appearance	Aerosol.
Colour	Black.
Odour	Ketonic. Characteristic of a solvent based paint product
Solubility	Insoluble in water
Initial boiling point and boiling range	
Technically not feasible.	The boiling point of the lowest boiling point material is minus 40 degrees Celcius (-40). This is the boiling point of the propellant (LPG - Liquefied Petroleum Gas).
Melting point (°C)	
Scientifically unjustified.	The resin binder in the paint film begins to soften at temperatures in excess of 80 degrees Celcius.
Relative density	Not relevant <1.000 Ambient Not applicable
Bulk Density	
Not relevant	Not applicable
Vapour density (air=1)	Not determined. >1 The vapours are heavier than air.
Vapour pressure	
Not determined.	Propellant vapour pressure 590 - 1760 KPa
Flash point	
Technically not feasible.	

BBQ SPRAY PAINT (SILVER & BLACK)

The flash point of the lowest flash point material is minus 104 degrees Celcius (-104). This is the flash point of the propellant (LPG - Liquefied Petroleum Gas).

Flammability Limit - Lower(%)	0.8
Flammability Limit - Upper(%)	13.0

9.2. Other information

Volatile Organic Compound (VOC)	Maximum 839 g/litre
---------------------------------	---------------------

Aerosol products which are used for vehicle refinishing are classed as Annex IIB subcategory (e). The maximum permitted VOC's are 840 g/l. The typical VOC content for this range of products is between 625 and 675 g/l. The VOC regulations do not apply to any other aerosol products except those which are used for vehicle refinishing.

SECTION 10: STABILITY AND REACTIVITY

10.1. Reactivity

The product may form explosive vapours/air mixtures even at normal room temperatures.

10.2. Chemical stability

Stable under normal temperature conditions and recommended use.

10.3. Possibility of hazardous reactions

Not available.

10.4. Conditions to avoid

Avoid heat, flames and other sources of ignition. Avoid contact with: Strong oxidising agents. Strong alkalis. Strong mineral acids. Avoid exposing aerosol containers to high temperatures or direct sunlight.

10.5. Incompatible materials

Materials To Avoid

Strong acids. Strong alkalis. Strong oxidising substances.

10.6. Hazardous decomposition products

Fire creates: Vapours/gases/fumes of: Carbon monoxide (CO). Carbon dioxide (CO2).

SECTION 11: TOXICOLOGICAL INFORMATION

11.1. Information on toxicological effects

Inhalation

May cause irritation to the respiratory system. Vapours may cause headache, fatigue, dizziness and nausea. Prolonged inhalation of high concentrations may damage respiratory system. Irritating to respiratory system.

Ingestion

May cause discomfort if swallowed. May cause stomach pain or vomiting. Gastrointestinal symptoms, including upset stomach.

Skin contact

Prolonged or repeated exposure may cause severe irritation. Acts as a defatting agent on skin. May cause cracking of skin, and eczema. May cause allergic contact eczema. May cause sensitisation by skin contact. Irritating to skin.

Eye contact

Irritating to eyes. May cause chemical eye burns.

Route of entry

Inhalation. Skin and/or eye contact. Ingestion.

SECTION 12: ECOLOGICAL INFORMATION

Ecotoxicity

Under normal use conditions, this material is unlikely to accumulate in sufficient quantities to present any aquatic toxicity hazard.

12.1. Toxicity

Data set not currently available.

12.2. Persistence and degradability

The majority of the constituents are readily degradable.

BBQ SPRAY PAINT (SILVER & BLACK)

12.3. Bioaccumulative potential

Bioaccumulative potential

No data available on bioaccumulation.

12.4. Mobility in soil

Mobility:

The product contains volatile organic compounds (VOC) which will evaporate easily from all surfaces.

12.5. Results of PBT and vPvB assessment

Not Classified as PBT/vPvB by current EU criteria.

12.6. Other adverse effects

Not known.

SECTION 13: DISPOSAL CONSIDERATIONS

13.1. Waste treatment methods

Empty containers must not be burned because of explosion hazard. Dispose of waste and residues in accordance with local authority requirements. Industrial and institutional users should dispose of aerosols through a registered waste disposal company.

SECTION 14: TRANSPORT INFORMATION

General For industrial and institutional users can transport these products as "Limited Quantities" (LQ). For the final stages of retail distribution within the UK (only), unpackaged LQ product may be transported without external packaging under the DfT road derogation 4. The user must confirm the condition of the derogation prior to road consignment.

14.1. UN number

UN No. (ADR/RID/ADN)	1950
UN No. (IMDG)	1950
UN No. (ICAO)	1950

14.2. UN proper shipping name

Proper Shipping Name AEROSOLS

14.3. Transport hazard class(es)

ADR/RID/ADN Class	2
ADR/RID/ADN Class	Class 2: Gases
ADR Label No.	2.1
IMDG Class	2.1
ICAO Class/Division	2.1
Transport Labels	



14.4. Packing group

ADR/RID/ADN Packing group	N/A
IMDG Packing group	N/A
ICAO Packing group	N/A

14.5. Environmental hazards

BBQ SPRAY PAINT (SILVER & BLACK)

Environmentally Hazardous Substance/Marine Pollutant
No.

14.6. Special precautions for user

EMS F-D, S-U
Tunnel Restriction Code (D)

14.7. Transport in bulk according to Annex II of MARPOL73/78 and the IBC Code

Not relevant

SECTION 15: REGULATORY INFORMATION

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

Uk Regulatory References

The Control of Substances Hazardous to Health Regulations 2002 (S.I 2002 No. 2677) with amendments.

Chemicals (Hazard Information & Packaging) Regulations.

Statutory Instruments

The Chemicals (Hazard Information and Packaging for Supply) Regulations 2002.

Control of Substances Hazardous to Health.

The Aerosol Dispensers Regulations 2009

Approved Code Of Practice

Classification and Labelling of Substances and Preparations Dangerous for Supply.

Guidance Notes

Workplace Exposure Limits EH40.

Introduction to Local Exhaust Ventilation HS(G)37.

CHIP for everyone HSG(108).

EU Legislation

Dangerous Preparations Directive 1999/45/EC.

Dangerous Substance Directive 67/548/EEC.

Regulation (EC) No 1272/2008 of the European Parliament and of the Council of 16 December 2008 on classification, labelling and packaging of substances and mixtures, amending and repealing Directives 67/548/EEC and 1999/45/EC, and amending Regulation (EC) No 1907/2006 with amendments.

The Aerosol Dispensers Directive 1975/324 EEC

15.2. Chemical Safety Assessment

No chemical safety assessment has been carried out.

SECTION 16: OTHER INFORMATION

Revision Date 05/12/2012

Revision 1

Supersedes date 15/01/2013

Safety Data Sheet Status Approved.

Date 05/12/2012

Signature A. Taylor

Risk Phrases In Full

R12 Extremely flammable.

R10 Flammable.

R20/21 Harmful by inhalation and in contact with skin.

R20 Harmful by inhalation.

R11 Highly flammable

R36 Irritating to eyes.

R37/38 Irritating to respiratory system and skin.

R38 Irritating to skin.

R66 Repeated exposure may cause skin dryness or cracking.

R41 Risk of serious damage to eyes.

R67 Vapours may cause drowsiness and dizziness.

BBQ SPRAY PAINT (SILVER & BLACK)

Hazard Statements In Full

EUH066	Repeated exposure may cause skin dryness or cracking.
H220	Extremely flammable gas.
H222	Extremely flammable aerosol.
H225	Highly flammable liquid and vapour.
H226	Flammable liquid and vapour.
H304	May be fatal if swallowed and enters airways.
H312	Harmful in contact with skin.
H315	Causes skin irritation.
H318	Causes serious eye damage.
H319	Causes serious eye irritation.
H332	Harmful if inhaled.
H335	May cause respiratory irritation.
H336	May cause drowsiness or dizziness.