

Rugged Classic VOM

MODEL 60

**28
Ranges!**

Applications

- Test electrical circuits

Features

- Diode overload protection and 2 fuse arrangement
- Mirrored scale to reduce parallax error
- Confidence Test to check batteries, fuses, leads and meter accuracy
- Decibel function for audio work
- 28 Ranges and Functions
- High Impact Orange Case
- AC/DC Voltage to 1000V
- DC Current to 1000mA
- Resistance to 10M Ω
- Decibel ranges from -20dBm to +52dBm
- Polarity Reversing Switch
- AC Voltage frequency response to 40KHz typical
- High impact case stands a 5 foot drop
- 3 year warranty

