

For more Information
please call

1-800-Belden1



General Description:

22 AWG stranded (19x34) tinned copper conductors, foam FEP Teflon® insulation, Duofoil® (100% coverage) plus a stranded tinned copper drain wire, FEP Teflon jacket.

Physical Characteristics (Overall)

Conductor

AWG:

# Pairs	AWG	Stranding	Conductor Material	Dia. (mm)
1	22	19x34	TC - Tinned Copper	0.7874

Total Number of Conductors: 2

Insulation

Insulation Material:

Insulation Trade Name	Insulation Material	Dia. (mm)
Teflon®	FFEP - Foam Fluorinated Ethylene Propylene	7.0612

Outer Shield

Outer Shield Material:

Outer Shield Trade Name	Type	Outer Shield Material	Coverage (%)
Duofoil®	Tape	Aluminum Foil-Polyester Tape-Aluminum Foil	100

Outer Shield Drain Wire AWG:

AWG	Stranding	Drain Wire Conductor Material
22	19x34	TC - Tinned Copper

Outer Jacket

Outer Jacket Material:

Outer Jacket Trade Name	Outer Jacket Material
Teflon®	FEP - Fluorinated Ethylene Propylene

Overall Cable

Overall Nominal Diameter: 7.798 mm

Pair

Pair Color Code Chart:

Number	Color
1	Black & Yellow

Pair Lay Length & Direction:

Lay Length (mm)	Twists (twist/m)	Direction
76.2	13.124	Left Hand Lay

Mechanical Characteristics (Overall)

Operating Temperature Range: -70°C To +200°C

Bulk Cable Weight: 72.475 Kg/Km

Max. Recommended Pulling Tension: 124.550 N

Min. Bend Radius/Minor Axis: 88.900 mm

Applicable Specifications and Agency Compliance (Overall)

Applicable Standards & Environmental Programs

CEC/C(UL) Specification:	CMP
EU Directive 2011/65/EU (ROHS II):	Yes
EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2002/95/EC (RoHS):	Yes
EU RoHS Compliance Date (mm/dd/yyyy):	04/01/2005
EU Directive 2002/96/EC (WEEE):	Yes
EU Directive 2003/11/EC (BFR):	Yes
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes

Flame Test

UL Flame Test:	NFPA 262
C(UL) Flame Test:	FT6

Plenum/Non-Plenum

Plenum (Y/N):	Yes
Non-Plenum Number:	9182

Electrical Characteristics (Overall)

Nom. Characteristic Impedance:

Impedance (Ohm)
150

Nom. Inductance:

Inductance (µH/m)
0.95149

Nom. Capacitance Conductor to Conductor:

Capacitance (pF/m)
28.8728

Nom. Capacitance Cond. to Other Conductor & Shield:

Capacitance (pF/m)
54.1365

Nominal Velocity of Propagation:

VP (%)
78

Nominal Delay:

Delay (ns/m)
4.2653

Nom. Conductor DC Resistance:

DCR @ 20°C (Ohm/km)
45.934

Nominal Outer Shield DC Resistance:

DCR @ 20°C (Ohm/km)
20.6703

Nom. Attenuation:

Freq. (MHz)	Attenuation (dB/100m)
1	1.3124
10	3.9372
50	8.8587
100	14.1083

200	20.3422
400	28.8728

Max. Operating Voltage - UL:

Voltage
300 V RMS (CMP)
150 V RMS (CL2P)

Notes (Overall)

Notes: Teflon® is a registered trademark of E. I. duPont de Nemours and Co. used under license by Belden, Inc. Other Maximum Continuous Currents: 2.9 Amps per conductor @ 25°C

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
89182 0085000	1,524 MT	115.667 KG	GRAY	C	2 #22 FFEP FS FEP
89182 010100	30 MT	2.903 KG	BLACK	C	2 #22 FFEP FS FEP
89182 0101000	305 MT	24.041 KG	BLACK	C	2 #22 FFEP FS FEP
89182 010500	152 MT	12.701 KG	BLACK	C	2 #22 FFEP FS FEP
89182 0105000	1,524 MT	115.667 KG	BLACK		2 #22 FFEP FS FEP
89182 0605000	1,524 MT	0.000 FT	CHROME		2 #22 FFEP FS FEP

Notes:

C = CRATE REEL PUT-UP.

Revision Number: 1 Revision Date: 04-17-2008

© 2013 Belden, Inc.
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.