
# SHIMPO

# Model DT-107AS Handheld Contact LED Digital Tachometer

## Instruction Manual



#### Features

The Shimpo DT-107AS is a battery operated, handheld, microprocessor-controlled contact type tachometer. It incorporates the latest micro-circuit technology and offers:

- Multi-mode capability -- measures RPM, FPM, YPM, mPM and other units without special accessories
- Large memory capacity
- · Wide speed range with automatic floating decimal point
- C-MOS single chip microprocessor for high reliability and low maintenance
- Rugged construction die-cast aluminum housing

### **Specifications**

MODEL	DT-107AS		
Display Range	0.10 to 25,000 rpm with floating decimal		
Accuracy	±0.06 rpm: 0.10 to 999.99 rpm		
医动脉性皮肤 医乳头	±0.6 rpm: 1,000.0 to 9,999.9 rpm		
	±0.006% of reading ±1 digit (or ±2rpm max.): 10,000 to 25,000 rpm		
Display	5 digit 10mm high LED		
Measuring Units	Revolutions: RPH, RPM Feet: FPH, FPM Miles: MPH		
	Yards: YPH, YPM Inches: IPM Meters: mPH, mPM		
	Length: m, cm, inches, feet, yards Total revolutions: REV		
Memory System	13 readings are stored in memory and retained for		
	5 minutes (last, max., min. and 10 extra measurements)		
Detection	Optical coupler, 60 pulses/rev		
System Control	Single chip C-MOS microprocessor		
Over Range Indicator	Flashing numerals		
Update Time	1 second (typical)		
Batteries Included	Size: 2 AA 1.5V		
<u> </u>	Life: Approx. 40 hrs		
Low Voltage Indicator	"B" display		
Operating Temperature	0° to 45°C		
Construction	Die-cast aluminum housing		
Weight	400g		
Dimensions	185mm x 60mm x 45.7mm		
Warranty	l year		
STANDARD ACCESSORIES	2 cone adapters, 1 funnel adapter, 3-1/2" extension shaft,		
<u> </u>	carrying case and 1 master wheel (12" cir.)		

### Range and Accuracy

MODEL

Using the 12" master wheel and proper mode selector switch the following industrial units of measurement are achieved:

MODEL	DT-107A			
R: REVOLUTIONS	SINGLE RANGE	ACCURACY	RESOLUTION	
Contact RPM (rev./min.)	0.10 - 999.99	± 0.06	0.01	
	1,000.0 - 9,999.9	± 0.6	0.1	
	10,000 - 25,000	±0.006% of reading ±1digit	1	
n .		(or ±2 rpm max.)		
Contact RPH (rev./hour)	6 - 99,999	±0.006% of reading ±1digit	1	
		(or ±6 rpm max.)		
REV (total revolution)	0.1 - 9,999.9	± 0.1	0.1	
	10,000 - 99,999	±1	1	
F: FEET	SINGLE RANGE	ACCURACY	RESOLUTION	
F/M (feet/min)	0.05 - 999.99	± 0.06	0.01	
	1,000.0 - 9,999.9	±0.6	0.1	
# 12 1. *** ** 12 14	10,000 - 12,500	±1	1	
F/H (feet/hour)	3 - 99,999	±0.006% of reading ±1digit	1	
		(or ±6 FPH max.)	_	
FT (length)	0.01 - 999.99	(11111111111111111111111111111111111111	0.01	
	1,000.0 - 9,999.9	<b>\</b>	0.1	
	10,000 - 99,999	1	1	
Y: YARDS	SINGLERANGE	ACCURACY	RESOLUTION	
Y/M (yards/min.)	0.02 - 999.99	±0.06	0.01	
	1,000.0 - 4,167.0	±0,3	0.1	
Y/H (yards/hour)	1.0 - 9,999.9	±0.6	0.1	
	10,000 - 99,999	±0.006% of reading ±1digit	1	
	,	(or ±6 YPH max.)	· ·	
YRd (length)	0.005 - 99.995	(11 11 11 11 11 11 11 11 11 11 11 11 11	0.005	
	100.00 - 999.99		0.01	
india 50 be espe	1,000.0 - 9,999.9		0.1	
	10,000 - 99,999		1	
I: INCHES	SINGLE RANGE	ACCURACY	RESOLUTION	
I/M (inches/min.)	0.6 - 9,999.9	±0.6	0.1	
	10,000 - 99,999	±0.006% of reading ±1digit	1	
		(or ±6 IPM max.)		
IN (length)	0.1 - 9,999.9		0.1	
	10,000 - 99,999		1	
m: METERS	SINGLE RANGE	ACCURACY	RESOLUTION	
m/M (meters/min.)	0.02 - 999.99	± 0.06	0.01	
	1,000.0 - 3,810.0	±0.3	0.1	
m/H (meters/hour)	0.9 - 9,999.9	±0.6	1.0	
	10,000 - 99,999	±0.006% of reading ±1digit	1	
		(or ±6 mPH max.)		
m (length)	0.005 - 99.995	,	0.005	
	100.00 - 999.99		0.01	
	1,000.0 - 9,999.9		0.1	
	10,000 - 99,999		1	
cm (length)	0.5 - 9,999.5		0.5	
	10,000 - 99,999		1	
M: MILES	SINGLE RANGE	ACCURACY	RESOLUTION	
M/H (miles/hour)	0.0006 - 9.9999	± 0.0006	0.0001	
	10.000 - 99.999	± 0.006	0.001	
	100.00 - 142.05	± 0.01	0.01	
	10000 ITENS	20.01	5.01	

**NOTE:** When using master wheel, accuracy can be affected a much as 0.3% of reading.

**CAUTION:** Although tachometer alone is able to achieve abov ranges, the master wheel has a maximum speed limitation o 3,000 m/M (for safety reasons).




## Surface Speed Metric Conversion

Conversions such as YPM to mPM or mPM to YPM may be obtained from the memory only by switching from one mode to another.

### Operating Procedure


1. Place adapter or wheel on shaft (as shown).

CAUTION: Do not attach master speed wheel on extension shaft. The wheel may slip off during measurement.





2. Turn selector switch to desired unit.



 After attaching proper ada with rotating object or mo measured. Apply only end blinking red dot appears on when shaft is turning.






- Press and hold the on-off switch. Display will update approximately every second.
- 5. Observe speed for as long as it is desired.
- On-off switch must be released prior to removal of tachometer from rotating object if last reading must be captured.
- 7. After release of power switch, the last reading will be displayed for approximately 10 seconds. Readings will be retained in memory for 5 minutes and can be extended any number of additional 5 minute periods by pressing the memory switch.

## Memory Recall

#### **A.AUTOMATICMEMORY**

The following are automatically stored in memory for 5 minutes following release of the power switch:

- · Last reading
- · Maximum reading
- Minimum reading



These readings will be displayed in the following order when the memory switch is pressed:

- · Last reading
- · Maximum reading
- · Minimum reading

To fill all three memory spaces, unit must operate for about 5 seconds. If any of the above memory readings are missing, unit must operate a few seconds longer.

#### **B.MEMORYSELECTION**

The DT-107AS has the capability of storing 10 extra readings in its memory. These readings can be obtained from the same machine or many machines (up to 10) by pressing the memory switch momentarily as the reading you wish stored appears on the display. An "M" will appear on the display briefly, and that reading will be stored in memory. Up to 10 readings can be stored.

NOTE: All memory data will be erased if automatic shut-off has occurred. To recall a specific reading, press the memory switch until the desired reading shows up on the display alternating with its position within the memory. To erase all data from the memory, press the memory switch for at least 5 seconds until display shows CCCCC. If you hold the memory switch, the display will alternate between CCCCC and 0.00. If the memory switch is released then the display will default to 0.00.

## Battery Replacement

Low battery voltage is indicated by a "B" on the display. Remove end cover by using a coin or appropriate screwdriver and replace both batteries. Please note polarity.



