

Industrial Ethernet Switch - FL SWITCH SFNT 8TX - 2891005

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)




Wide-temperature Ethernet switch, 8 TP RJ45 ports, automatic detection of data transmission speed of 10/100 Mbps (RJ45), autocrossing function, reads QoS priority messages, accepts security frames

Why buy this product

- Auto negotiation and autocrossing detection simplifies installation and setup
- Alarm contact for power supply and link status diagnostics
- Local diagnostic indicators with LEDs
- The switch also offers cable locking and port blocking
- QoS-prioritized (Quality of Service) messages
- Wide operating temperature range (-40°C ... +75°C)
- RJ45 ports support a transmission speed of 10/100 Mbps; fiber optic ports support 100 Mbps



Key commercial data

Packing unit	1 pc
GTIN	 4 046356 457200
Weight per Piece (excluding packing)	633.9 g
Custom tariff number	85176200
Country of origin	Taiwan

Technical data

Dimensions

Width	50 mm
Height	130 mm
Depth	100 mm

Ambient conditions

Degree of protection	IP20
Ambient temperature (operation)	-40 °C ... 75 °C
Ambient temperature (storage/transport)	-40 °C ... 85 °C
Permissible humidity (operation)	5 % ... 95 % (non-condensing)

Industrial Ethernet Switch - FL SWITCH SFNT 8TX - 2891005

Technical data

Ambient conditions

Permissible humidity (storage/transport)	5 % ... 95 % (non-condensing)
Air pressure (operation)	62 kPa ... 108 kPa (up to 4160 m above mean sea level)
Air pressure (storage/transport)	62 kPa ... 108 kPa (up to 4160 m above mean sea level)
Noise immunity	EN 61000-6-2

Interfaces

Interface 1	Ethernet (RJ45)
No. of ports	8 (RJ45 ports)
Connection method	RJ45
Note on connection method	Auto negotiation and autocrossing
Transmission physics	Ethernet in RJ45 twisted pair
Transmission speed	10/100 MBit/s

Function

Basic functions	Unmanaged switch / autonegotiation, complies with IEEE 802.3, store and forward switching mode, includes QoS and alarm contact
Status and diagnostic indicators	LEDs: U _{S1} , U _{S2} (redundant voltage supply), link and activity per port, alarm (power and link down)

Network expansion parameters

Cascading depth	Network, linear, and star structure: any
Maximum conductor length ((twisted pair)	100 m

Supply voltage

Supply voltage	24 V DC (redundant)
Residual ripple	3.6 V _{PP} (within the permitted voltage range)
Supply voltage range	9 V DC ... 32 V DC
Typical current consumption	155 mA (@24 V DC)
Max. current consumption	490 mA (@9 V DC)

General

Mounting type	DIN rail
Type AX	Block design
Weight	460 g
Housing material	Aluminum
Noise emission	EN 61000-6-4

Classifications

eCl@ss

eCl@ss 4.0	27250501
eCl@ss 4.1	27250501
eCl@ss 5.0	19030117
eCl@ss 5.1	19030117

Industrial Ethernet Switch - FL SWITCH SFNT 8TX - 2891005

Classifications

eCl@ss

eCl@ss 6.0	19170106
eCl@ss 7.0	19170106
eCl@ss 8.0	19170106

ETIM

ETIM 2.0	EC000734
ETIM 3.0	EC000734
ETIM 4.0	EC000734
ETIM 5.0	EC000734

UNSPSC

UNSPSC 6.01	43172901
UNSPSC 7.0901	43201404
UNSPSC 11	43172015
UNSPSC 12.01	43201410
UNSPSC 13.2	43201410

Approvals

Approvals

Approvals

LR / GL / BV / DNV / ABS / NK / GL-SW / BSH / UL Listed / cUL Listed / GL / cULus Listed

Ex Approvals

UL Listed / cUL Listed / cULus Listed

Approvals submitted

Approval details

LR

GL

BV

DNV

Industrial Ethernet Switch - FL SWITCH SFNT 8TX - 2891005

Approvals

ABS

NK


GL-SW

BSH

UL Listed 

cUL Listed 

GL

cULus Listed 

Accessories

Accessories

Assembly adapter

Mounting plate - FL PA SFNT 5-8 - 2891012



Mounting plate for SFNT switches

End block

End clamp - E/NS 35 N - 0800886



End clamp, width: 9.5 mm, color: gray

Industrial Ethernet Switch - FL SWITCH SFNT 8TX - 2891005

Accessories

Patch cable

Patch cable - FL CAT5 PATCH 0,3 - 2832250



Patch cable, CAT5, assembled, 0.3 m

Patch cable - FL CAT5 PATCH 0,5 - 2832263



Patch cable, CAT5, assembled, 0.5 m

Patch cable - FL CAT5 PATCH 1,0 - 2832276



Patch cable, CAT5, assembled, 1.0 m

Patch cable - FL CAT5 PATCH 1,5 - 2832221



Patch cable, CAT5, assembled, 1.5 m

Patch cable - FL CAT5 PATCH 2,0 - 2832289



Patch cable, CAT5, assembled, 2.0 m

Industrial Ethernet Switch - FL SWITCH SFNT 8TX - 2891005

Accessories

Patch cable - FL CAT5 PATCH 3,0 - 2832292



Patch cable, CAT5, assembled, 3.0 m

Patch cable - FL CAT5 PATCH 5,0 - 2832580



Patch cable, CAT5, assembled, 5.0 m

Patch cable - FL CAT5 PATCH 7,5 - 2832616



Patch cable, CAT5, assembled, 7.5 m

Patch cable - FL CAT5 PATCH 10,0 - 2832629



Patch cable, CAT5, assembled, 10.0 m

Security element - FL SEC PAC 4TX - 2832865



Layer1 security elements for four RJ45 network connections for use with patch boxes and panels

Protective cap

Industrial Ethernet Switch - FL SWITCH SFNT 8TX - 2891005

Accessories

Dust protection - FL RJ45 PROTECT CAP - 2832991



Dust protection caps for RJ45 socket