


## Plug-in unit in kit form for CompacPCI and VME64x applications



Dimension 3 / 6 U

**Part no.: 20848-587**

### Features:

- Meets IEEE 1101.10 and IEC 60297-3-102 standards
- Codable to IEC 60297-3-103
- Front panel shielded, without offset
- Suitable for insertion and extraction forces up to 700 N (per pair)
- Designed for fitting of microswitches

Add to basket




### Technical information:

Description	Height	Width
Front assembly	3 U	6 HP

### Downloads:

User manual, plug-in unit IEEE ([Log in](#) Required)  
 User Manual ([Log in](#) Required)  
 User manual, coding IEEE ([Log in](#) Required)



Product illustrations are exemplary illustrations and can deviate from supplied products.

To gain access to the additional information you must [Log in](#).  
If you do not yet have a user name, you may [Register here](#).

### Delivery comprises: kit

Item	Qty	Description
	3 U	
	<8 HP	
1	1	Front panel (U profile), Al, front anodised, rear conductive
2	1	EMC sealing (textile), Core: foam, Sleeve: textile cladding, CuNi coated
3	1	Handle with integrated alignment pin for perforated strip and guide rails, lever: plastic, PC, black, RAL 9005 Key: Plastic, PC, light grey, RAL 7035
4	1	Board support, die-cast zinc
5	1	Raised Pozidrive countersunk screw M2.5 × 8, St, nickel-plated
6	1	Sleeve, PA, grey
7	2	Pozidrive collar screw, M2.5 × 12.3, St, nickel-plated
8	2	Panhead screw with Torx/slot, M2.5 × 6, St, zinc-plated, self-locking
9	2	Washer A2.7, DIN 125, St, nickel-plated
10	1	Panhead screw with Torx, M2.5 × 7, St, nickel-plated

**Accessories:**

Part no.	Description	
20817-606	Microswitch for handles, CompactPCI/VME64x application Qty: 10 pieces	Add to basket