



IEC Thermocouple Extension Leads with Miniature or Standard Connectors

About Labfacility

Formed in 1971, Labfacility specialize in the field of Temperature and Process Measurement.

We are the largest UK manufacturer of both temperature sensors and thermocouple connectors

Quality & Service


Quality and Service are key elements in the continued growth of Labfacility.

Technical support is always freely available from our experienced technical sales teams and the company has ISO9001 accreditation.

Contact Details

Email
sales@labfacility.com

Website
www.labfacility.com



Specifications

- Cable Construction:** Single pair 7/0.2
PVC insulated cable / wire
Laid flat, side by side & PVC sheathed
Tolerance class 2
Insulation rating -10 to 105°C
IEC colour coded
- Miniature Connectors:** Miniature connector with flat plug pins
Miniature socket with thermocouple contacts
Contacts are polarised to prevent incorrect connection
Max temperature 220°C
IEC colour coded
- Standard Connectors:** Standard connector with solid, round plug pins
Standard socket with thermocouple contacts
Suitable for industrial applications
contacts are polarised to prevent incorrect connection
Max temperature 220°C
IEC colour coded

LABFACILITY

TEMPERATURE & PROCESS TECHNOLOGY

About Labfacility

Formed in 1971, Labfacility specialize in the field of Temperature and Process Measurement.

We are the largest UK manufacturer of both temperature sensors and thermocouple connectors.

Quality & Service

Quality and Service are key elements in the continued growth of Labfacility.

Technical support is always freely available from our experienced technical sales teams and the company has ISO9001 accreditation.

Contact Details

Email
sales@labfacility.com

Website
www.labfacility.com

Type	Length	Connector	Description	Manufactures Part No.	Farnell Order Number
K	2 metre	Miniature	EXT-K-C1-2.0-MP-MS	XF-774-FAR	242-0256
K	5 metre	Miniature	EXT-K-C1-5.0-MP-MS	XF-775-FAR	242-0257
K	10 metre	Miniature	EXT-K-C1-10.0-MP-MS	XF-776-FAR	242-0258
K	2 metre	Standard	EXT-K-C1-2.0-SP-SS	XF-777-FAR	242-0261
K	5 metre	Standard	EXT-K-C1-5.0-SP-SS	XF-778-FAR	242-0262

