

6.01533.00

Basic 250-24 W

Compressor Basic 250-24 W



0153300S_51.EPS

- Powerful, robust compressor for simple, commercial use
- Oil-lubricated piston condenser
- For single phase alternating current
- Working pressure can be regulated according to application by means of pressure reducer with manometer
- Good cold start feature thanks to push button with safety valve
- Overload protection: protects the motor from overheating
- Rubberised, stable wheels for mobile use
- Testing not necessary before initial operation
- Additional manometer for displaying the tank pressure
- Rubber-coated handle for comfortable handling
- 10 years tank warranty against rusting

Comparative technical values

Suction rate	200 l/min
Filling capacity	110 l/min
Effective delivery volume (at 80% max.)	95 l/min
Maximum pressure	8 bar
Rated input power	1,5 kW
Maximum speed	2.850 /min
Tank capacity	24 l
Sound pressure level (LpA)	97 dB(A)
Dimensions	630 x 406 x 630 mm
Weight	27 kg
Cable length	1,5 m

Scope of delivery

Universal quick-action coupling, Pull handle with rubber-coating