# High Power Chip Resistors



#### SC3 Series


- 3 Watts in a 1 Watt size package\*
- Resistance range from 1R0 to 10K
- Tolerances to ±1%
- **AEC-Q200 Qualified**
- \* Rated Power @ 70°C




### **Electrical Data**

Characteristic	Value					
Power dissipation @70° C	3 Watts					
Resistance Range	1R0 to 10K					
LEV	50V					
Ambient temp range	-55 to +150°C					
Resistance tolerance	1, 2, 5%					
TCR	±100ppm/°C					
Termination	Leach-resistant solder-plated					
Terrimation	copper wrap-around					
Pad & trace area for maximum power rating	300mm²					

### Power Derating Curve



## Physical Data



TT electronics reserves the right to make changes in product specification without notice or liability. All information is subject to TT electronics' own data and is considered accurate at time of going to print.







### High Power Chip Resistors

SC3 Series



#### Construction

Resistive thick film material, overglaze and organic protection are screen printed on a 96% alumina substrate. The components are laser trimmed to achieve the required resistance tolerance.

#### **Terminations**

The wrap-around terminations have an electroplated nickel barrier and matte tin finish. This ensures excellent 'leach' resistance properties and solderability. Chips can withstand immersion in solder at 250°C for 90 seconds and are suitable for reflow or wave soldering mounting applications.


#### Marking

The body protection and marking are resistant to all normal industrial cleaning solvents suitable for printed circuits. Chips are packed and mounted with marking side up. The SC3 Chips are mounted with the actual resistor element mounted face down on its termination pads.


### Performance Data

AEC-Q200 Table 7		Method	М	-		
ref	Test	ivietnoa	IVI	Тур.		
3	High Temp. Exposure	MIL-STD-202 Method 108	ΔR%	0.5	0.2	
4	Temperature Cycling	JESD22 Method JA-104	ΔR%	0.25	0.1	
6	Moisture Resistance	MIL-STD-202 Method 106	∆R%	0.5	0.2	
7	Biased Humidity	MIL-STD-202 Method 103	∆R%	0.5	0.1	
8	Operational Life (Cyclic Load)	MIL-STD-202 Method 108	∆R%	1.5	0.5	
14	Vibration	MIL-STD-202 Method 204	∆R%	0.25	0.05	
15	Resistance to Soldering Heat	MIL-STD-202 Method 210	∆R%	0.25	0.05	
16	Thermal Shock	MIL-STD-202 Method 107	∆R%	0.5	0.2	
18	Solderability	J-STD-002	>95% coverage			
21	Board Flex	AEC-Q200-005	∆R%	0.25	0.05	
22	Terminal Strength	AEC-Q200-006	∆R%	0.25	0.05	
	Short Term Overload	6.25 x Pr for 2s	∆R%	0.5		
	Low Temperature Storage	-65°C for 100 hours	∆R%	0.5		
	Shelf Life Test	Room temp for 12 months	∆R%	0.1		
	Leach Resistance	Solder dip at 250°C				

### Temperature Rise vs Pad Area



### Pulse Power Rating



#### General Note

TT electronics reserves the right to make changes in product specification without notice or liability. All information is subject to TT electronics' own data and is considered accurate at time of going to print.




SC3 Series



### Packaging

SC3 Resistors are supplied taped and reeled as per IEC 286-3. The standard quantity per reel is 1800 parts.



Tape dimensions in mm														
	W	P1	P0	P2	D0	D1	E	F	A0	В0	K0	Т	T1	T2
	±0.3	±0.1	±0.1	±0.05	±0.1	±0.2	±0.1	±0.05	±0.1	±0.1	±0.1	±0.05	nom	±0.15
SC3	12	8	4	2	1.5	1.5	1.75	5.5	3.61	6.96	1.17	0.28	0.06	1.45

### Ordering Procedure

Specify type reference etc. as shown in this example of SC3 at 33  $\Omega$ 1% on a reel of 1800 pieces:

