

# HP531

# MOBILE HEADPHONES

Featuring Built-in Mic & Remote



## Perfect For On-The-Go Listening



### BUILT-IN REMOTE

Featuring essential functions including: Pause, skip to next song, activate voice control, answer & end incoming calls.



### RIGHT ANGLED CONNECTOR

Lies flat against your device rather than protruding upwards for added comfort when your device is being carried in your pocket.



### BUILT-IN MIC

Ensures an easy switch between music & incoming calls, carry out your phone calls without removing your headphones.



### ACOUSTIC TECHNOLOGY

Creates more depth and clarity to your music resulting in a high performance sound experience.



### AROUND EAR CUSHIONED PADS

Create a long lasting comfortable fit and ensure you hear less noise & more music.



### COMPLETE COMFORT

Lightweight design, padded & adjustable headframe creates a custom fit for everyone.

**The ultimate mobile experience headphones are a perfect choice for outstanding sound & a stylish look!**

Enjoy your music at home, work or when travelling from your favourite audio devices. Compatible with music players, mobile phones & tablet PC's for all round functionality.

### FEATURES

- Right angled connector lies flat against your device rather than protruding upwards for added comfort when your device is being carried in your pocket. Also prevents damage to the connector, accidental removal & provides less stress on the cable.
- Built-in microphone ensures an easy switch between music & incoming calls, carry out your phone calls without removing your headphones.



## COMPUTER GEAR

Essential PC Accessories

### HEADPHONE SPECIFICATIONS

- Drive unit: F40mm
- Impedance: 32Ω
- Frequency range: 20Hz-20,000Hz
- Sensitivity: 105dB S.PL at 1KHz
- Rated power: 100mW
- Cable length: 1.2m ±0.3cm
- Connector: 3.5mm 4 Pole TRRS Connector

### MICROPHONE SPECIFICATIONS

- Directivity: Omni Direction
- Sensitivity: -58dB±2dB
- Output impedance: Low
- Frequency response: 30Hz to 16,000Hz
- Operating voltage: 0.6V

### PACKAGING DETAILS

- Product box dimensions: 210 x 250 x 88 (W x H x D)
- Primary packaging material: Cardboard
- Primary packaging weight: 0.01410Kg
- Secondary packaging material: Plastic
- Secondary packaging weight: 0.0185Kg
- Product weight: 0.3174Kg
- Product and packaging weight: 0.35Kg
- Box qty: 14
- Carton size: 495 x 230 x 665mm
- Total carton weight: 5.6Kg
- Country of origin: China

PRODUCT CODE

24-1531

DETAILS

Black/red