

## Higher quality work with less effort



Utilize the power of a compound lever!

Drop-forged cutter heads are always tempered and the edges double hardened! This produces high durability and burr-free cuts. Ergonomic handle has standard plastic coating and an anti-slip protection.

Both parts are joined in such a manner that it provides additional leverage. You can do the same work quicker with much less effort. Less worker fatigue = improved production! Try it out!

Shape and straight cutting snips D29ASS-2 and D27A – ideal for continuous, straight and curved cuts.

Shape cutting snips D17SS – exceptionally robust for critical outline cuts.



# Compound leverage snips



- NEW: ERGO-handle for increased comfort – reduced hand fatigue!
- For short, straight and shaped cuts
- Edges with micro-serrations for slip-proof working
- Available in right- or left cutting versions



## Shape cutting snips

N <sup>o</sup>	< a >		< b >		kg	5	€
	mm	"	mm	"			
D29SS-2	260	10 1/4	40	1 9/16	0,48	5	42,00
D29SSL-2	260	10 1/4	40	1 9/16	0,48	5	42,00
D29SS-2-SB	260	10 1/4	40	1 9/16	0,48	5	43,00
D29SSL-2-SB	260	10 1/4	40	1 9/16	0,48	5	43,00



- NEW: ERGO-handle for increased comfort – reduced hand fatigue!
- For continuous, straight and shaped cuts
- Compact cutter head:  
High manoeuvrability for shape cutting
- Optimised leverage ratio:  
25 % less effort
- Optimised edge shape:  
No slipping even without serrations
- Available in right- or left cutting versions



## Shape and straight cutting snips

N <sup>o</sup>	< a >		< b >		kg	5	€
	mm	"	mm	"			
D29ASS-2	260	10 1/4	33	1 5/16	0,48	5	44,00
D29ASSL-2	260	10 1/4	33	1 5/16	0,48	5	44,00
D29ASS-2-SB	260	10 1/4	33	1 5/16	0,48	5	45,00
D29ASSL-2-SB	260	10 1/4	33	1 5/16	0,48	5	45,00



- NEW: ERGO-handle for increased comfort – reduced hand fatigue!
- For continuous, straight cuts
- Edges with micro-serrations for slip-proof working
- Available in right- or left cutting versions



## Straight cutting snips

N <sup>o</sup>	< a >		< b >		kg	5	€
	mm	"	mm	"			
D29BSS-2	260	10 1/4	33	1 5/16	0,51	5	47,70
D29BSSL-2	260	10 1/4	33	1 5/16	0,51	5	47,70
D29BSS-2-SB	260	10 1/4	33	1 5/16	0,52	5	48,70
D29BSSL-2-SB	260	10 1/4	33	1 5/16	0,52	5	48,70

