

KA03

ILLUSTRATED ASSEMBLY MANUAL HKA03IP'1

Motor & Power shield Arduino®



velleman®
projects



Power shield that can drive: relays, solenoids, DC and stepper motors

Features

- For use with Arduino Due™, Arduino Uno™, Arduino Mega™
- Based on L298P dual full bridge driver IC
- Outputs: up to 2 DC motors or 1 bipolar stepper motor
- Power supply: external power or power from Arduino board

Specifications

- Power supply: 7..46VDC
- Max current: 2A
- Dimensions: 68 x 53mm / 2.67 x 2.08"



Search product

Search Product

Navigation

- Home page
- Products
- Sales outlets
- Support
- Publications
- Jobs
- About us

News

NEW PINKO LED CUBE

CubeAnimator software available for download here!!!

Posted on 04-06-12

[Read more...](#)
velleman
projects

Velleman Projects
All about the Velman own
Developments: Kits, Modules,
Instruments and more automation

United Kingdom -
English (UK)
Change

Velleman Projects Newsletter

Are you an electronics enthusiastic or simply interested in our kits, modules, modules and instruments?

Subscribe to our Newsletter and receive every month the latest news, new products & updates on Velleman Projects.

You will receive an e-mail. Click on the link in that e-mail to confirm your subscription.

Email:



Do you want to unsubscribe? Click on the 'unsubscribe' link in the footer of the last received newsletter from Velleman Projects.

- velleman.eu
- lappower.eu
- panel.eu
- vellemanprojects.com
- velman.eu
- forum.velleman.eu

Advertisements

- MAC1
- MAC2
- MAC3
- MAC4
- MAC5
- MAC6
- MAC7
- MAC8
- MAC9
- MAC10
- MAC11
- MAC12
- MAC13
- MAC14
- MAC15
- MAC16
- MAC17
- MAC18
- MAC19
- MAC20
- MAC21
- MAC22
- MAC23
- MAC24
- MAC25
- MAC26
- MAC27
- MAC28
- MAC29
- MAC30
- MAC31
- MAC32
- MAC33
- MAC34
- MAC35
- MAC36
- MAC37
- MAC38
- MAC39
- MAC40
- MAC41
- MAC42
- MAC43
- MAC44
- MAC45
- MAC46
- MAC47
- MAC48
- MAC49
- MAC50
- MAC51
- MAC52
- MAC53
- MAC54
- MAC55
- MAC56
- MAC57
- MAC58
- MAC59
- MAC60
- MAC61
- MAC62
- MAC63
- MAC64
- MAC65
- MAC66
- MAC67
- MAC68
- MAC69
- MAC70
- MAC71
- MAC72
- MAC73
- MAC74
- MAC75
- MAC76
- MAC77
- MAC78
- MAC79
- MAC80
- MAC81
- MAC82
- MAC83
- MAC84
- MAC85
- MAC86
- MAC87
- MAC88
- MAC89
- MAC90
- MAC91
- MAC92
- MAC93
- MAC94
- MAC95
- MAC96
- MAC97
- MAC98
- MAC99
- MAC100

Subscribe
Newsletter



Subscribing our newsletter?, visit www.vellemanprojects.eu

velleman
projects

INSTRUMENTS
KIT
velleman

Support Forum (ENTIRE)
velleman-projects

login register

How personalized pages / View active topics

Support index

	Topics	Posts	Last post
General			
Forum rules, Regulations de Forum			
Feedback - A trier en premier lieu			
Forum Administration			
Velleman In-house Forum Discussions			
Feedback - Velleman Support			
Software			
Velleman Module Customization			
Support section for our new Velleman Home Automation System (Domotica)			
Feedback - Velleman Support			
Kits (Outstanding category - Projects & modules)			
General			
For other home, general kit and tools, new ideas			
Feedback - Velleman Support			
Audio & Hi-Fi projects			
All audio related projects, amplifiers, radio amplifiers			
Feedback - Velleman Support			
AC Related Projects			
All projects that are connected to the AC line interface cards			
Feedback - Velleman Support			
Microcontroller Programmer - Expanding Projects			
Here you can discuss PIC programming, assembly with			
Feedback - Velleman Support			
Tools and Chips			
All about our time related projects from regular clocks to programmable timers			
Feedback - Velleman Support			
Home Projects			
Household related projects, from light drivers to remote control			
Feedback - Velleman Support			

View
Forum



Participate our Velleman Projects Forum



Velleman N.V.
Legen Heirweg 33
9890 Gavere
(België)

assembly hints


1. Assembly (Skipping this can lead to troubles !)

Ok, so we have your attention. These hints will help you to make this project successful. Read them carefully.



1.1 Make sure you have the right tools:

- A good quality soldering iron (25-40W) with a small tip.
- Wipe it often on a wet sponge or cloth, to keep it clean; then apply solder to the tip, to give it a wet look. This is called 'thinning' and will protect the tip, and enables you to make good connections. When solder rolls off the tip, it needs cleaning.
- Thin raisin-core solder. Do not use any flux or grease.
- A diagonal cutter to trim excess wires. To avoid injury when cutting excess leads, hold the lead so they cannot fly towards the eyes.
- Needle nose pliers, for bending leads, or to hold components in place.
- Small blade and Phillips screwdrivers. A basic range is fine.



For some projects, a basic multi-meter is required, or might be handy



1.2 Assembly Hints :

- Make sure the skill level matches your experience, to avoid disappointments.
- Follow the instructions carefully. Read and understand the entire step before you perform each operation.
- Perform the assembly in the correct order as stated in this manual
- Position all parts on the PCB (Printed Circuit Board) as shown on the drawings.
- Values on the circuit diagram are subject to changes, the values in this assembly guide are correct*
- Use the check-boxes to mark your progress.
- Please read the included information on safety and customer service


* Typographical inaccuracies excluded. Always look for possible last minute manual updates, indicated as 'NOTE' on a separate leaflet.

1.3 Soldering Hints :

1. Mount the component against the PCB surface and carefully solder the leads




2. Make sure the solder joints are cone-shaped and shiny



3. Trim excess leads as close as possible to the solder joint






REMOVE THEM FROM THE TAPE ONE AT A TIME !

Included in
this kit



2. RESISTOR




COLOUR	COLOUR NAME	1ST DIGIT/ STRIPE	2ND DIGIT/ STRIPE	3RD DIGIT/ STRIPE	MULTIPLIER STRIPE	TOL- 4TH
	BLACK	0	0	0	x1	1%
	BROWN	1	1	1	x10	
	RED	2	2	2	x100	
	ORANGE	3	3	3	x1.000	
	YELLOW	4	4	4	x10.000	
	GREEN	5	5	5	x100.000	
	BLUE	6	6	6	x1.000.000	

DO NOT BLINDLY FOLLOW THE ORDER OF THE COMPONENTS ONTO THE TAPE. ALWAYS CHECK THEIR VALUE ON THE PARTS LIST!


CONSTRUCTION

1 Resistors



- ☐ R1: 4K7 (4 - 7 - 2 - B)
- ☐ R2: 10K (1 - 0 - 3 - B)
- ☐ R3: 4K7 (4 - 7 - 2 - B)
- ☐ R4: 4K7 (4 - 7 - 2 - B)
- ☐ R5: 10K (1 - 0 - 3 - B)
- ☐ R6: 4K7 (4 - 7 - 2 - B)
- ☐ R7: 1K (1 - 0 - 2 - B)
- ☐ R8: 1K (1 - 0 - 2 - B)
- ☐ R9: 100K (1 - 0 - 4 - B)
- ☐ R10: 10K (1 - 0 - 3 - B)

2 Ceramic capacitors




- ☐ C1: 100nF (104)

3 Shottky diode




- ☐ D1: 1N5819
- ☐ D2: 1N5819
- ☐ D3: 1N5819
- ☐ D4: 1N5819
- ☐ D5: 1N5819
- ☐ D6: 1N5819
- ☐ D7: 1N5819
- ☐ D8: 1N5819

4 Transistors




- ☐ T1: BC547B
- ☐ T2: BC547B

5 Male header



- ☐ SK8... SK10: 2x3pin



6 Female header



- ☐ 2 x 6p




Do not cut the connector pins!



- ☐ 2 x 8p


7 LED's



Watch the polarity!


- ☐ LD1
- ☐ LD2

8 Terminal blocks



- SK5 : 2p (motor 1)
- SK6 : 2p (motor 2)
- SK12 : 2p (power supply)


9 Electrolytic capacitors



Watch the polarity!



- C3: 22µF
- C2: 100µF

10 Dual Full Bridge driver




Watch the position of the notch!

□ IC1: L298P





Solder each connection

II CONNECTION DIAGRAM




DOWNLOAD SAMPLE CODE FROM KA03 PAGE ON WWW.VELLEMAN.BE






Leds and how to use them



Leds feature a specific voltage drop, depending on type and colour. Check the datasheet for exact voltage drop and rated current !



Never connect leds in parallel



How to Calculate the series resistor:

Example: operate a red led (1.7V) on a 9Vdc source.

Required led current for full brightness: 5mA (this can be found in the datasheet of the led)

$$\frac{\text{Supply voltage (V) - led voltage (V)}}{\text{required current (A)}} = \text{series resistance (ohms)}$$



$$\frac{9V - 1.7V}{0.005A} = 1460 \text{ ohm}$$

closest value :
use a 1k5 resistor

Required resistor power handling=
voltage over resistor x current passed trough resistor




$$(9V - 1.7V) \times 0.005A = 0.036W$$

a standard 1/4W resistor
will do the job

LEDs in series:

Example: 3 x red led (1.7V) on 9V battery

Required led current for full brightness: 5mA
(this can be found in the datasheet of the led)



$$\frac{\text{Supply voltage (V) - (number of leds x led voltage (V))}}{\text{required current (A)}} = \text{series resistance (ohms)}$$




$$\frac{9V - (3 \times 1.7V)}{0.005A} = 780 \text{ ohm}$$


use an
820 ohm resistor


open collector outputs

An open collector output can be compared to a switch which switches to ground when operated



Example: How to switch an LED by means of an open collector output





The new Velleman Projects catalogue is
now available. Download your copy here:

www.vellemanprojects.eu



Modifications and typographical errors reserved - © Velleman nv. HKA03'IP
Velleman NV, Legen Heirweg 33 - 9890 Gavere.