

ERSADUR long-life soldering tip series 842



- ANALOG 60/60 A
- ANALOG 80/80 A
- DIGITAL 80 A
- DIGITAL 2000 A with POWER TOOL soldering iron
- ELS 8000/M/D
- MICRO-CON 60 iA with POWER TOOL soldering iron
- MS 6000
- MS 8000/D
- MULTI-PRO
- MULTI-SPRINT
- MULTI-TC
- RDS 80
- TWIN 80 A with ERGO TOOL soldering iron

<p>0842UD/UDLF</p> <p>pencil point, 0.4 mm ϕ, extended</p>	<p>0842SD/SDLF</p> <p>pencil point, 0.8 mm ϕ, extended</p>	<p>0842BD/BDLF</p> <p>pencil point, 1.0 mm ϕ</p>
<p>0842YD/YDLF</p> <p>chisel-shaped, 1.6 mm</p>	<p>0842CD/CDLF</p> <p>chisel-shaped, 2.2 mm</p>	<p>0842KD/KDLF</p> <p>chisel-shaped, 2.2 mm, extended</p>
<p>0842ED/EDLF</p> <p>chisel-shaped, 3.2 mm</p>	<p>0842ID</p> <p>pencil point, 0.4 mm ϕ, bent</p>	<p>0842JD</p> <p>chisel-shaped, 2.2 mm, bent</p>

ERSADUR/nickel-plated desoldering tip series 722



- DIGITAL 2000 A with X-TOOL desoldering iron
- XT00LKIT1
- i-CON with X-TOOL desoldering iron
- i-CON2 with X-TOOL desoldering iron
- i-CON2 C with X-TOOL desoldering iron
- i-CON VARIO 2/4 with X-TOOL desoldering iron

<p>0722ED0821</p> <p>ERSADUR, ID 0.8 mm, OD 2.1 mm</p>	<p>0722ED1023 ERSADUR, ID 1.0 mm, OD 2.3 mm</p> <p>0722ED1226 ERSADUR, ID 1.2 mm, OD 2.6 mm</p>	<p>0722ED1529 ERSADUR, ID 1.5 mm, OD 2.9 mm</p> <p>0722ED2438 ERSADUR, ID 2.4 mm, OD 3.8 mm</p>
<p>0722EN0615S nickel-plated, ID 0.6 mm, OD 1.5 mm</p> <p>0722EN1018S nickel-plated, ID 1.0 mm, OD 1.8 mm</p>	<p>0722ED1023 nickel-plated, ID 1.0 mm, OD 2.3 mm</p> <p>0722EN0823 nickel-plated, ID 0.8 mm, OD 2.3 mm</p>	<p>0722EN1020 nickel-plated, ID 1.0 mm, OD 2.0 mm</p> <p>0722EN1023 nickel-plated, ID 1.0 mm, OD 2.3 mm</p>
<p>0722EN1223</p> <p>nickel-plated, ID 1.2 mm, OD 2.3 mm</p>	<p>0722EN1529 nickel-plated, ID 1.5 mm, OD 2.9 mm</p> <p>0722EN1548 nickel-plated, ID 1.5 mm, OD 4.8 mm</p>	<p>0722EN2332 nickel-plated, ID 2.3 mm, OD 3.2 mm</p> <p>0722EN2348 nickel-plated, ID 2.3 mm, OD 4.8 mm</p>