Rev. 3.7.13 LCM1500 Series 1 of 5

LCM1500 1500 Watts

Bulk Front End

Total Power: 1500 W # of Outputs: Single 12 to 48V Output: Optional 5.0 V standby






Electrical Specifications

Input Input range:

Input range:	90 - 264 Vac (Operating) 115/230 Vac (Nominal) TERMINAL BLOCK
Frequency:	47 - 440 Hz, Nominal 50/60
Input fusing:	Internal 20 A fuses, both lines fused
Inrush current:	\leq 25 A peak, either hot or cold start
Power factor:	0.99 typical, meets EN61000-3-2
Harmonics:	Meets IEC 1000-3-2 requirements
Input current:	18 A RMS max input current, at 100 Vac
Hold up time:	20 ms minimum for Main O/P, at full rated load
Efficiency:	> 91% typical at full Load / 230VAC nominal
Leakage current:	< 0.3 mA at 264 Vac
ON/OFF power switch:	N/A
Power line transient:	MOV directly after the fuse
Isolation(Production):	PRI-Chassis 2500 Vdc Basic PRI-SEC 2500 Vdc Reinforced SEC-Chassis 500 Vdc

LCM1500Q Efficiency Without the 5 Vsb



Special Features

- 1500 W output power
- Low Cost
- 2.5" x 5.2" x 10.0"
- 12 Watts Per Cubic Inch
- Industrial/Medical safety
- -40 °C to 70 °C with derating
- Optional 5 V @ 2 A Housekeeping
- High Efficiency: 89% typical
- Variable speed "Smart Fans"
- DSP controlled
- Conformal coat option
- ± 10% adjustment range
- Margin programming
- OR-ing FET

Compliance

- EMI Class A
- EN61000 Immunity
- RoHS 2
- PMBUS

Safety

• UL	60950-1 508/1598/1433 60601-1 Ed 3
CSA	60950-1
• VDE	60950-1
• China	60601 CCC

• CB Scheme Report/Cert

Rev. 3.7.13 LCM1500 Series 2 of 5

Output		
Output rating:	See table 1	90 - 264 Vac
Set point:	± 0.5%	90 - 264 Vac
Total regulation range:	Main output ± 2% 5 Vsb ± 1%	Combined line/load/transient when measured at output terminal
Rated load:	1500 W maximum	Derate linear to 50% from 50 °C to 70 °C
Minimum load:	Main output @ 0.0 A 5 Vsb @ 0.0 A	No loss of regulation
Output noise (PARD):	1% max p-p 50 mV max p-p	Main output 5 Vsb output Measured with a 0.1 μF Ceramic and 10 μF Tantalum Capacitor on any output, 20 MHz
Output voltage overshoot:		No overshoot/undershoot outside the regulation band during on or off cycle
Transient response:	< 300 μSec	50% load step @ 1 A/µs Step load valid between 10% to 100% of output rating Recovery time to within 1% of set point at onset of transient
Max units in parallel:		Up to 10
Short circuit protection:	Protected, no damage to occur	Bounce mode
Remote sense:		Compensation up to 500 mV
Output isolation:		Standard per safety requirements
Forced load sharing:	To within 10% of all shared outputs	Analog sharing control
Overload protection (OCP):	105% to 125% 120% to 170%	Main output 5 Vsb output
Overvoltage protection (OVP):	125% to 145% 110% to 125%	12 V output 5 Vsb output
Overtemp protection:	10 - 15 °C above safe operating area	Both PFC and output converter monitored


Environmental Specifications

Operating temperature:	-40 °C to +70 °C, linear derating to 50% from 50 °C to 70 °C
Storage temperature:	-40 °C to +85 °C
Humidity:	20 to 90%, non-condensing. Operating. Conformal coat option available
Fan noise:	< 45 dBA, 80% load at 30
Altitude:	Operating - 16,405 feet (3000m) Storage - 30,000 feet
Shock:	MIL-STD-810F 516.5, Procedure I, VI. Storage
Vibration:	MIL-STD-810F 514.5, Cat. 4, 10. Storage

Ordering Information

ordening i	monnac									
Model		Nominal Output	Set Point	Adjustment	Cur	rent	Output Ripple	Max	Combined	A
Number*	Output	Voltage Set Point	Tolerance	Range	Min	Max	P/P (0-50 deg C)	Continuous Power	Line/Load Regulation	Availability
LCM1500L	12V	12V	+/-0.5%	10.8-13.2V	0A	133A	120mV	1500	2%	APR 2013
LCM1500N	15V	15V	+/-0.5%	13.5-16.5V	0A	100A	150mV	1500	2%	AUG 2013
LCM1500Q	24V	24V	+/-0.5%	21.6-26.4V	0A	67A	240mV	1500	2%	NOW
LCM1500R	28V	28V	+/-0.5%	25.2-30.8V	0A	53.6A	280mV	1500	2%	JUNE 2013
LCM1500U	36V	36V	+/-0.5%	32.4-39.6V	0A	43A	360mV	1500	2%	MAR 2013
LCM1500W	48V	48V	+/-0.5%	43.2-52.8V	0A	33A	480mV	1500	2%	DEC 2012

Pin Assignment		
Signals	Name Description	Pin Number(s)
+Vout	Power rail	SK4
GND	Power GND	SK5
Signals	Name Description	SK2 Pin Number
A2	EEPROM Address	1
-VPROG	Return connection of external supply for Margin Programming	2
A1	EEPROM Address	3
-Vsense	Remote Sense Return	4
ISHARE	Load share voltage	5
A0	EEPROM Address	6
SDA1	Serial Data Signal (I2C)	7
+VPROG	Positive connection of external supply for Margin Programming	8
SCL1	Serial Clock Signal (I2C)	9
+Vsense	Remote Sense Positive	10
5VSB	5V standby	11
GND	5V standby Return	12
5VSB	5V standby	13
G_DCOK_C	Global DCOK Collector	14
GPIOA6	EEPROM Write Protect	15
G_DCOK_E	Global DCOK Emitter (GND)	16
GND	Return Ground for output signal and I2C communication	17
G_ACOK_C	Global ACOK Collector	18
INH_EN	Turn Off Main Output	19
G_ACOK_E	Global ACOK Emitter (GND)	20
Note: Mating connecto	or for SK2 is LANDWIN CI0120P1HD0-LF	



_	1	3	5	7	9	11	13	15	17	19
	巖	審	密	密	嚠	啣	働	嚻	●	
F	豳	歯	歯	僿	靈	串	啣	串	串	₩ -
난뇌	2	4	6	8	10	12	14	16	18	20

Signal Output Signal Connectors (SK2)

LED Indicators

2 provided are clearly visible up to a 45 degree offset from vertical with office environment ambient lighting. The status is reflected in the indicator color.

The DC_OK LED is bicolor. It shall light green if the DC output is within specification, and amber if the output falls out of specification.

The AC_OK LED is Green if the AC is within specification and off when out of specification. Note: With 5 V standby, Amber also indicates that PSU is in standby mode/output off.

Control Signals

AC_OK Open collector 0.5 V maximum at 10 mA. Both emitter and collector access provided. **DC_OK** Open collector 0.5 V maximum at 10 mA. Both emitter and collector access provided. **PS_INHIBIT/ENABLE Signal** 0.0 - 0.5 V contact closure, output OFF Rev. 3.7.13 LCM1500 Series 3 of 5

Rev. 3.7.13

								LCM15
Ordering Informat	tion							
LCMXXXXY	-	- A	-	В	-	С	-	###
Case Size		Input Termination		Acoustic Noise		Option Codes		Hardware Code
1-Phase input where λ	XXX=							
1500 = 2.4" x 5.0" x 1 , 1500W	0.0"			Blank = Standard		Blank = No Options		Factory Assigned for Modiefied standards
		T = Terminal Block				1 = Conformal Coat		
Voltage Code Y =						4 = 5V Standby		
Code						5 = Opt 1 + 4		
L	12							
Ν	15							

Mechanical Drawing - IEC Input

24

36


48


Weight: 4.20 lbs (1.91 Kg)


Q


U

W










Accessories



Order kit part number 73-788-001 for control connector interface with .3m wires attached



Order kit part number 73-788-002 for control connector interface with unloaded housing and 20 pins

Miscellaneous Specifications

Burn-In

100% Burn-in at 45 °C, at 80 - 90 % load. Duration of burn-in determined by Quality Assurance Procedures

MTBF

The power supply has a minimum MTBF of 300K hours using the Bell core 332, issue 6 specification @ 25 °C and 40 °C, ambient, at full load. With the power supply installed in a system in a 25 °C ambient environment and operating at full load, capacitor life shall be 10 years, minimum for ALL electrolytic capacitors contained within this power supply. The power supply shall demonstrate a MTBF level of > 500,000 hours.

Quality Assurance

Full QAV testing shall be conducted in accordance with Emerson Network Power Standards with reports available upon request.

Warranty

Emerson Network Power shall warrant the power supply to be free of defects in materials and workmanship for a minimum period of three years from the date of shipment, when operated within specifications. The warranty shall be fully transferable to the end owner of the equipment powered by the supply.

Americas

LCM1500 Series 5810 Van Allen Way Carlsbad, CA 92008

Rev 3713

5 of 5

USA Telephone: +1 760 930 4600 Facsimile: +1 760 930 0698

Europe (UK)

Waterfront Business Park Merry Hill, Dudley West Midlands, DY5 1LX United Kinadom Telephone: +44 (0) 1384 842 211 Facsimile: +44 (0) 1384 843 355

Asia (HK)

14/F, Lu Plaza 2 Wing Yip Street Kwun Tong, Kowloon Hong Kong Telephone: +852 2176 3333 Facsimile: +852 2176 3888

For global contact, visit:


www.Emerson.com/EmbeddedPower

techsupport.embeddedpower @emerson.com

While every precaution has been taken to ensure accuracy and completeness in this literature, Emerson Network Power assumes no responsibility, and disclaims all liability for damages resulting from use of this information or for any errors or omissions.

Emerson Network Power.

The global leader in enabling business-critical continuity.



EmersonNetworkPower.com

Emerson and the Emerson Network Power logo are trademarks of Emerson Electric Co. ©2013 Emerson Electric Co. All rights reserved.