


# Data Sheet

## RT063xxHBWC

### Illustration



see enlarged drawing at the end of the document

### Product specification

- screw type terminal block, solderable
- centerline 3.50 mm, direction of connection 90°
- wire protector, fittable without loss of poles
- color black
- Connection data

**CRIUS** V / A / AWG 150 / 10 / 28 - 16

**SEV** 1 mm<sup>2</sup> 125 V / 13.5 A / T60

# Data Sheet



## RT063xxHBWC

### Technical Data

#### General Data

Tightening torque SEV	0.15 Nm		
Tightening torque UL	3 lb-in		
Solder pin length	3.4 mm		
min. number of poles	2		
max. number of poles	16		
Insulating material class	CTI 600		
clearance/creepage dist.	2.1 mm		
protection category	IP 00		
Overvoltage category	III	III	II
Pollution degree	3	2	2
Rated voltage	160 V	400 V	400 V
Rated test voltage	2.5 kV	2.5 kV	2.5 kV

#### Connection data

 V / A / AWG	150 / 10 / 28 - 16
 1 mm <sup>2</sup>	125 V / 13.5 A / T60

#### Material

insulating material	PA66
flammability class	V0
terminal body material	CuZn
terminal body surface	Cu + Ni + Sn
screw surface	Zn Cr(VI)-frei/free
wire protector material	CuSn
wire protector surface	Sn
screw thread	M2

#### Climatic properties

upper limit temperature	105 °C
lower limit temperature	-40 °C

#### General

solderability	For THR products acc. to IPC/JEDEC J-STD-020D-MSL 1   For THT products max. 260 °C / 10 s
Tolerance	ISO 2768 -mH

# Data Sheet

## RT063xxHBWC

Page 3/4

P/N


310591xx

xx=number of poles

2013/12/05

### Illustration

Drawing



$L = (\text{pole size} - 1) \times \text{centerline} + 3.5 [0.138]$



# Data Sheet

## RT063xxHBWC

Page 4/4

P/N

310591xx

xx=number of poles

2013/12/05

### PCB Layout

