




PART NUMBER	CRIMP ID	ØA ±.13 [.005]	ØB ±.13 [.005]	ØC ±.13 [.005]	CONDUCTOR WIRE SIZE REF 	WEIGHT REF GR [OZ]
SRK-PC-080-16-**	A	8.10 [.319]	5.20 [.205]	9.59 [.378]	16mm ² 6 AWG	16.26 [.574]
SRK-PC-080-20-**	B	8.10 [.319]	5.80 [.228]	9.59 [.378]	5 AWG	15.65 [.552]
SRK-PC-080-25-**	C	9.50 [.374]	6.90 [.272]	9.50 [.374]	25mm ² 4 AWG	16.51 [.582]
SRK-PC-080-32-**	D	11.30 [.445]	8.00 [.315]	9.59 [.374]	2 AWG	18.36 [.648]
SRK-PC-080-35-**	E	12.00 [.472]	8.90 [.350]	9.59 [.374]	35mm ²	18.34 [.647]

REV
A

SRK-PC-080-16/35-**

REVISIONS

SYM	DESCRIPTION	DATE	APPROVED
NC	NEW RELEASE PER E.O. P20459	3-5-10	R.D.R.
A	REVISED PER E.O. P20612	9-9-10	RDR



4. WHEN ** = 601: PLATING IS SILVER AND MAY TARNISH.

3. MATERIAL: COPPER.

2. DIMENSIONS ARE IN MILLIMETERS [inch].

 FOR CRIMPING INFORMATION SEE DRAWING 8925-003-0000.

NOTES: UNLESS OTHERWISE SPECIFIED

	SIGNATURE & DATE
DR	D. MEYER 03-04-10
CHK	D. Meyer 9/9/10
PE	D. Meyer 9/9/10
APPD	R. Reed 9-9-10
SCALE	NONE WT SEE TABLE

CONTACT, PIN, Ø8mm

SRK SERIES

ENVELOPE

EP 199	MATL. CODE
	3850 INDUSTRIAL AVE. HEMET, CA 92545
B	SRK-PC-080-16/35-**
DWG SIZE	CODE 11139 SHEET OF