




PART NUMBER	CRIMP ID	ØA ±.13 [.005]	ØB ±.13 [.005]	ØC ±.13 [.005]	CONDUCTOR WIRE SIZE REF 	WEIGHT REF GR [OZ]
SRK-SC-080-16-**	A	8.10 [.319]	5.20 [.205]	9.59 [.378]	16mm ² 6 AWG	12.53 [.442]
SRK-SC-080-20-**	B	8.10 [.319]	5.80 [.228]	9.59 [.378]	5 AWG	11.91 [.420]
SRK-SC-080-25-**	C	9.50 [.374]	6.90 [.272]	9.50 [.374]	25mm ² 4 AWG	12.76 [.450]
SRK-SC-080-32-**	D	11.30 [.445]	8.00 [.315]	9.59 [.374]	2 AWG	14.59 [.515]
SRK-SC-080-35-**	E	12.00 [.472]	8.90 [.350]	9.59 [.374]	35mm ²	14.55 [.513]



REV
A
SRK-SC-080-16/35-**

REVISIONS			
SYM	DESCRIPTION	DATE	APPROVED
NC	NEW RELEASE PER E.O. P20459	3-5-10	R.D.R.
A	REVISED PER E.O. P20612	9-9-10	



4. WHEN ** = 601: PLATING IS SILVER AND MAY TARNISH.
3. MATERIAL: SOCKET BODY & INSERT: COPPER.
2. DIMENSIONS ARE IN MILLIMETERS [inch].
-  FOR CRIMPING INFORMATION SEE DRAWING 8925-003-0000.

NOTES: UNLESS OTHERWISE SPECIFIED

SIGNATURE & DATE		CONTACT, SOCKET, Ø 8mm		EP 199	MATL. CODE
DR	D. MEYER 03-05-10	SRK SERIES		 3850 INDUSTRIAL AVE. HEMET, CA 92545	
CHK	D. Meyer 9/9/10				
PE	D. Meyer 9/9/10				
APPD	R. Rad 9-9-10	ENVELOPE		B SRK-SC-080-16/35-**	
SCALE	NONE				
WT SEE TABLE				DWG SIZE	CODE 11139 SHEET 1 OF 1