



199Z Master Precision Level

The Starrett 199 Master Precision Level provides the ability to ensure a level machine setup, which in turn increases the efficiency of modern, high speed machinery. Master Precision Level, 15" (380mm)



- Specially designed to set up, check and test machinery of all types
- At-a-glance reading of the exact variation of machinery levelness
- Auxiliary level vial shows lateral position and assists in horizontal setting
- Level vials are positioned so breakage is reduced to a minimum
- Fool-proof adjustment
- Seasoned, machined castings
- Finished wood case
- Groove has a special involute design, permitting better centering and greater capacity to handle larger rounds
- Groove and bearing flats are machined together for maximum accuracy
- Ground and graduated main vial of 10-second accuracy; one division equals 1/2 thousandth (0.0005) of an inch per foot, or 0.04mm per meter
- Main vials have seven graduations on each side of the bubble
Special alloy iron used to obtain freedom from thermal effects All level bases are made from the finest quality seasoned cast iron and are precision-machined on the reference surface Scraped reference surface

Specifications

Length (in)	15"
Length (mm)	380mm
Width (in)	1-5/8"
Width (mm)	40mm